

ELECTRONIC PLIERS ESD

CLASSICline 2.0

- box joint - double leaf spring
- mirror polished - ergonomically formed bicoloured hand guard

CUTTING PLIERS

No.	Lenght mm	Headwidth mm	Finish	Cutting capacity			Weight g
				Wire soft	mm medium	Ø hard	

Side cutters

with slim, rounded head

3-601-15	115	11	semi flush	1.5	1.2	0.4	70
3-602-15	115	11	flush	1.5	1.2	-	70

Side cutters

with slim, pointed head and special flat cutting edge

3-603-15	115	11	semi flush	1.5	1.2	0.3	65
3-604-15	115	11	flush	1.5	1.2	-	65

End cutters

with angular tips 30° and oblique cutting edge

3-606-15	120	10,5	flush	0.8	0.6	-	55
----------	-----	------	-------	-----	-----	---	----

Oblique top cutters

with angular tips 15°

3-625-15	120	10,5	flush	1.5	1.2	-	90
----------	-----	------	-------	-----	-----	---	----

Top cutters

with 17 mm width tips

3-627-15	120	10,5	flush	1.5	1.2	-	85
----------	-----	------	-------	-----	-----	---	----

ROUND, FLAT AND SNIPE NOSE PLIERS

3-631-15	Round nose pliers	120	10	plain jaws	55
3-632-15	Flat nose pliers	120	9	plain jaws	60
3-633-15	Snipe nose pliers	120	10	plain jaws	60
3-634-15	Snipe nose pliers, angular	120	10	plain jaws	60

3-650 V BERNSTEIN ESD Set of pliers

5-piece set dissipative pliers from the series POLISHline on the ESD tool holder "VARIO"

No. Description of individual tools Weight: 750 g

3-601-15	Side cutters, 120 mm, for soft wire up to 1.5 mm, for hard wire up to 0.4 mm
3-631-15	Round nose pliers, 120 mm, plain jaws
3-632-15	Flat nose pliers, 120 mm, plain jaws
3-633-15	Snipe nose pliers, 120 mm, plain jaws
3-634-15	Snipe nose pliers, angular, 120 mm, plain jaws



3-601-15



3-602-15



3-603-15



3-604-15



3-606-15



3-625-15



3-627-15



3-631-15



3-632-15



3-633-15



3-634-15



3-650V