

Wiha SoftFinish® electric.

The safe and comfortable insulated VDE screwdriver.



The right tool at a glance, thanks to the printed screw symbol on the handle end.



For slotted screws.



320N

SoftFinish® electric slotted screwdriver.

Individually tested protective insulation 1,000 V AC, VDE and GS tested.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.
Insulation moulded directly onto blade.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN ISO 2380.
Manufactured acc. to IEC 60900:2012.

Application: For all work on or around electrical components up to 1,000 V AC.

Order-No.	⌀	↔	⊖	↔	↔	↔
00819	2.0	60	0.4	164	23	10
00820	2.5	75	0.4	179	23	10
00821	3.0	100	0.5	204	23	10
00822	3.5	100	0.6	204	23	10
00823	4.0	100	0.8	211	30	10
00824	4.5•	125	1.0	236	30	10
00825	4.5•	175	1.0	286	30	5
31863	4.5•	200	1.0	311	30	10
00826	5.5	125	1.0	243	36	10
00827	5.5•	175	1.0	293	36	5
00828	6.0•	150	1.2	268	36	10
00829	6.5	150	1.2	268	36	10
00830	8.0	175	1.2	299	41	10
00831	8.0	175	1.6	299	41	10
00832	10.0	200	1.6	324	41	10

• Additional dimension. Non-DIN size.



Wiha SoftFinish® electric.

- Safety when working with live equipment up to 1,000 V AC and 1,500 V DC
- Each screwdriver is individually tested in a water bath at 10,000 volts according to IEC 60900:2012
- Awarded the GS symbol for tested safety
- Multi-component SoftFinish® handle provides maximum user comfort

Applications on live equipment are subject to very special requirements. The focus is on absolute user safety and Wiha demonstrates this with a wealth of details.

The high quality blade insulation is moulded directly onto the blade and therefore guarantees safety when working on live equipment up to 1,500 V DC / 1,000 V AC. To maintain this safety, each screwdriver of the SoftFinish® electric series is individually tested in a water bath at 10,000 Volts according to IEC 60900:2012.

The roll-off protection and the special handle geometry offer optimum handling and electrical safety, even in critical applications.

Wiha SoftFinish® electric.

The safe and comfortable insulated VDE screwdriver.

For Phillips, Pozidriv and TORX® screws.



1000 V
IEC 60900:2012

321N SoftFinish® electric Phillips screwdriver.
Individually tested protective insulation
1,000 V AC, VDE and GS tested.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.

Insulation moulded directly onto blade.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN ISO 8764. Manufactured acc. to IEC 60900:2012.

Application: For all work on or around electrical components up to 1,000 V AC.

Order-No.	PH	PZ	T	Icons	
00846	PH0	60	164	23	10
00847	PH1	80	191	30	10
00848	PH2	100	218	36	10
00849	PH3	150	268	41	10
00850	PH4	200	318	41	5



1000 V
IEC 60900:2012

324 SoftFinish® electric Pozidriv screwdriver.
Individually tested protective insulation
1,000 V AC, VDE and GS tested.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.

Insulation moulded directly onto blade.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN ISO 8764. Manufactured acc. to IEC 60900:2012.

Application: For all work on or around electrical components up to 1,000 V AC.

Order-No.	PZ	T	Icons		
00877	PZ0	60	164	23	10
00878	PZ1	80	191	30	10
00879	PZ2	100	218	36	10
00880	PZ3	150	324	41	5



1000 V
IEC 60900:2012

325 SoftFinish® electric TORX® screwdriver.
Individually tested protective insulation
1,000 V AC, VDE and GS tested.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish.

Insulation moulded directly onto blade.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: Manufactured acc. to IEC 60900:2012.

Application: For all work on or around electrical components up to 1,000 V AC.

Extra: Sizes T10 to T40 are in the 3251 series with the slimFix screwdrivers.

Order-No.	T	Icons			
03760	T5	60	164	23	10
03761	T6	60	164	23	10
03762	T7	60	164	23	10
00881	T8	60	164	23	10
00882	T9	60	164	23	10

For allen screws and internal square-drive screws.



1000 V
IEC 60900:2012

322 SoftFinish® electric hex nut driver.
Individually tested protective insulation
1,000 V AC, VDE and GS tested.

Blade: Chrome-vanadium steel, through hardened, black-finish.
Insulation moulded directly onto blade.

Deep drawn socket.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 3125. Manufactured acc. to IEC 60900:2012.

Application: For external hex screws and hex nuts.

Order-No.	Hex	Icons				
00853	4	125	236	30	10.2	10
00855	5	125	236	30	11.2	10
00856	5.5	125	236	30	11.2	10
00857	6	125	236	30	12.2	10
00858	7	125	243	36	14.5	10
00859	8	125	243	36	15.2	10
00860	9	125	243	36	16.0	10
00861	10	125	243	36	17.2	10
00862	11	125	243	41	19.2	5
00863	12	125	243	41	20.2	5
00864	13	125	243	41	22.2	5
00865	14	125	243	41	23.2	5
00866	15	125	243	41	25.2	5
00867	16	125	243	41	25.2	5
00868	17	125	243	41	27.2	5



1000 V
IEC 60900:2012

323N SoftFinish® electric hex screwdriver.
Individually tested protective insulation
1,000 V AC, VDE and GS tested.

Blade: Chrome-vanadium steel, through hardened, black-finish.
Insulation moulded directly onto blade.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: Manufactured acc. to IEC 60900:2012.

Application: For allen screws.

Order-No.	Hex	Icons			
30361	2.5	75	179	23	10
30362	3.0	75	179	23	10
30363	4.0	75	186	30	10
30364	5.0	75	186	30	10
30365	6.0	100	218	36	10
30366	8.0	100	218	36	10



1000 V
IEC 60900:2012

358N SoftFinish® electric square (Robertson) screwdriver.
Individually tested protective insulation
1,000 V AC, VDE and GS tested.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, black-finish. Insulation moulded directly onto blade.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: Manufactured acc. to IEC 60900:2012.

Application: For fastening and unfastening internal square-drive (Robertson) screws.

Order-No.	Robertson	Icons				
32396	Robertson 1	2.3	100	211	30	10
32397	Robertson 2	2.8	150	268	36	10