



OVERHEAD TRANSPARENCIES: B/W LASER PRINTERS & COPIERS

- Special coating for pin-sharp printouts and excellent toner adhesion
- Multi-sheet feed, via collective tray
- Available with (for optical pass-through) or without sensor strip / backing paper
- Quick and hassle-free creating of presentations
- Water-based coating

Art No.	Format DIN	Description	Multi sheet feed	Thickness transparency	Content	Printers I L K CL
1 3552	A4	coated	•	0,10 mm	100	• •
1 3562	A4	coated	•	0,10 mm	25	• •
1 3563	A4	coated, extremely heat -resistant with increased transparency thickness	•	0,13 mm	100	• •
2 3553	A4	coated, with removable sensor strip on the long side	•	0,10 mm	100	• •



OVERHEAD TRANSPARENCIES FOR B/W COPIERS

- Either with backing paper glued top edge or side edge
- Available with backing paper for optical pass-through
- Quick and hassle-free creating of presentations
- · Water-based coating


	Art No.	Format DIN	Description	Multi sheet feed	Thickness transparency	Content	Printers I L K CL
3	3555	A4	Uncoated, with paper interleaved, only for single sheet feed		0,10 mm	100	•
4	3557	A4	Coated, glued top edge backing paper	•	0,10 mm	100	•
4	3567	A4	Coated, glued top edge backing paper	•	0,10 mm	10	•
6	3568	A4	Coated, glued side edge backing paper	•	0,10 mm	10	•

OVERHEAD TRANSPARENCIES FOR COLOUR LASER PRINTER

- Special coating for pin-sharp printouts and excellent toner adhesion
- Multi-sheet feed, via collective tray
- Available with sensor strip for optical pass-through
- · Quick and hassle-free creating of presentations in brilliant colours
- Water-based coating

	Art No.	Format DIN	Description	Multi sheet feed	Thickness transparency	Content	Printers I L K CL
6	3559	A4	Special coating, with removable sensor strip on the short side	•	0,10 mm	50	•
2	3560	A4	Special coating, with removable sensor strip on the long side	•	0,10 mm	50	•
7	3561	A4	Special coating, extremely heat -resistant with increased transparency thickness	•	0,13 mm	50	•
7	3566	A4	Special coating, extremely heat -resistant with increased transparency thickness	•	0,13 mm	20	•





1 3552/3562/3563Coated transparencies



2 3553/3560 Coated transparencies, with removable sensor strip on the long side



3555 Uncoated transparencies with paper interleaved, only for single sheet feed



4 3557/3567 Coated transparencies glued top edge backing paper



3568
Coated transparencies glued side edge backing paper



Coated transparencies, with removable sensor strip on the short side



7 3561/3566 Coated transparency, extremely heat -resistant