Wiha SYSTEM 6.

The space-saving all-rounder.



Are you looking for a versatile and space-saving system for your toolbox or for use on the road?

Then our **SYSTEM 6** exchange tools with 6 mm reversible blades and suitable handles are exactly the right solution for you. Just select the right variations for your application among the wide choice of handles and reversible blades or simply decide for one of the **SYSTEM 6** sets.

• The starter sets with tough roll-up bag are already equipped with the most common reversible blades, but also offer room for a maximum of 11 further reversible blades.

• The extensive professional sets are the perfect solution if you need a professional universal set in a rigid box.


• The practical roll-up bag sets are especially handy and space-saving.

The Wiha **SYSTEM 6** reversible blade systems are high quality products with industrial quality that fulfill maximum demands thanks to first class materials and manufacturing. The 150 mm long reversible blades are manufactured from chrome-vanadium molybdenum steel and are through hardened. The various handles are particularly ergonomically designed and guaranteeing optimal power transmission.

With the Wiha **SYSTEM 6** series you always have the right tool on hand for a wide range of applications - ideal for industry, trade and the ambitious handymen.



The Wiha SYSTEM 6 range is the compact all-rounder for different applications.



Thanks to the ClickStop ball clamp in each telescopic handle, 24 different visible blade lengths can be set between 42 and 114 mm in 3 mm increments.

Wiha SYSTEM 6.

- Versatile reversible blade system in industrial quality
- Expandable individual tool system
- Ergonomic handles for almost every application
- Blades of high-quality, tough yet elastic chrome-vanadium-molybdenum steel, through hardened
- Titanium silver surface for high corrosion protection



Wiha SYSTEM 6.

can also be used for TORX® screws,

but not vice versa.

The space-saving all-rounder.

-						-	-						
	SYSTEM 6 TORX [®] Tamper Resistant reversible blade. For TORX [®] screws with locking pin.						0						
84							7802 SYSTEM 6 bit holder.						
ade:	High quality CVM steel, through hardened. Titanium silver, laserd tip sizes. With borehole in the blade tip.						Blade:	Suitable for C 6.3 and E 6.3 (1/4") bits. Chrome-vanadium steel, through hardened. Titanium silver.					
								Bit retainer made of stainless steel with integrated permanent magne					
Order-No.	۲	۲		• 1	_		Order-No. 03882	0	150	• 1		4	5
27630	T6H	T8H	← 150	6.0	5		03002	1/4	150	6.0	10		0
27631	T7H	T9H	150	6.0	5								
27632	T10H	T15H	150	6.0	5								
27633	T20H	T25H	150	6.0	5			tin	David St. 1				in the second
27634	T30H	T40H	150	6.0	5		\cup	-					
_						_	7803	SYSTE	M 6 adap	ter blad	e.		
									le for 1/4"	-			
004	OVOTE		Vin of the second	ugunikla klada			Blade:		e-vanadiun Juare drive		hrough hardened retainer.	d. Titanium silve	r.
284		Wing® se	-	versible blade. crews.			Order-No.		·			4	-
Blade:		-	-	nrough hardened.			03883	1/4	150	6.0			5
		n silver, la											-
Order-No.	٩	Ð	$\overline{\longleftrightarrow}$	●1									
27637	TW0	TW1	150	6.0	5		\cap						
27638	TW2	TW3	150	6.0	5			10	_	a second			
27639	TW4	TW5	150	6.0	5		NEW						
							28339-91				iversal bit holde	er.	
									modates		s.		
	0	- 197		wite	N4		Blade: Application:		uality CVM plications v		commended torg	ue settinas are	important.
204			A 18										1
284				versible blade.			Order-No. 39255	0		۲		4	
N = -l =	For Torq-Set® security screws.							1/4	45	6	11.4		1
lade:		n silver, la											
Order-No.	Ð	Ð		• 1	_			10	-	-			
27635	TS2	TS4	150	6.0	5				-	_			
27636	TS6	TS8	150	6.0	5		NEW						
							28339-92	Torque	TR / Topr	a 2K ad	lapter blade.		
								Suitab	le for 1/4"	respc. 3	3/8" square soc	kets.	
							Blade:		uality CVM				
$\mathbf{)}$					ally		Application:	For cor	ntrolled turr	ning of s	crews with nuts a	at a prescribed	torque.
	_						Order-No.	0		۲			_
J109 00	SYSTE	M 6 exte	nsion bl	ade.			39256	1/4	52	6			1
		e for bla					39250	3/8	52	6			1
lade:	Chrome-vanadium steel, through hardened. Titanium silver.						00201	5/0	52	0			
				ades up to 100 mn									
Order-No.	0		• 1		-								
08921	6.0	↔ 150	6.0	, 11	5		\cap	(married	-	1000			
			0.0		ŭ			and the second	-	1			
							NEW	0.407-		· · · · ·	- 01/		
							28339-94		M 6 adap	•			
	Wiha Info								on of SYS		lades.		
							Blade:	High qu	uality CVM	steel.			
	Did yo	u alread	y know?	,			•	•		0			
	TORX®	Tamper	Resistan	t screwdrivers			Order-No.	0		۲		4	
				RX [®] screws			39383	6	58.5	6			

39383

