



3M™ 4000 Series Maintenance-Free Reusable Respirators

The 4000 Series Respirators by 3M are a range of ready-to-use, maintenance-free half masks designed for effective and comfortable protection against a combination of many gases, vapours and particulate

hazards found throughout industry. Utilising unique filter technology enables a very low-profile design for undisturbed field of vision to make your worklife more comfortable.

Features and Benefits:

Facepiece

- + Low profile design for better peripheral vision
- + Lightweight, well balanced design
- + Soft, non-allergenic material with textured face seal

Built In Filters

- + Four versions available, each offering protection against differing hazards throughout industry
- + One piece, maintenance-free construction

Exhalation Valve

- + Central position for effective removal of heat and moisture build up within face piece

Adjustable Head Cradle and Neck Straps

- + Stable secure fit
- + Easy to fasten neck strap

Cost Effective

- + Use until damaged, particulate filters clog, gas filters become saturated or after one month

Convenience

- + Resealable bag provides convenient and clean storage between uses

Extras

- + 3M™ 400 Overspray Guard pre-filter is available to help prolong the life of the main particulate filters

Compatible with

- + Eyewear from 3M
- + Hearing Protection from 3M



3M™ 4251 Maintenance-Free Respirator
EN405:2001+A1:2009

3M™ 4000 Series Maintenance Free Respirators available:

3M™ 4251
Organic vapour +
particulate respirator
FFA1P2 R D

3M™ 4255
Organic vapour +
particulate respirator
FFA2P3 R D

3M™ 4279
Organic vapour /
inorganic + acid gas /
ammonia / particulate
respirator
FFABEK1P3 R D

3M™ 4277
Organic vapour /
inorganic +
acid gas / particulate
respirator
FFABE1P3 R D

3M™ Accessories for 4000 Series



3M™ 400
Overspray Guard