


Sheets and accessories



Smooth sheets

Color	Thickness	Packaging	Min.OU	Width	Length	EAN / item no.
1 Galvanized steel sheet						
galvanized	0.5 mm	loose	5 pcs.	250 mm	500 mm	4001116380549
galvanized	0.5 mm	loose	5 pcs.	120 mm	1000 mm	4001116380501
galvanized	0.5 mm	loose	5 pcs.	200 mm	1000 mm	4001116380518
galvanized	0.5 mm	loose	5 pcs.	300 mm	1000 mm	4001116380525
galvanized	0.5 mm	loose	5 pcs.	600 mm	1000 mm	4001116380532
galvanized	0,5 mm	loose	5 pcs.	1000 mm	2000 mm	4001116380594
1 Raw steel sheet						
raw	0.75 mm	sealed	5 pcs.	250 mm	500 mm	4001116381041
raw	0.75 mm	sealed	5 pcs.	120 mm	1000 mm	4001116381003
raw	0.75 mm	sealed	5 pcs.	200 mm	1000 mm	4001116381010
raw	0.75 mm	sealed	5 pcs.	300 mm	1000 mm	4001116381027
raw	0.75 mm	sealed	5 pcs.	600 mm	1000 mm	4001116381034
raw	0,75 mm	loose	5 pcs.	1000 mm	2000 mm	4001116381096
1 Copper sheet, solid						
copper	0.5 mm	sealed	5 pcs.	250 mm	500 mm	4001116381546
copper	0.5 mm	sealed	5 pcs.	120 mm	1000 mm	4001116381508
copper	0.5 mm	sealed	5 pcs.	200 mm	1000 mm	4001116381515
copper	0.5 mm	sealed	5 pcs.	300 mm	1000 mm	4001116381522
copper	0.5 mm	sealed	5 pcs.	600 mm	1000 mm	4001116381539
1 Stainless steel sheet						
stainless steel	0,5 mm	sealed	2 pcs.	250 mm	500 mm	4001116382543
stainless steel	0,5 mm	sealed	2 pcs.	120 mm	1000 mm	4001116382505
stainless steel	0,5 mm	sealed	2 pcs.	200 mm	1000 mm	4001116382512
stainless steel	0,5 mm	sealed	2 pcs.	300 mm	1000 mm	4001116382529
stainless steel	0,5 mm	sealed	2 pcs.	600 mm	1000 mm	4001116382536