

Installation mandrels for **HELICOIL® Plus**



**Only for HELICOIL® Plus thread inserts type
Free Running.**

Not to be used for type Screwlock!

Thread size	Installation mandrel for HELICOIL® Plus		
	d x P	Order no.	€
M 2		4150 010 2000	on request
M 2.5		4150 012 5000	on request
M 3		4150 010 3000	on request
M 3.5		4150 013 5000	on request
M 4		4150 010 4000	on request
M 5		4150 010 5000	on request
M 6		4150 010 6000	on request
M 6*		4150 906 0002	on request
M 6**		4169 230 6002	on request
M 7		4150 010 7000	on request
M 8		4150 010 8000	on request
M 8 x 1		4150 010 8300	on request
M 9		4150 010 9000	on request
M 10		4150 011 0000	on request
M 10 x 1		4150 011 0300	on request
M 10 x 1.25		4150 011 0900	on request
M 11		4150 011 1000	on request
M 12		4150 011 2000	on request
M 12 x 1.25		4150 011 2900	on request
M 12 x 1.5		4150 011 2400	on request
M 14		4150 011 4000	on request
M 14 x 1.25		4150 011 4900	on request
M 14 x 1.5		4150 011 4400	on request
M 16		4150 011 6000	on request
M 16 x 1.5		4150 011 6400	on request
M 18		4150 011 8000	on request
M 18 x 1.5***		4150 918 4001	on request
M 20		4150 012 0000	on request
M 22		4150 012 2000	on request
M 24		4150 012 4000	on request

*M 6: for injector screw kit 4185 906 0002

**M 6: for injector screw kit 4185 906 0004

***M 18 x 1.5: for lambda probe kit 4185 918 4003