



Original Consumables Catalogue

**ALIVE WITH COLOUR**



# OKI Original Consumables

## 5 Reasons why OKI Original Consumables gives you the best value for money.




### Big on colour, small on mono costs

With OKI's LED colour range for the office, it will never cost you more to print mono pages on an OKI colour device than on a standard mono printer. So you can keep printing your black and white documents and colour is available when you want to stand out. We believe that every business deserves great graphics, reliable printing and flexible media capability.

### Always the best quality

Using OKI's Original Consumables with OKI's hardware guarantees quality for every print. Third party products aren't designed specifically for OKI's devices, so they can't guarantee the stunning print quality, low cost and reliability you enjoy with OKI's Original Consumables.



### Warranty

To give you complete peace of mind, OKI's hardware comes with a three-year warranty as standard on registration of your device within 30 days of purchase, and providing you continue to use OKI Original Consumables.

### Helpful advice when you need it

If you're ever unsure about OKI's products, our dedicated Customer Service Desk and friendly, professional staff are always on hand to help you with any queries you may have. However, we can only provide support for OKI Original Consumables.



### Guaranteed toner yields

OKI uses ISO-approved testing methods to accurately determine the declared yield for our original toner cartridges. That means you always get the number of pages promised from your OKI Original Consumables.

# Protect your business

OKI Original Consumables are specifically designed and crafted to fit your device perfectly. This precision matching is why only OKI Original Consumables offer guaranteed reliability and print quality.



Keypoint Intelligence Buyers Lab, an industry-leading independent research analyst and testing firm, compared the performance, image quality, reliability and yields of genuine OKI Original Consumables versus three third-party compatible cartridges.\*

BLI tested OKI Original Consumables and third-party products used in OKI devices and found the following benefits of OKI Original Consumables:



Better print yields



Higher quality print



Consistent colour and quality



No delivery spillage



No damage to devices

\*Visit your local OKI website for further information on BLI Testing.

## How to check if your consumables are OKI Original



### 1) Look for the hologram

You can always tell if a product is an OKI Original Consumable by looking for the hologram on the packaging and making sure you can see numbers 18 and 81 in the holographic 'window'.

### 2) Check the serial number

Every OKI Original Consumable has a unique serial number. Visit the OKI website for the authentication tool.



Colour pg 4

Mono pg 14

MFPs pg 17

Dot Matrix pg 26

# Colour Printers

Did you know...  
**OKI offers a 3 year warranty  
 at no extra cost if you register  
 your product within 30 days  
 of purchase.**



## C500 Series printers

Printer model	Consumable	Order code	Unitary EAN code	Life (pages)	Gross dimensions (mm) w x d x h
C510/C511/C530/C531	Std Cap Black Toner	44469803	5031713047995	3,500	314 x 112 x 120
C510/C511/C530/C531	Std Cap Cyan Toner	44469706	5031713047988	2,000	300 x 56 x 52
C510/C511/C530/C531	Std Cap Magenta Toner	44469705	5031713047971	2,000	300 x 56 x 52
C510/C511/C530/C531	Std Cap Yellow Toner	44469704	5031713047964	2,000	300 x 56 x 52
C510/C530	High Cap Black Toner	44469804	5031713048008	5,000	312 x 123 x 123
C511/C531	High Cap Black Toner	44973508	5031713054825	7,000	312 x 123 x 123
C510/C511/C530/C531	High Cap Cyan Toner	44469724	5031713048626	5,000	300 x 56 x 52
C510/C511/C530/C531	High Cap Magenta Toner	44469723	5031713048619	5,000	300 x 56 x 52
C510/C511/C530/C531	High Cap Yellow Toner	44469722	5031713048602	5,000	300 x 56 x 52
C532/C542	Std Cap Black Toner	46490404	5031713067689	1,500	305 x 106 x 73
C532/C542	Std Cap Cyan Toner	46490403	5031713067672	1,500	305 x 106 x 73
C532/C542	Std Cap Magenta Toner	46490402	5031713067665	1,500	305 x 106 x 73
C532/C542	Std Cap Yellow Toner	46490401	5031713067658	1,500	305 x 106 x 73
C532/C542	High Cap Black Toner	46490608	5031713067764	7,000	305 x 106 x 73
C532/C542	High Cap Cyan Toner	46490607	5031713067757	6,000	305 x 106 x 73
C532/C542	High Cap Magenta Toner	46490606	5031713067740	6,000	305 x 106 x 73
C532/C542	High Cap Yellow Toner	46490605	5031713067733	6,000	305 x 106 x 73
C510/C530	Image Drum Unit	44494202	5031713048947	20,000	392 x 385 x 320
C511/C531	Image Drum Unit	44968301	5031713054702	30,000 K 20,000 CMY	396 x 376 x 241
C532/C542	Black Image Drum	46484108	5031713068167	30,000	322 x 138 x 82
C532/C542	Cyan Image Drum	46484107	5031713068150	30,000	322 x 138 x 82
C532/C542	Magenta Image Drum	46484106	5031713068143	30,000	322 x 138 x 82
C532/C542	Yellow Image Drum	46484105	5031713068136	30,000	322 x 138 x 82
C510/C511/C530/C531	Transfer Belt	44472202	5031713048961	60,000	378 x 374 x 167
C532/C542	Transfer Belt	46394902	5031713066705	60,000	390 x 140 x 248
C510/C511/C530/C531	Fuser Unit	44472603	5031713048954	60,000	387 x 142 x 243
C532/C542	Fuser Unit	46358502	5031713066712	60,000	389 x 376 x 165

NB Toner yields based on ISO/IEC 19798 • Drums average A4 life based on a typical office environment  
 Transfer belt yield based on 3 pages per job A4 • Std Cap = Standard Capacity • High Cap = High Capacity

# Colour Printers

## C5000 Series printers

Printer model	Consumable	Order code	Unitary EAN code	Life (pages)	Gross dimensions (mm) w x d x h
C5600/C5700	Black Toner	43324408	5031713031260	6,000	302 x 113 x 72
C5600/C5700	Cyan Toner	43381907	5031713031413	2,000	302 x 113 x 72
C5600/C5700	Magenta Toner	43381906	5031713031406	2,000	302 x 113 x 72
C5600/C5700	Yellow Toner	43381905	5031713031390	2,000	02 x 113 x 72
C5600/C5700	Black Image Drum	43381708	5031713031482	20,000	372 x 149 x 231
C5600/C5700	Cyan Image Drum	43381707	5031713031475	20,000	372 x 149 x 231
C5600/C5700	Magenta Image Drum	43381706	5031713031468	20,000	372 x 149 x 231
C5600/C5700	Yellow Image Drum	43381705	5031713031451	20,000	372 x 149 x 231
C5650/C5750	Black Toner	43865708	5031713039808	8,000	302 x 113 x 72
C5650/C5750	Cyan Toner	43872307	5031713039792	2,000	302 x 113 x 72
C5650/C5750	Magenta Toner	43872306	5031713039785	2,000	302 x 113 x 72
C5650/C5750	Yellow Toner	43872305	5031713039778	2,000	302 x 113 x 72
C5650/C5750	Black Image Drum	43870008	5031713040125	20,000	372 x 149 x 231
C5650/C5750	Cyan Image Drum	43870007	5031713040118	20,000	372 x 149 x 231
C5650/C5750	Magenta Image Drum	43870006	5031713040101	20,000	372 x 149 x 231
C5650/C5750	Yellow Image Drum	43870005	5031713040095	20,000	372 x 149 x 231
C5800/C5900	Black Toner	43324424	5031713031680	6,000	302 x 113 x 72
C5800/C5900	Cyan Toner	43324423	5031713031253	5,000	302 x 113 x 72
C5800/C5900	Magenta Toner	43324422	5031713031246	5,000	302 x 113 x 72
C5800/C5900	Yellow Toner	43324421	5031713031239	5,000	302 x 113 x 72
C5800/C5900	Black Image Drum	43381724	5031713031734	20,000	72 x 149 x 231
C5800/C5900	Cyan Image Drum	43381723	5031713031727	20,000	372 x 149 x 231
C5800/C5900	Magenta Image Drum	43381722	5031713031710	20,000	372 x 149 x 231
C5800/C5900	Yellow Image Drum	43381721	5031713031703	20,000	372 x 149 x 231
C5850/C5950	Black Toner	43865724	5031713039884	8,000	302 x 113 x 72
C5850/C5950	Cyan Toner	43865723	5031713039877	6,000	302 x 113 x 72
C5850/C5950	Magenta Toner	43865722	5031713039860	6,000	302 x 113 x 72
C5850/C5950	Yellow Toner	43865721	5031713039853	6,000	302 x 113 x 72
C5850/C5950	Black Image Drum	43870024	5031713040200	20,000	372 x 149 x 231
C5850/C5950	Cyan Image Drum	43870023	5031713040194	20,000	372 x 149 x 231
C5850/C5950	Magenta Image Drum	43870022	5031713040187	20,000	372 x 149 x 231
C5850/C5950	Yellow Image Drum	43870021	5031713040170	20,000	372 x 149 x 231
C5600/C5700/C5800/C5900	Transfer Belt	43363412	5031713031543	60,000	419 x 369 x 223
C5650/C5750/C5850/C5950	Transfer Belt	43363412	5031713031543	60,000	419 x 369 x 223
C5600/C5700/C5800/C5900	Fuser Unit	43363203	5031713031536	60,000	378 x 160 x 258
C5650/C5750/C5850/C5950	Fuser Unit	43853103	5031713039761	60,000	378 x 160 x 256

NB Toner yields based on 5% coverage • Drums average A4 life based on a typical office environment • Transfer belt yield based on 3 pages per job A4



# Product compatibility

## C300 Series / C3000 MFP Series / C500 Series / MC300 Series MC500 Series image drums / image drum unit

Order codes	● 43460224	● 43460223	● 43460222	● 43460221	● 46484108	● 46484107	● 46484106	● 46484105	44494202	44968301
C301/C321										DU
C310/C330										DU
C331/C332										DU
C510/C530										DU
C511/C531										DU
C532/C542					EP	EP	EP	EP		
C3520 MFP/C3530 MFP	EP	EP	EP	EP						
MC332/MC342										DU
MC350/MC360	EP	EP	EP	EP						
MC351/MC361										DU
MC352/MC362/MC363										DU
MC561										DU
MC562										DU
MC563/MC573					EP	EP	EP	EP		

Key: EP = Image drum DU = Image drum unit

# Product compatibility

## C5000 Series / MC560 toner

Order codes	● 42127408	● 42127407	● 42127406	● 42127405	● 43324408	● 43381907	● 43381906	● 43381905	● 43865708	● 43865707	● 43865706	● 43865705	● 43324424	● 43324423	● 43324422	● 43324421	● 43865724	● 43865723	● 43865722	● 43865721	
C5100/C5300	T	T	T	T																	
C5200/C5400	T	T	T	T																	
C5600/C5700					T	T	T	T													
C5650/C5750									T	T	T	T									
C5800/C5900													T	T	T	T					
C5850/C5950																	T	T	T	T	
C5550 MFP													T	T	T	T					
MC560																	T	T	T	T	

Key: T = Toner

## C5000 Series / MC560 image drums

Order codes	● 42126608	● 42126607	● 42126606	● 42126605	● 43381708	● 43381707	● 43381706	● 43381705	● 43870008	● 43870007	● 43870006	● 43870005	● 43381724	● 43381723	● 43381722	● 43381721	● 43870024	● 43870023	● 43870022	● 43870021	
C5100/C5300	EP	EP	EP	EP																	
C5200/C5400	EP	EP	EP	EP																	
C5600/C5700					EP	EP	EP	EP													
C5650/C5750									EP	EP	EP	EP									
C5800/C5900													EP	EP	EP	EP					
C5850/C5950																	EP	EP	EP	EP	
C5550 MFP													EP	EP	EP	EP					
MC560																	EP	EP	EP	EP	

Key: EP = Image drum

## Business Printing Specialists

OKI is a global business-to-business brand dedicated to creating cost effective, professional in-house printing solutions which are designed to increase the efficiency of today's and tomorrow's businesses and their workflows. As pioneers in innovative print technologies from digital LED to High Definition Colour, we have a portfolio of award winning A3 and A4 colour and mono printers and MFPs, for workgroups and businesses of all sizes. This combined with our solutions enables businesses to achieve both image focused, vibrant, professional quality print communications and budget flexibility.

OKI's portfolio also includes precision-engineered large-format printing systems specifically designed for the sign, graphics, CAD and GIS markets that provide industry-leading productivity and image quality. In addition, our POS and dot matrix printers complete our range of printing solution.



### Considering the Environment

OKI is committed to its role as a responsible partner for all its stakeholders: Shareholders, business partners, end-users, local communities and employees.

As part of the OKI Group's Charter of Corporate Conduct, OKI continually reviews its efforts to provide environmentally sound solutions to its customers:

- OKI products are designed and manufactured with reducing the impact on the environment in mind.
- Increasing the amount of our hardware products and consumables that are recycled is one of our strategic objectives.
- We feel responsible for conducting our business in an environmentally sound manner, contributing to conservation and activities within our local communities.

OKI's Green Leaf symbol, found on all products and packaging, represents our total commitment to collection, recycling and environmental processes.



### 3 Year Warranty

Our devices are manufactured to the highest standards of quality and technology, which has been confirmed by independent tests.

We are so convinced of the high quality of our products that we are offering you an extension of the standard warranty period to 3 years – for free! Simply register your product within 30 days of purchase to be eligible for our unique all inclusive offer. Fully covered by OKI! For further information please visit your local website.



### 20 years of LED Technology

OKI pioneered the development of digital LED technology in printers over 20 years ago. This innovation delivers High Definition printing – for more accurate, striking printed documents. Thanks to this digital LED technology, our printers are compact, environmentally friendly and energy efficient, using significantly less raw materials in the manufacturing process and consuming less energy. LED print heads have no moving parts, making our LED printers robust and ultra reliable.



### High Definition Colour

High Definition Colour is OKI's own unique collection of market-defining hardware and software technologies. Together, these components deliver unsurpassed colour printing – simply, intelligently, perfectly.

We pioneered Single-pass Flat Paper Path technology to bring you fast affordable colour printing. In consumables, we created a special Microfine High Definition Toner to ensure your documents are printed in superior quality.

We championed digital LED printing technology: our High Definition LED printheads have no moving parts and deliver pin sharp images.

The combination of the range of media and software solutions we offer means you have much more control of what you want to print, when you want to print – without leaving the office.

#### OKI EUROPE LTD.

EMEA Head Office  
Blays House, Wick Road  
Egham TW20 0HJ  
United Kingdom  
T +44(0) 20 8219 2190  
F +44(0) 20 8219 2199  
[WWW.OKI.COM/EU](http://WWW.OKI.COM/EU)