

140/Narrow blisters

140

Description	Specification	Pcs	Art. No.	EAN Code	Units
140/6 mm	Galvanized	970	40109513	3221631095136	5
140/8 mm	Galvanized	970	40109514	3221631095143	5
140/10 mm	Galvanized	648	40109515	3221631095150	5
140/12 mm	Galvanized	648	40109516	3221631095167	5
140/14 mm	Galvanized	648	40109517	3221631095174	5
140/8 mm	Stainless Steel	970	5000703	4051661022005	5
140/10 mm	Stainless Steel	648	40109575	3221631095754	5
140/12 mm	Stainless Steel	648	5000690	4051661021442	5
140/14 mm	Galvanized; Divergent points	648	40109576	3221631095761	5



13/2.5M boxes

13

Description	Specification	Pcs	Art. No.	EAN Code	Units
13/4 mm	Galvanized	2500	11825725	7313469013027	10
13/6 mm	Galvanized	2500	11830725	7313469013041	10
13/8 mm	Galvanized	2500	11835625	7313469013072	10
13/10 mm	Galvanized	2500	11840625	7313469013096	10
13/14 mm	Galvanized	2500	11850525	7313469013119	10
13/6 mm	Stainless Steel	2500	11830726	7313469013058	5
13/8 mm	Stainless Steel	2500	11835626	7313469013126	5



53/5M PP

53

Description	Specification	Pcs	Art. No.	EAN Code	Units
53/6 mm	Galvanized	5000	40303083	7313463030839	5
53/8 mm	Galvanized	5000	40303084	7313463030846	5
53/10 mm	Galvanized	5000	40303085	7313463030853	5
53/12 mm	Galvanized	5000	40303086	7313463030860	5
53/14 mm	Galvanized	5000	40303087	7313463030877	5
53/16 mm	Galvanized	2400	5000202	4051661007989	5



13/5M PP

13

Description	Specification	Pcs	Art. No.	EAN Code	Units
13/6 mm	Galvanized	5000	40303079	7313463030792	5
13/8 mm	Galvanized	5000	40303080	7313463030808	5
13/10 mm	Galvanized	5000	40303081	7313463030815	5
13/14 mm	Galvanized	5000	40303082	7313463030822	5



53/5M boxes

53

Description	Specification	Pcs	Art. No.	EAN Code	Units
53/4 mm	Galvanized	5000	23808700	7313468087005	50
53/6 mm	Galvanized	5000	11856250	7313468562502	50
53/8 mm	Galvanized	5000	11857050	7313468570507	35
53/10 mm	Galvanized	5000	11858810	7313468585105	35
53/12 mm	Galvanized	5000	11859610	7313468596101	30
53/14 mm	Galvanized	5000	11860410	7313468604103	25
53/16 mm	Galvanized	5000	11860490	7313468604905	20



13/5M boxes

13

Description	Specification	Pcs	Art. No.	EAN Code	Units
13/4 mm	Galvanized	5000	11825700	7313469013010	50
13/6 mm	Galvanized	5000	11830700	7313469013034	50
13/8 mm	Galvanized	5000	11835600	7313469013065	40
13/10 mm	Galvanized	5000	11840600	7313469013089	35
13/14 mm	Galvanized	5000	11850500	7313469013102	25



53/2.5M boxes

53

Description	Specification	Pcs	Art. No.	EAN Code	Units
53/6 mm	Galvanized	2500	11856225	7313469053016	10
53/8 mm	Galvanized	2500	11857025	7313469053023	10
53/10 mm	Galvanized	2500	11858825	7313469053054	10
53/12 mm	Galvanized	2500	11859625	7313469053061	5
53/14 mm	Galvanized	2500	11860425	7313469053078	10
53/20 mm	Galvanized	1250	11894301	7313468943011	10
53/8 mm	Stainless steel	2500	23808000	7313468080006	10
53/10 mm	Stainless steel	2500	23807500	7313468075002	10



13/Narrow blister

13

Description	Specification	Pcs	Art. No.	EAN Code	Units
13/4 mm	Galvanized	1650	40109518	3221631095181	5
13/6 mm	Galvanized	1650	40109519	3221631095198	5
13/8 mm	Galvanized	1650	40109520	3221631095204	5
13/10 mm	Galvanized	1100	40109521	3221631095211	5
13/14 mm	Galvanized	1100	40109522	3221631095228	5

