molex

Molex's range of pre-crimped leads offers a simple, cost-effective solution for pre-production and prototype requirements. These leads are offered in female-to-female and male-to-male configurations in lengths of 150.00 and 300.00mm


Feature

Features and Advantages		
Pre-crimped and fully tested cables	Decrease time to market	
Available in 150 and 300mm lengths	Works well for all prototype and pre-production requirements	
Leads crimped on both ends	Allows for wire-to-wire applications and when cut in half, wire-to-board applications	
UL listed cables	Assures high-quality approved materials	
Available for most popular Molex families	Helps customers choose the right connector before investing	

in application tooling

Pre-Crimped Leads





molex

Pre-Crimped Leads

Ordering Information

Product Family	Order Number	Length	Connector A	Connector B	Wire Size	Wire/Cable Type
C-Grid	797582022	150.00mm	Female	Female	22 AWG	UL 1061
G-Grid	797582023	300.00mm	Female	Female	22 AWG	UL 1061
CLIK-Mate	797581011	300.00mm	Female	Female	24 AWG	UL 1061
	797581012	150.00mm	Female	Female	28 AWG	UL 1061
	797581013	300.00mm	Male	Male	28 AWG	UL 1061
	797581014	150.00mm	Male	Male	24 AWG	UL 1061
	797581015	300.00mm	Male	Male	24 AWG	UL 1061
DuraClik	797581008	150.00mm	Female	Female	26 AWG	UL 1061
Bardonix	797581009	300.00mm	Female	Female	26 AWG	UL 1061
	797580007	150.00mm	Female	Female	22 AWG	UL 1061
KK	797580011	300.00mm	Female	Female	22 AWG	UL 1061
I/I/	797580015	300.00mm	Male	Male	22 AWG	UL 1061
	797582024	300.00mm	Female	Female	24 AWG	UL 1007
L1NK 396	797582145	150.00mm	Female	Female	18 AWG	UL 1051
	797582146	300.00mm	Female	Female	18 AWG	UL 1051
	797582037	150.00mm	Female	Female	16 AWG	UL 1015
Mega-Fit	797582038	300.00mm	Female	Female	16 AWG	UL 1015
	797582039	150.00mm	Female	Female	12 AWG	UL 1015
	797582040	300.00mm	Female	Female	12 AWG	UL 1015
Micro-Clasp	797581001	150.00mm	Female	Female	24 AWG	UL 1007
	797581002	300.00mm 150.00mm	Female	Female	24 AWG	UL 1007
	797580002 797580004	150.00mm	Female	Female	20 AWG 20 AWG	UL 1061 UL 1061
Micro-Fit 3.0	797580004	300.00mm	Female Female	Female Female	20 AWG 20 AWG	UL 1061
	797580010	300.00mm	Female	Female	20 AWG 20 AWG	UL 1061
	797582143	150.00mm	Female	Female	26 AWG	UL 1061
	797582144	300.00mm	Female	Female	26 AWG	UL 1061
Micro-Lock Plus	797581148	150.00mm	Female	Female	26 AWG	UL 1061
	797581149	300.00mm	Female	Female	26 AWG	UL 1061
	797581095	150.00mm	Female	Female	24 AWG	UL 1061
Milli-Grid	797581096	300.00mm	Female	Female	24 AWG	UL 1061
	797580001	150.00mm	Female	Female	18 AWG	UL 1061
	797580005	150.00mm	Male	Male	18 AWG	UL 1061
Mini-Fit	797580009	300.00mm	Female	Female	18 AWG	UL 1061
	797580013	300.00mm	Male	Male	18 AWG	UL 1061
	797582147	150.00mm	Female	Female	22 AWG	UL 1061
Mini-Lock	797582148	300.00mm	Female	Female	22 AWG	UL 1061
	797582029	150.00mm	Male	Male	18 AWG	UL 1015
BAL Y	797582030	300.00mm	Male	Male	18 AWG	UL 1015
MLX	797582031	150.00mm	Female	Female	18 AWG	UL 1015
	797582032	300.00mm	Female	Female	18 AWG	UL 1015
Multicat	797582059	150.00mm	Male	Male	8 AWG	UL 1199
	797582060	300.00mm	Male	Male	9 AWG	UL 1199
	797582061	150.00mm	Male	Male	12 AWG	UL 1199
	797582062	300.00mm	Male	Male	12 AWG	UL 1199
	797582063	150.00mm	Male	Male	16 AWG	UL 1199
	797582064	300.00mm	Male	Male	16 AWG	UL 1199
	797582065	150.00mm	Female	Female	8 AWG	UL 1199
	797582066	300.00mm	Female	Female	8 AWG	UL 1199
	797582067	150.00mm	Female	Female	12 AWG	UL 1199
	797582068	300.00mm	Female	Female	12 AWG	UL 1199
	797582069	150.00mm	Female	Female	16 AWG	UL 1199
	797582070	300.00mm	Female	Female	16 AWG	UL 1199
	797582129	150.00mm	Female	Female	20 AWG	UL 1061
Nano-Fit	797582130	300.00mm	Female	Female	20 AWG	UL 1061
	797582139	150.00mm	Female	Female	20 AWG	UL 1061
PicoBlade	797582140 797581059	300.00mm	Female	Female	20 AWG	UL 1061
		150.00mm	Female	Female	28 AWG	UL 1061
	797581060	300.00mm 150.00mm	Female	Female	28 AWG	UL 1061
	797581061		Female	Female	28 AWG	UL 1061
	797581062 797581063	150.00mm	Female	Male Male	28 AWG 28 AWG	UL 1061
	797581063	300.00mm 150.00mm	Female	1	28 AWG 26 AWG	UL 1061 UL 1061
			Female	Female		1
	797580014	300.00mm	Female	Female	26 AWG	UL 1061

molex

Pre-Crimped Leads

Ordering Information

Product Family	Order Number	Length	Connector A	Connector B	Wire Size	Wire/Cable Type
Pico-Clasp	797581016	150.00mm	Female	Female	28 AWG	UL 1571
	797581017	300.00mm	Female	Female	28 AWG	UL 1571
	797581018	150.00mm	Female	Female	28 AWG	UL 1571
	797581019	300.00mm	Female	Female	28 AWG	UL 1571
Pico-EZmate	797581010	300.00mm	Female	Female	28 AWG	UL 1516
	797581003	150.00mm	Female	Female	24 AWG	UL 1061
	797581004	300.00mm	Female	Female	24 AWG	UL 1061
Pico-Lock	797581005	150.00mm	Female	Female	30 AWG	UL 1571
	797581006	300.00mm	Female	Female	30 AWG	UL 1571
	797580008	150.00mm	Female	Female	24 AWG	UL 1061
Pico-SPOX	797580016	300.00mm	Female	Female	24 AWG	UL 1061
	797581007	300.00mm	Female	Female	24 AWG	UL 1061
	797582041	150.00mm	Male	Male	16 AWG	UL 1015
	797582042	300.00mm	Male	Male	16 AWG	UL 1015
Sabre	797582043	150.00mm	Female	Female	16 AWG	UL 1015
	797582044	300.00mm	Female	Female	16 AWG	UL 1015
Sherlock	797581020	150.00mm	Female	Female	26 AWG	UL 1061
	797581021	300.00mm	Female	Female	26 AWG	UL 1061
SL	797580003	150.00mm	Female	Female	22 AWG	UL 1061
	797582025	150.00mm	Male	Male	22 AWG	UL 1015
Standard .062"	797582026	300.00mm	Male	Male	22 AWG	UL 1015
	797582027	150.00mm	Female	Female	22 AWG	UL 1015
	797582028	300.00mm	Female	Female	22 AWG	UL 1015
Standard .093"	797582033	150.00mm	Male	Male	18 AWG	UL 1015
	797582034	300.00mm	Male	Male	18 AWG	UL 1015
	797582035	150.00mm	Female	Female	18 AWG	UL 1015
	797582036	300.00mm	Female	Female	18 AWG	UL 1015
	797582131	150.00mm	Female	Female	16 AWG	UL 1061
Ultra-Fit	797582132	300.00mm	Female	Female	16 AWG	UL 1061
	797582141	150.00mm	Female	Female	16 AWG	UL 1061
	797582142	300.00mm	Female	Female	16 AWG	UL 1061

www.molex.com/link/precrimped.html

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.