

BaiSpot LED PAR | Aluminum



Bailey Nr.	Shape	Base	W	K	lm	°	ØxL (mm)
80100039963	PAR20	E27	7	3000	500	40	63x79
80100039964	PAR30	E27	13	3000	1000	40	95x95
80100039965	PAR38	E27	18	3000	1400	40	122x134



BaiSpot LED AR111



Bailey Nr.	Base	W	K	lm	°	ØxL (mm)
80100036876	GU10	12	2700	550	24	111x91
80100036877	GU10	12	2700	550	40	111x91
80100036878	GU10	12	4000	600	24	111x91
80100036879	GU10	12	4000	600	40	111x91



BaiSpot LED AR111 | High CRI



- High CRI is perfect to highlight exact colours

Bailey Nr.	Base	W	K	lm	°	ØxL (mm)
80100036872	GU10	15	2700	780	24	111x91
80100036873	GU10	15	2700	780	40	111x91
80100036874	GU10	15	4000	820	24	111x91
80100036875	GU10	15	4000	820	40	111x91

