

TOOL CABINETS, CHESTS AND MODULES SELECTION GUIDE




TOOL KITS IN ROLLER CABINETS

Tool System Solutions from RS PRO for Garages, Factories and Workshops

RS PLUS

Our revised program consists of various combinations of tools for users in different industries, presented in roller cabinets with the highest build quality. All the tools in the system are offered in double colour EVA modules, each tool has its unique 3D cutout slot for a comfortable and snug fit. This system helps inventory control by the detection of missing tools at a glance, contributing to your overall economy and efficiency. All the mechanical hand tools in the system are guaranteed against defects in material and production.





6 DRAWERS RS PLUS

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- 6 fully extendible drawers compatible with SBS inlays
- Each drawer can accommodate 3 SBS EVA tool modules
- Smart-Lock™ system on every drawer preventing accidental opening while the cabinet is on the move.
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Bottom drawer with double slides.
- Central locking mechanism.
- Holders for spray cans and paper rolls.
- Recessed worktop with a high quality mat to ensure a convenient working area.
- · Compatible with A01-PS tool panel.








6 DRAWERS WRS PLUS

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- 6 drawers compatible with SBS inlays.
- Low friction telescopic ball bearing slides ensuring silk smooth operation. Bottom drawer with double slides.
- Each drawer can accommodate 3 SBS EVA tool modules
- Smart-Lock™ system on every drawer preventing accidental opening while the cabinet is on the move.
- Central locking mechanism.
- Directly accessible tray for bulky items. The middle tray's height is adjustable.
- Recessed worktop with a high quality mat to ensure a convenient working area.
- Compatible with A01-PL tool panel.



STOCK NO	HxWxD / mm	\(\rightarrow \) kg \(\rightarrow \)
875-5789	980 × 1090 × 450	66.3




RS PLUS



7 DRAWERS RS PLUS


- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- 7 fully extendible drawers compatible with tool modules inlays
- Each drawer can accommodate 3 EVA tool modules
- Smart-Lock™ system on every drawer preventing accidental opening while the cabinet is on the move.
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Central locking mechanism.
- Heavy duty oil proof rubber wheels, two fixed and two swivelling, one with an emergency brake.
- Holders for spray cans and paper rolls.
- Recessed worktop with a high quality mat to ensure a convenient working area.





7 DRAWERS RS PLUS JUMBO

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- 7 fully extendible drawers compatible with tool modules inlays
- Each drawer can accommodate 4 EVA tool modules
- Smart-Lock™ system on every drawer preventing accidental opening while the cabinet is on the move.
- \bullet Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Central locking mechanism.
- Holders for spray cans and paper rolls.
- \bullet Recessed worktop with a high quality mat to ensure a convenient working area.



STOCK NO	HxWxD / mm	∆ kg ∆
833-5903	975 × 890 × 450	72.5




RS PLUS



4 DRAWERS CHEST JUMBO


- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- 4 drawers compatible with tool modules inlays.
- Each drawer can accommodate 4 EVA tool modules.
- 80 mm deep top locker with integrated locking mechanism
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Integrated carrying handles.



STOCK NO	HxWxD / mm	∆ kg ∆
833-5907	476 × 794 × 440	20

11 DRAWERS CABINET

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- $\bullet\,$ 11 fully extendible drawers 5 of which are compatible with tool modules in lays.
- Each drawer on the left can accommodate 3 EVA tool modules.
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
 Bottom drawer with double slides.
- Foamed rubber mats in drawer bases.
- Central locking mechanism. No possibility of key match.
- Smart-Lock™ system on every drawer preventing accidental opening while the cabinet is on the move.
- Recessed worktop with a high quality mat to ensure a convenient working area.








TOOL PANELS (FOR ROLLER CABINETS)

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- A01-PS is designed to fit roller cabinets A01-06 and A01-07.
- A01-PL is designed to fit roller cabinets A01-11 and A01-06W.
- Compatible with A17-H hooks.
- Includes bolts and washers required to fix the panel to the cabinet.



STOCK NO	HxW / mm	∆ kg △
875-5777	630 × 600	5.6
875-5786	1100 × 600	8.6




HOOK FOR TOOL PANELS

For use with A01-PS, A01-PL, A20-100, A20-170 tool panels and A17(S)P work benches with tool panels











CHEST JUMBO FOR A01-11 - 8 DRAWERS

- Sturdy and durable construction, premium quality sheet steel
- Fits onto A01-11 jumbo roller cabinet
- 8 drawers compatible with SBS inlays
- ullet 80 mm deep top locker with integrated locking mechanism
- Low friction telescopic ball bearing slides ensuring silk smooth operation
- Integrated carrying handles







8 drawers

STOCK NO	HxWxD / mm	∆ kg ∆
125-3044	476 × 798 × 442	30





- Heavy Duty Tool Cabinets
- Standard Duty Tool Cabi-

nets

- Maintenance Cart
- Mobile Tool Cupboard
- Service Cart



Recessed worktop












3 DRAWERS HEAVY DUTY TOOL CABINET

- Sturdy and dependable construction, premium quality sheet steel. Elegant and durable electrostatic matt powder coated, scratch proof.
- 3 fully extendible drawers
- Each drawer can accommodate 3 EVA tool modules.
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Central locking mechanism.
- 100 diameter, 2 locking swivel castors and 2 fixed castors

Heavy Duty



STOCK NO	HxWxD / mm	∆ kg ∆
752-1572	830 v 630 v h20	3030




5 DRAWERS HEAVY DUTY TOOL CABINET

- Sturdy and dependable construction, premium quality sheet steel. Elegant and durable electrostatic matt powder coated, scratch proof.
- 5 fully extendible drawers
- Each drawer can accommodate 3 EVA tool modules.
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Central locking mechanism.
- 100 diameter, 2 locking swivel castors and 2 fixed castors

Heavy Duty











6 DRAWERS HEAVY DUTY TOOL CABINET

- Sturdy and dependable construction, premium quality sheet steel.
 Elegant and durable electrostatic matt powder coated, scratch proof.
- 6 fully extendible drawers
- Each drawer can accommodate 3 EVA tool modules.
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Central locking mechanism.
- 100 diameter, 2 locking swivel castors and 2 fixed castors






STOCK NO	HxWxD / mm	∆ kg △
753-1570	830 × 630 × 450	47.70

7 DRAWERS HEAVY DUTY TOOL CABINET

- Sturdy and dependable construction, premium quality sheet steel.
 Elegant and durable electrostatic matt powder coated, scratch proof.
- 7 fully extendible drawers
- Each drawer can accommodate 3 EVA tool modules.
- \bullet Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Central locking mechanism.
- 100 diameter, 2 locking swivel castors and 2 fixed castors

Heavy Duty









12 DRAWERS MAINTENANCE CART

• Sturdy and dependable construction, premium quality sheet steel. Elegant and durable electrostatic matt powder coated, scratch proof.

• 12 fully extendible drawers

• Each drawer on the left can accommodate 3 EVA tool modules.

• Low friction telescopic ball bearing slides ensuring silk smooth operation.

• Central locking mechanism.

• 125 diameter, 2 locking swivel castors and 2 fixed castors


Heavy Duty



STOCK NO	HxWxD / mm	∆ kg ∆
753-1582	870×1085×450	87.75

SERVICE CART

- Sturdy and dependable construction, premium quality sheet steel. Elegant and durable electrostatic matt powder coated, scratch proof.
- Base, middle and bottom shelfs with edges to contain tools.
- 125 diameter, 2 locking swivel castors and 2 fixed castors



STOCK NO	HxWxD / mm	∆ kg ∆
7531-592	970 × 760 × 450	31.60




5 DRAWERS STANDARD DUTY TOOL CABINET

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- 5 fully extendible drawers
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Padlock locking mechanism.
- 75 diameter, 2 locking swivel castors and 2 fixed castors



Standard Duty






STOCK NO	HxWxD / mm	∆ kg △
753-1586	650 × 560 × 350	28.65

6 DRAWERS STANDARD DUTY TOOL CABINET

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- 6 fully extendible drawers
- \bullet Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Padlock locking mechanism.
- 75 diameter, 2 locking swivel castors and 2 fixed castors

Standard Duty




STOCK NO	HxWxD / mm	∆ _{kg} ∆
753-1595	750 × 560 × 350	33.45





MOBILE TOOL CUPBOARD

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- · Locking mechanism.
- 75 diameter, 2 locking swivel castors and 2 fixed castors








3 DRAWERS TOOL CHEST

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- Easily fits onto RS PLUS and RS series roller cabinets. Especially recommended to increase the stocking capacity of these roller cabinets.
- 3 drawers compatible with tool modules inlays.
- Each drawer can accommodate 3 EVA tool modules.
- 80 mm deep top locker with integrated locking mechanism
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Integrated carrying handles.



STOCK NO	HxWxD / mm	∆ kg ∆
768-1678	360 × 620 × 440	20







8 DRAWERS STEEL TOOL CHEST

- Top locker area for storage of larger tools
- Strong hinges to hold lid in open position
- Locking mechanism with key
- Carrying handles



Standard Duty 8 drawers

STOCK NO HxWxD / mm 773-2735 427 × 660 × 307



2 DRAWERS MOBILE TOOL TROLLEY

- Lockable
- Lined shelves
- Two lockable drawers with ball bearing slides and liners
- Four large castors with two locking
- Some self-assembly required





STOCK NO HxWxD / mm 851-7581 985 × 815 × 410





WALL MOUNT TOOL CABINET WITH DRAWERS

- Lockable doors
- Hook tool storage
- Fully extendable drawer
- Sturdy steel construction
- Two piano hinged lockable doors
- Assorted hooks
- Made from heavy gauge steel





Heavy Duty

2 drawers

STOCK NO HxWxD / mm 851-7610 890 × 750 × 225



Heavy Duty


1 drawers

 STOCK NO
 HxWxD / mm

 851-7616
 900 × 615 × 195

6 DRAWERS TOOL CHEST

- Sturdy and dependable construction, premium quality sheet steel.
- Elegant and durable electrostatic matt powder coated, scratch proof.
- 3 small drawers on the top row.
- 80 mm deep top locker.
- Low friction telescopic ball bearing slides ensuring silk smooth operation.
- Integrated carrying handles.







IP67 TOOL CASES

RS PRO has introduced a new tool case programme for professionals working in challenging conditions. Look after your tools with new tool case—a highly versatile case for technicians, engineers and maintenance operatives.

- Waterproof design
- Customizable tool fixing system
- Impact resistant material
- Stackability
- Soft grip handle
- Available as Standard and Mobility version













STOCK NO	HxWxD / mm	∆ kg ∆
125-3050	530 × 400 × 230	6.0



19" PLASTIC TOOL BOX (EMPTY)

- Compact dimensions with highest possible storage capacity.
- Two organizers on top with lids.
- Telescoping design carry handle.
- Removable tote tray.
- Sturdy plastic latches.
- Padlock clasp (padlock not supplied)
- Industrial quality tools




43PC TOOL KIT

- The perfect tool kit for professional mechanics in the industry and trade
- Industrial quality tools

833-5975



6.9



PRO

TOOL MODULES SIZE: 370 mm x 175 mm x 35 mm

16PC COMBINATION WRENCH SET



CTOOK NO	DIE	SEC.

STOCK NO	PIECES
833-5922	16

18PC 3/8" DRIVE SOCKET SET



C11-12 3/8" Drive Quick Release Reversible Ratchet
C11-70 3/8" Drive Extension Bars (75, 150 mm)
C11-40 3/8" Drive Sliding T-Handle (200 mm)

C11-80 3/8" Drive Universal Joint

C12-H (6, 7, 8, 9, 10, 11, 12, 13, 14, 15, 17, 19, 22 mm) 3/8" Drive 6-Point Sockets

STOCK NO	PIECES
125-3053	18

39PC SLOTTED/PZ SCREWDRIVER AND BIT SET



F10 (3.0×75, 4.0×100, 5.5×125, 6.5×150 mm) Slotted Screwdrivers

F17 (PZ1×80, PZ2×100 mm) Pozidriv Screwdrivers

F26/BT 1/4"x100 mm Bit Driver

CR/ST31 31 Piece Bit Set

6106 Voltage Tester (VDE Approved-Long)

STOCK NO	PIECES
833-5947	39

12PC RATCHETING COMBINATION WRENCH SET



B05 (8, 10, 11, 12, 13, 14, 17,19 mm) C-GEAR Ratcheting Combination Wrenches (Straight)

B05-14S (1/4"- 10 mm), **B05-38S** (3/8"- 13 mm), **B05-12S** (1/2"- 19 mm) C-GEAR Socket Adaptors,

B05-14B (1/4"- 10 mm) C-GEAR Bit Adaptor

STOCK NO	PIECES
833-5925	12

23PC 1/2" DRIVE SOCKET SET WITH RATCHET



C21-12 1/2" Drive Quick Release Reversible Ratchet C21-70 1/2" Drive Extension Bars (125, 250 mm)

C21-80 1/2" Drive Universal Joint

C21-40 1/2" Drive Sliding T-Handle (250 mm)

C22-H (8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 24, 27, 30, 32mm) 1/2" Drive 6-Point Sockets

STOCK NO	PIECES
833-5950	23

18PC 1/2" DRIVE IMPACT SOCKET SET



C61-74 1/2" Drive Impact Extension Bar (125 mm)
C61-92 1/2" Drive Impact Socket Adaptor - F3/8" M1/2"
C62-H (10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 24, 27, 30, 32 mm) 1/2" Drive 6-Point Impact Sockets

STOCK NO	PIECES
125-3055	18

12PC C-GEAR RATCHETING COMBINATION WRENCH SET (FLEX HEAD)




B06 (8, 10, 11, 12, 13, 14, 17,19 mm)
C-GEAR Ratcheting Combination Wrenches (Flex Head)
B05-14S (1/4"- 10 mm), B05-38S (3/8"- 13 mm),

B05-12S (1/2"- 19 mm) C-GEAR Socket Adaptors,

B05-14B (1/4"- 10 mm) C-GEAR Bit Adaptor

STOCK NO	PIECES
125-3051	12

17PC 1/2" DRIVE DEEP SOCKET SET



C24-H (8, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19, 21, 22, 24, 27, 30, 32mm) 1/2" Drive 6-Point Deep Sockets

STOCK NO	PIECES
125-3054	17

10PC 1/2" DRIVE IMPACT DEEP SOCKET SET




C64-H (10, 11, 12, 13, 14, 17, 19, 21, 22, 24 mm) 1/2" Drive 6-Point Impact Deep Sockets

STOCK NO	PIECES
125-3056	10



29PC 1/2" TORX/HEX/XZN SOCKET BITS SET



C28S-T (T20, T25, T30, T40, T45, T50, T55, T60) x 30 mm 1/2" Drive TORX Socket Bits (Replaceable Bit) - Short

C28S-TL (T30, T40, T45, T50) x 75 mm 1/2" Drive TORX Socket Bits (Replaceable Bit) - Long

C28S-H (5, 6, 7, 8, 10, 12, 14 mm) x 30 mm 1/2" Drive Hexagon Socket Bits (Replaceable Bit) - Short

C28S-HL (6, 8, 10, 12 mm) x 75 mm 1/2" Drive Hexagon Socket Bits (Replaceable Bit) - Long

C28S-X (M05, M06, M08, M10, M12) x 30 mm
1/2" Drive XZN Socket Bits (Replaceable Bit) - Short
L (2.5 mm) Hexagon L Key (Short Arm)

STOCK NO	PIECES
833-5957	29

15PC T-HANDLE & BALLPOINT L HEX KEY SET



K10 (2.0, 2.5, 3.0, 4.0, 5.0, 6.0 mm) T-Handle Hexagon Keys **LT/900** (1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 mm) Ball End Hexagon L Key Set

STOCK NO	PIECES
833-5913	15


14 PIECE T-HANDLE AND L TORX KEY SET



K12 (T10, T15, T20, T25, T30, T40) T-Handle TORX Keys LT/700L (T9, T10, T15, T20, T25, T27, T30, T40) TORX L Key Set (Long Arm)

STOCK NO	PIECES
125-3052	14

7 PIECE SLOTTED/PH SCREWDRIVER SET




F10 (3.0×75, 4.0×100, 5.5×125, 6.5× 150, 8.0×150 mm)

F14 (PH1×80, PH2×100 mm) Phillips Screwdrivers

STOCK NO	PIECES
125-3057	7


7 PIECE TORX SCREWDRIVER SET



F18 (T10×80, T15×80, T20×100, T25×100, T27×115, T30×115, T40×130 mm) TORX Screwdrivers

STOCK NO	PIECES	
125-3060	7	

7 PIECE TORX TAMPER RESISTANT SCREWDRIVER SET



F19 (T10×80, T15×80, T20×100, T25×100, T27×115,T30×115, T40×130 mm) TORX Tamper Resistant Screwdrivers

STOCK NO	PIECES
125-3061	7

5 PIECE NUT DRIVER SET



F20 (6, 7, 8, 10, 13 mm) Nut Drivers

STOCK NO	PIECES
125-3062	5

39 PIECE SLOTTED/PH SCREWDRIVER AND BIT SET



F10 (3.0×75, 4.0×100, 5.5×125, 6.5×150 mm)

F14 (PH1×80, PH2×100 mm) Phillips Screwdrivers

F26/BT 1/4"x100 mm Bit Driver CB/ST31 31 Piece Bit Set

6106 Voltage Tester (VDE Approved-Long)

STOCK NO	PIECES	
125-3059	39	

52PC 1/4" DRIVE SOCKET AND HEX KEY SET



C01-12 1/4" Drive Quick Release Reversible Ratchet

C01-20 1/4" Drive Spinner Handle

C01-80 1/4" Drive Universal Joint

C01-40 1/4" Drive Sliding T-Handle (115 mm)

C01-70 1/4"" Drive Extension Bar (50, 150 mm)

C02-H (4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm) 1/4" 6-Point Socket

C04-H (4, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm) 1/4" 6-Point Deep Socket

C08-T (T10, T15, T20, T25, T30, T40) 1/4" Drive TORX Socket Bits

C08-H (3.0, 4.0, 5.0, 6.0, 8.0) 1/4" Drive Hexagon Socket Bits **C08-S** (5.5 mm) 1/4" Drive Slotted Socket Bits


C08-PH (PH2) 1/4" Drive Phillips Socket Bits

C08-PZ (PZ2) 1/4" Drive Pozidriv Socket Bits

LT/9 (1.5, 2, 2.5, 3, 4, 5, 6, 8, 10 mm) 9 Piece Hexagon L Key Set (Short Arm-Matt Chrome)

STOCK NO	PIECES
833-5935	52

7 PIECE SLOTTED/PZ SCREWDRIVER SET




F10 (3.0×75, 4.0×100, 5.5×125, 6.5× 150, 8.0×150 mm) Slotted Screwdrivers

F17 (PZ1×80, PZ2×100 mm) Pozidriv Screwdrivers

STOCK NO	PIECES	
125-3058	7	

TOOL CABINETS, CHESTS AND MODULES

7PC INSULATED SLOTTED/PH SCREWDRIVER SET



♠ 1000 V EN 60900

G01 (3.0×100, 4.0×100, 5.5×125, 6.5×150 mm) VDE 1000V Insulated Slotted Screwdrivers

G02 (PH1×80, PH2×100 mm)

VDE 1000V Insulated Phillips Screwdrivers

6106 Voltage Tester (VDE Approved-Long)

STOCK NO	PIECES
833-5941	7

3PC VDE INSULATED PLIERS SET




G10-18-0180 180 mm VDE 1000V Insulated Combination

G12-18-0160 160 mm VDE 1000V Insulated Diagonal Cutter G15-18-0160 160 mm VDE 1000V Insulated Long Nose Pliers

STOCK NO	PIECES
833-5931	3

10PC PRECISION PLIER AND **SCREWDRIVER SET**



H30S-110SB Electronics Diagonal Cutter (Oval Head-

H33S-120 Electronics Short Needle Nose Pliers (Toothed Gripping Surface)

H35S-140 Electronics Long Needle Nose Pliers


H01 (1.5 × 60, 2.0 × 60, 2.5 × 80, 3.0 × 80 mm) Electronics Slotted Screwdrivers

H02 (PH00 × 60, PH0 × 60 mm) Electronics Phillips

H41-06-0115 Tweezer (Stainless Steel)

STOCK NO	PIECES	
8335010	10	

7 PIECE INSULATED SLOTTED/ PZ SCREWDRIVER SET (VDE APPROVED)



↑ 1000 V EN 60900

G01 (3.0×100, 4.0×100, 5.5×125, 6.5×150 mm) VDE 1000V Insulated Slotted Screwdrivers

G03 (PZ1×80, PZ2×100 mm)

VDE 1000V Insulated Phillips Screwdrivers

6106 Voltage Tester (VDE Approved-Long)

STOCK NO	PIECES	
125-3063	7	

3 PIECE PLIERS AND ADJUSTABLE WRENCH SET



E30-54-0250 250 mm Water Pump Pliers (Box Joint/PVC Sleeves)

E50-240-2 240 mm Grip Pliers (Curved Jaws)

B21-250B 250 mm Adjustable Wrench (Phosphated-PVC Grip)

125-3064

Spring)

STOCK NO

PIECES 3

6PC MEASURING AND CUTTING TOOL SET



G40-48 (145 mm) Multi-Purpose Electrician's Shears

J06-250 (250 mm) English Pattern Snip

J45-07 Utility Knife (18 mm-Metal Body)


P05-0519 (5 m x 19 mm) Compact Tape Measure

P15-030 (30 cm) Stainless Steel Rule

P54-20S Feeler Gauge (20 Leaves - Metric)

STOCK NO **PIECES** 8335944 6

3PC SOFTGRIP PLIERS SET



E01-41-0180 180 mm Combination Pliers (Polished Finish/

E06-41-0160 160 mm Diagonal Cutter (Polished Finish/ DuoTech Handles)

E15-41-0160 160 mm Long Nose Pliers (Polished Finish/ DuoTech Handles

STOCK NO	PIECES
833-5972	3

4PC CIRCLIP PLIERS SET



E65-44-0180 180 mm External Circlip Pliers (Straight-with Sprinal

E66-44-0180 180 mm External Circlip Pliers (Bent-with Spiring)

E67-44-0180 180 mm Internal Circlip Pliers (Straight-without E68-44-0180 180 mm Internal Circlip Pliers (Bent-without

STOCK NO	PIECES
833-5929	4

11PC STANDARD AND NEEDLE **FILE SET**



J55-108H Hand File - Bastard, 200 mm

J56-108H Half Round File - Bastard, 200 mm J57-108H Round File - Bastard, 200 mm

J58-108H Sauare File - Bastard, 200 mm


J59-108H Three Square File - Bastard, 200 mm

J75-R06 Needle File Set:

Flat File (7.3×1.8×160 mm), Hand File (7.3×1.8×160 mm). Three Square File (3.4×160 mm), Round File (\emptyset 4.0×160 mm), Square File (5.0×160 mm), Half Round File (7.3×2.6×160 mm)

STOCK NO	PIECES	
8335953	11	





STOCK NO PIECES 833-5963

2PC CRIMPER AND STRIPPER SET



STOCK NO PIECES
833-5966 2

5PC HAND RIVERTER SET



STOCK NO PIECES 833-5969 5







KITS BY SECTORS


Mechanic



Maintenance



Electrician



General Purpose





RS PRO 240 PIECES TOOL TROLLEY TOOL KIT



•	STOCK NO	HxWxD / mm	∆ kg ∆
	125-3046	975 × 710 × 450	60.2


CONTENT		PIECES
8335966	2pc Climper and Stripper Set	2
8335969	5pc Hand Riverter Set	5
3 8335925	12pc Ratcheting Combination Wrench Set	12
8335944	6pc Measuring and Cutting Tool Set	6
5 8335931	3pc VDE Insulated Pliers Set	3
6 8335929	4pc Circlip Pliers Set	4
7 8335922	16pc Combination Wrench Set	16
8335935	52pc 1/4" Drive Socket and Hex Key Set	52
9 8335950	23pc 1/2" Drive Socket Set with Ratchet	23
10 8335957	29pc 1/2" TORX/Hex/XZN Socket Bits Set	29
11 8335941	7pc Insulated Slotted/PH Screwdriver Set	7
12 8335953	11pc Standard and Needle File Set	11
13 8335947	39pc Slotted/PZ Screwdriver and Bit Set	39
14 8335972	3pc Softgrip Pliers Set	3
15 8335938	3pc Pliers and Adjustable Wrench Set	3
13 8335919	10pc Precision Plier and Screwdriver Set	10
14 8335913	15pc T-Handle & Ballpoint L Hex Key Set	15
15 8335963	5 Division EVA Module	-














RS PRO 213 PIECES TOOL TROLLEY TOOL KİT




	CONTENT		PIECES
1	8335922	16 Piece Combination Wrench Set	16
2	8335935	52pc 1/4" Drive Socket and Hex Key Set	52
3	8335950	23pc 1/2" Drive Socket Set with Ratchet	23
4	8335957	29pc 1/2" TORX/Hex/XZN Socket Bits Set	29
5	8335941	7pc Insulated Slotted/PH Screwdriver Set	7
6	8335953	11pc Standard and Needle File Set	11
7	8335947	39pc Slotted/PZ Screwdriver and Bit Set	39
8	8335972	3pc Softgrip Pliers Set	3
9	8335938	2pc Pliers and Adjustable Wrench Set	2
10	8335919	10pc Precision Plier and Screwdriver Set	10
11	8335913	15pc T-Handle & Ballpoint L Hex Key Set	15
12	8335944	6pc Measuring and Cutting Tool Set	6

STOCK NO	HxWxD / mm	
125-3047	975 × 710 × 450	











RS PRO 160 PIECES TOOL TROLLEY TOOL KIT

HEAVY DUTY *Roller Cabinet*







	CONTENT		PIECES
1	8335922	16pc Combination Wrench Set	16
2	8335935	52pc 1/4" Drive Socket and Hex Key Set	52
3	8335950	23pc 1/2" Drive Socket Set with Ratchet	23
4	8335947	39pc Slotted/PZ Screwdriver and Bit Set	39
5	8335972	3pc Softgrip Pliers Set	3
6	8335938	2pc Pliers and Adjustable Wrench Set	2
7	8335919	10pc Precision Plier and Screwdriver Set	10
8	8335913	15pc T-Handle & Ballpoint L Hex Key Set	15
9	8335963	5 Division EVA Module	Empty


STOCK NO HxWxD / mm 125-3048 825 × 630 × 450











RS PRO products are audited against demanding international standards, inspected for durability and consistency and tested by leading engineers.

Only when products have been through this process are they awarded our seal of approval, quality that can be trusted. Confidence in this process is reflected in our long product warranties, proof that our products will consistently deliver the quality you expect for a long time to come.



