

International earthing contact plug

Art. no.	Version	Unit
Earthing contact plug, Switzerland CH, 10A/250V~		CH
Cables up to 3G 1.00 mm ²		
<ul style="list-style-type: none"> · Thermoplastic version · With strain relief 		
910.175	· Black, T12 plug	1 item
910.275	· White, T12 plug	1 item
Earthing contact plug, UK, 13A/250V~		UK
Cables up to 3G 1.50 mm ²		
<ul style="list-style-type: none"> · Plastic version · Integral 13A miniature fuse · With strain relief 		
910.176	· Black	1 item
910.276	· White	1 item
Earthing contact plug, USA, 15A/125V~		USA
3-pole		
<ul style="list-style-type: none"> · Non-polarised · Thermoplastic version 		
910.179	· Black, Nema 5-15P	20 items
USA plug		USA
2-pole		
<ul style="list-style-type: none"> · Not polarised, Duroplast 		
910.178	· Black	100 items
Earthing contact plug, Italy, 10A/250V~		Italy
3-pole		
<ul style="list-style-type: none"> · Thermoplastic version 		
910.174	· Black	50 items
Earthing contact plug, Australia, 10A/250V~		Australia
3-pole		
<ul style="list-style-type: none"> · With insulated pins and sleeve 		
910.182	· Black	40 items
910.282	· White	40 items

International earthing contact couplings

Art. no.	Version	Unit
Earthing contact coupling, Switzerland CH, 10A/250V~		CH
<ul style="list-style-type: none"> · Thermoplastic version 		
912.174*	· Black	50 items
912.274	· White	50 items
Earthing contact coupling, UK, 13A/250V~UK		
With function display		
<ul style="list-style-type: none"> · Thermoplastic version 		
910.177*	· Black	10 items
910.277*	· White	10 items
Earthing contact coupling with earthing pin, Belgium/France 15A/125V~		Earthing contact /UTE
With kink protection sleeve		
<ul style="list-style-type: none"> · Thermoplastic version 		
912.173	· Black	35 items
912.273	· White	35 items