



QuickScan™ I QM2100 General Purpose Handheld Linear Imager Bar Code Reader with Datalogic's STAR Cordless System™

QuickScan I QM2100 readers are available in Black or White. Radio communications are offered in 433 or 910 MHz radio frequencies (check with your local Datalogic Representative for frequencies allowed in your country). Multi-interface kits are available that include reader and base stations and may include cables. Power supplies/cords must be ordered separately except where noted. Base stations, cables and other accessories can also be ordered separately.

Standard factory warranty is three years. Cables have a 90-day warranty.

Please note that items in this catalog may not be available in all regions of the world. To verify availability of any particular item listed, please check with your local Datalogic Scanning Representative or sales office.



QuickScan I QM2100 Models and Kits

QuickScan Mobile QM2130, 433 MHz, Kit, Linear Imager, Black (Kit inc. Imager and Base Station/Charger. Cables and power supply must be ordered separately)	QM2130-BK-433
QuickScan Mobile QM2130, 433 MHz, Kit, Linear Imager, White (Kit inc. Imager and Base Station/Charger. Cables and power supply must be ordered separately)	QM2130-WH-433
QuickScan Mobile QM2130, 433 MHz, Kit, Linear Imager, White (Kit inc. Imager, Base Station/Charger and Magellan Bi-Optic AUX Port Cable 90G001092)	QM2130-WH-433LPK2
QuickScan Mobile QM2130, 433 MHz, Kit, USB, Linear Imager, Black (Kit - Imager and Base Station and USB Cable 90A051945.)	QM2130-BK-433K1
QuickScan Mobile QM2130, 433 MHz, Kit, USB, Linear Imager, White (Kit- Imager and Base Station and USB Cable 90A051945.)	QM2130-WH-433K1
QuickScan Mobile QM2130, 910 MHz, Kit, Linear Imager, Black (Kit inc. Imager and Base Station/Charger. Cables and power supply must be ordered separately)	QM2130-BK-910
QuickScan Mobile QM2130, 910 MHz, Kit, Linear Imager, White (Kit inc. Imager and Base Station/Charger. Cables and power supply must be ordered separately)	QM2130-WH-910
QuickScan Mobile QM2130, 910 MHz, Kit, Linear Imager, White (Kit inc. Imager, Base Station/Charger and Magellan Bi-Optic AUX Port Cable 90G001092)	QM2130-WH-910LPK2
QuickScan Mobile QM2130, 910 MHz, Kit, USB, Linear Imager, Black (Kit inc. Imager and Base Station and USB Cable 90A051945.)	QM2130-BK-910K1
QuickScan Mobile QM2130, 910 MHz, Kit, USB, Linear Imager, White (Kit inc. Imager and Base Station and USB Cable 90A051945.)	QM2130-WH-910K1



Base Stations

QuickScan Mobile QM2100, 433 MHz, Base Station, RS-232, Wedge, USB and Wand Emulation, Black	90A401005
QuickScan Mobile QM2100, 433 MHz, Base Station, RS-232, Wedge, USB and Wand Emulation, White	90A401004
QuickScan Mobile QM2100, 910 MHz, Base Station, RS-232, Wedge, USB and Wand Emulation, Black	90A401007
QuickScan Mobile QM2100, 910 MHz, Base Station, RS-232, Wedge, USB and Wand Emulation, White	90A401006

EASEOFCARE AGREEMENTS

Contract, Quick Replacement, 3 Years, QuickScan QM2100	Q-QM21-3
Contract, Quick Replacement, 5 Years, QuickScan QM2100	Q-QM21-5
Contract, Service Plus 2-day, 3 Years, QuickScan QM2100	W-QM21-3
Contract, Service Plus 2-day, 5 Years, QuickScan QM2100	W-QM21-5
Contract, Service Plus 5-day, 3 Years, QuickScan QM2100	E-QM21-3
Contract, Service Plus 5-day, 5 Years, QuickScan QM2100	E-QM21-5

BATTERIES/BATTERY CHARGERS




Battery Pack, QuickScan Mobile QM2100

90ACC1945

CABLES

Cable, IBM AT/XT, KBW, Din Connector, Straight, CAB-322, 7 ft.	90G001020
Cable, IBM PS/2, KBW, Minidin Connector, Coiled, CAB-365, 6 ft.	90A051360
Cable, IBM PS/2, KBW, Minidin Connector, External Power Supply, Coiled, CAB-391, 11 ft.	90A051740
Cable, IBM VDT. 3151, 34XX, KBW, 8-pin Telephone Connector, Straight, CAB-325, 11 ft.	90G001050
Cable, KBW, 4P, Telephone Connector, DEC VDT VT200/220/240/300/320/340/420, CAB-375, 6 ft.	90A051490
Cable, RS-232 to C-Box Adapter, Coiled, CAB-409 (Requires 90A051500 Sold Separately When Used with Diamond), 20 ft.	90A051895

Cable, RS-232, 25P, Female, Coiled, CAB-363 (Power available on pin 9 of the connector or through external power supply), 6 ft.	90A051340	
Cable, RS-232, 25P, Female, Straight, CAB-328 (Power Supply available on pin 9 of the connector or with external power supply), 2 Meters	90G001080	
Cable, RS-232, 25P, Male, Coiled, CAB-364 (Power Supply available on pin 9 of the connector or through external power supply), 6.5 ft.	90A051350	
Cable, RS-232, 25P, Male, Straight, CAB-320 (Power available on pin 25 of the connector or through power supply), 6 ft.	90G001000	
Cable, RS-232, 9P, Female, Coiled, CAB-362, External Power, 6 ft.	90A051330	
Cable, RS-232, 9P, Female, Coiled, CAB-408 (Power available on pin 9 of the connector or through external power supply), 6 ft.	90A051891	
Cable, RS-232, 9P, Female, Straight, CAB-327, Requires External Power, 6 ft.	90G001070	
Cable, RS-232, 9P, Female, Straight, CAB-350 (Power Supply available on pin 9 of the connector or through external power supply), 6 ft.	90A051230	
Cable, RS-232, 9P, Male, Beetle POS, Straight, CAB-389, External Power, 6.5 ft.	90A051710	
Cable, RS-232, 6' (For Magellan)	90G001092	
Cable, RS-232/Beetle, 9P, Male, Coiled, CAB-388	90A051700	
Cable, USB, IBM PowerPlus Mode, Straight CAB-413, 6 ft.	90A051903	
Cable, USB, Type A, Optional POT or through external power supply, Coiled, CAB-412, 9 ft.	90A051922	
Cable, USB, Type A, Optional Power USB Keyboard, USB COM Mode, Straight, CAB-412, 6 ft.	90A051902	
Cable, USB, Type A, Straight, CAB-426, 6 ft.	90A051945	
Cable, Wand Emulation, 9P, Male, Coiled, CAB-348, 3.2 ft.	90A051210	
Cable, Wand Emulation, 9P, Male, Straight, CAB-323, 6 ft.	90G001030	
Cable, WYSE VDT 60/120/160/185/370, KBW, 4P, Telephone Connector, Straight, CAB-373, 6 ft.	90A051470	
MISCELLANEOUS		
	Manual, Hand-Held Devices II, Software Configuration	90ACC1877
POWER SUPPLIES/CORDS		
Power Cord, 2-Pin, AUS	90ACC1884	
Power Cord, 2-Pin, EU	90ACC1885	
Power Cord, 2-Pin, UK	90ACC1887	
Power Cord, 2-Pin, US	90ACC1886	

Power Supply, 5VDC, PG5-05P55 (without power cord)	90ACC1882
Power Supply, 5VDC, US, PG5-05P55-US (includes power cord)	90ACC1893