

# 3. POLYETHYLENE BAGS

## TRIBOCHARGING

### 3.1. Pink Poly Bag

IEC  
61340  
Compliant  
RoHS, REACH  
Directive



Heat-sealable bags made from pink low tribocharging and dissipative LDPE (Low Density PolyEthylene).



- Avoids static electricity creation in protected environments
- 3 thicknesses available, with or without zip

#### Technical Data

- Surface resistance:  $R_{pp} < 1 \times 10^{11} \Omega$
- Characteristics : Low Density dissipative PolyEthylene (LDPE) amine free

#### Dimensions available - Thickness $\mu\text{m}$ (+/- 10%)

Dim. mm	Dim. inches	Thickness 50		Thickness 75		Thickness 90	
		Without zip	With zip	Without zip	With zip	Without zip	With zip
76 x 80	3 x 3,2	-	20-010-0006	-	20-112-0001	-	20-014-0002
76 x 100	3 x 4	-	-	20-111-0304	20-112-0002	20-013-0003	20-014-0006
76 x 127	3 x 5	20-007-0305	20-008-0305	20-111-0305	20-112-0305	20-011-0305	20-012-0305
102 x 152	4 x 6	20-007-0406	20-008-0406	20-111-0406	20-112-0406	20-011-0406	20-012-0406
127 x 203	5 x 8	20-007-0508	-	20-111-0508	20-112-0508	20-011-0508	20-012-0508
152 x 203	6 x 8	20-007-0608	-	20-111-0608	-	20-011-0608	-
152 x 254	6 x 10	20-007-0610	20-008-0610	20-111-0610	20-112-0610	20-011-0610	20-012-0610
203 x 254	8 x 10	20-007-0810	-	20-111-0810	20-112-0810	20-011-0810	20-012-0810
203 x 305	8 x 12	20-007-0812	20-008-0812	20-111-0812	20-112-0812	20-011-0812	20-012-0812
203 x 406	8 x 16	20-007-0816	-	-	-	-	-
254 x 305	10 x 12	20-007-1012	20-008-1012	20-111-1012	20-112-1012	20-011-1012	20-012-1012
254 x 356	10 x 14	-	20-010-0007	-	-	-	-
305 x 356	12 x 14	-	-	20-111-1214	-	20-011-1214	-
305 x 406	12 x 16	20-007-1216	20-008-1216	20-111-1216	20-112-1216	20-011-1216	20-012-1216
406 x 508	16 x 20	20-007-1620	-	20-111-1620	-	20-011-1620	-
457 x 610	18 x 24	-	-	20-111-1824	--	20-011-1824	-