

Test leads SML 4W 4 mm safety plug-in technology

Accessory information

- Safety test lead, flexible 0.8 mm²
- Current-carrying capacity 16 A
- Measurement category CAT III / 600 V

Design

- PVC insulation
- Two-way safety plugs with onward connection capability in accordance with DIN VDE 0411/ EN 61010/IEC 61010

307111 (red - 1000mm)

Article no. 2146495

307112 (black - 1000mm)

Article no. 3313550

307121 (red - 2000mm)

Article no. 2146508

307122 (black - 2000mm)

Article no. 3313561





Safety clamp-type test probe

Accessory information

• Current-carrying capacity 2 A

• Measurement category CAT III/1000 V

• Safety clamp-type test probe with 4-mm

Approx. 155x 49 mm

EN 61010/IEC 61010

4 mm plug-in technology

• Spring wire grabber with flexible, insulated shaft

safety jack in accordance with DIN VDE 0411/

Set, consisting of: 1x SKP 41 gray/red, 1x SKP 41 gray/black

SKP 41 set

Design

370010 Article no. 2146701

Probes PSS set of 2 Accessory information

- Approx. 100 x 21 mm
- Current-carrying capacity 6 A
- Measurement category CAT III/1000 V

Design

 Safety probe with 4-mm safety jack in accordance with DIN VDE 0411/EN 61010/IEC 61010

Set, consisting of:

1x probe PSS 2 gray/red 1x probe PSS 2 gray/black

370008

Article no. 2146694





Probes PSK set of 2

2 mm probe, short version

Accessory information

- Approx. 102x 10 mm
- Current-carrying capacity 16 A
- Measurement category CAT III/1000 V, CAT IV/600 V (with cover)
- Measurement category CAT II/1000 V (without cover)

Design

• Safety probe with safety jack 4-mm and 2 mm stainless steel probe in accordance with DIN VDE 0411/EN 61010/ IEC 61010


Set, consisting of:

1x probe PSK 2, gray/red (with cover) 1x probe PSK 2 gray/black (with cover)

370004

Article no. 2146675





High current safety clamp-type test probe HCP 41 set

4 mm plug-in technology

Accessory information

- Approx. 160 x 60 mm
- Current-carrying capacity 10 A
- Measurement category CAT III/1000 V

Design

 Safety clamp-type test probe with 4-mm safety jack in accordance with DIN VDE 0411/EN 61010/IEC 61010

Set, consisting of: 1x HCP 41 gray/red, 1x HCP 41 gray/black

370024

Article no. 2146758





TL-300

Test lead set with crocodile

(red, black, yellow), case, and temperature probe

Technical specifications

| ceimieai speeime | 40.01.5 |
|---------------------------|-------------------------------|
| Current-carrying capacity | 10 A |
| Current-carrying capacity | 10 A |
| Measurement Category | |
| Probes | CAT IV/1000 V (with cover) |
| | CAT II/1000 V (without cover) |
| Crocodile clips | CAT IV/600 V, CAT III/1000 V |
| Pollution degree | 2 |
| Safety cert.: | DIN VDE 0411/ |
| | EN 61010/IEC 61010 |
| Temperature probes | K-type flexible wire probe |
| | 4 mm plug (distance 19 mm) |
| Probe length | approx. 0.9 m |
| Temperature range | -20 °C+250 °C |
| Accuracy | -200 °C: ±2.5 °C or |
| | ±1.5% rdg. |
| | 0250 °C: ±1.1 °C or |
| | ±0.4% rdg. |
| | |

TI -300

Article no. 4588279

