

#### TL36A

# Test lead set with crocodile clips 2 mm safety probes

## **Accessory information**

- Test lead set with 4 mm safety technology
- PVC-insulated leads
- Threaded test probes
- Crocodile clips with thread connection, opening approx. 10 mm

#### **Technical specifications**

Measurement categories	
Test lines	CAT III/1000 V, CAT IV/600 V (with cover) CAT II / 1000 V (without cover)
Current-carrying capacity	10 A
Crocodile clips	CAT III / 1000 V, CAT IV / 600 V
Pollution degree	2
Safety cert.:	DIN VDE 0411/EN 61010/ IEC 61010

**Included:** 2x test leads, approx. 1 m long, with covers, 2x crocodile clips

#### TL36A

Article no. 3034444





#### TL35B

# Test lead set with safety crocodile clips 2 mm safety probes

#### **Accessory information**

- Test lead set with 4 mm safety technology
- PVC-insulated leads
- Threaded test probes
- Safety crocodile clips with thread connection, opening approx. 16 mm

#### **Technical specifications**

recrimed specimentoris		
Measurement categories		
Test lines	CAT III/1000 V, CAT IV/600 V (with cover) CAT II / 1000 V (without cover)	
Current-carrying capacity	10 A	
Crocodile clips	CAT III / 1000 V, CAT IV / 600 V	
Pollution degree	2	
Safety cert.:	DIN VDE 0411/EN 61010/ IEC 61010	

Included: 2x test leads, approx. 1 m long, with covers, 2x crocodile clips

#### TL35A

Article no. 3068232





#### EU-200 Test lead set

#### **Accessory information**

- Test lead set with 4 mm safety technology
- 4 mm test probes

#### **Technical specifications**

Measurement categories	
Test leads	CAT III / 1000 V
Probes	CAT IV / 600 V, CAT III / 1000 V (with cover)
	CAT II / 1000 V (without cover)
Current-carrying capacity	16 A
Crocodile clips	CAT III / 1000 V, CAT IV / 600 V
Pollution degree	2
Safety cert.:	DIN VDE 0411/EN 61010/

Included: 2x test leads, 2x probes (with covers), 2x crocodile clips

#### EU-200

Article no. 2745046





#### Safety set

#### **Accessory information**

• Test lead set with 4 mm safety technology

#### Technical specifications

ieciincai specincations	
Current-carrying capacity	16 A
Measurement Category	
Safety test	
leads	CAT III/1000 V
Probes	CAT III/1000 V, CAT IV / 600 V
	(with cover)
	CAT II / 1000 V (without cover)
Crocodile clip	CAT III/1000 V
Pollution degree	2
Safety cert.:	DIN VDE 0411/EN 61010/
	IEC 61010

**Included:** 1x safety test lead, red, 1x safety test lead, black, 1x probe, red, with cover, 1x probe, black, with cover, 1x crocodile clip, red, 1x crocodile clip, black

#### 370003

Article no. 2146666





#### Electronics set

#### **Accessory information**

• Test lead set with 4 mm safety plug-in technology

#### Technical specifications

Current-carrying capacity	2A/6A/16A
Measurement Category	
Safety test leads	CAT III/1000 V
Probes	CAT III/1000 V
Crocodile clip	CAT III/1000 V
Clamp-type test probes	CAT III/1000 V
Pollution degree	2
Safety cert.:	DIN VDE 0411/EN 61010/
	IEC 61010

**Included:** 1x safety test lead, red, 16A, 1 s safety test lead, black, 16A, 1x crocodile clip, red, 16A, 1x crocodile clip, black, 16A, 1x safety clamp-type test probe, red, 2A, 1x safety clamp-type test probe, black, 2A, 1x safety probe, red, 6A, 1x safety probe, black, 6A

#### 370001

Article no. 3313577





### Electrician set

#### **Accessory information**

• Test lead set with 4 mm safety plug-in technology

#### **Technical specifications**

Current-carrying capacity	6A/10A/16A
Measurement Category	
Safety test	
leads	CAT III/1000 V
Probes	CAT III/1000 V
Crocodile clip	CAT III/1000 V
Clamp-type test probes	CAT III/1000 V
Pollution degree	2
Safety cert.:	DIN VDE 0411/EN 61010/
	IEC 61010

**Included:** 1x safety test lead, red, 16A, 1 s safety test lead, black, 16A, 1x safety probe, red, 6A, 1x safety probe, black, 6A, 1x safety clamp-type test probe, red, 10A, 1x safety clamp-type test probe, black, 10A, 1x crocodile clip, red, 16A, 1x crocodile clip, black, 16A

#### 370000

Article no. 2146653

