

## TZe Tape range

3,5 mm	6 mm	9 mm	12 mm	18 mm	24 mm	36 mm
<b>Standard laminated (8 metres / *4 metres)</b>						
	TZe-111	TZe-121	TZe-131 / 131S*	TZe-141	TZe-151	TZe-161
			TZe-132			
			TZe-133			
			TZe-135	TZe-145		
	TZe-211	TZe-221	TZe-231 / 231S*	TZe-241	TZe-251	TZe-261
		TZe-222	TZe-232	TZe-242	TZe-252	TZe-262
		TZe-223	TZe-233	TZe-243	TZe-253	TZe-263
			TZe-334	TZe-344	TZe-354	
	TZe-315	TZe-325	TZe-335	TZe-345	TZe-355	TZe-365
		TZe-421	TZe-431	TZe-441	TZe-451	TZe-461
			TZe-435			
		TZe-521	TZe-531	TZe-541	TZe-551	TZe-561
			TZe-535		TZe-555	
	TZe-611	TZe-621	TZe-631 / 631S*	TZe-641	TZe-651	TZe-661
		TZe-721	TZe-731	TZe-741	TZe-751	
<b>Fluorescent Laminated - 5 m</b>						
			TZe-B31		TZe-B51	
			TZe-C31		TZe-C51	
<b>Matt Laminated - 8 m</b>						
			TZe-M31			
			TZe-MQL35**			
			TZe-MQP35**			
			TZe-MQG35**			
<b>Metallic Laminated - 8 m</b>						
		TZe-M921	TZe-M931		TZe-M951	TZe-M961
<b>Non-Laminated - 8 m</b>						
TZe-N201		TZe-N221	TZe-N231	TZe-N241	TZe-N251	
<b>Flexible ID Laminated - 8 m</b>						
	TZe-FX211	TZe-FX221	TZe-FX231	TZe-FX241	TZe-FX251	TZe-FX261
	TZe-FX611	TZe-FX621	TZe-FX631	TZe-FX641	TZe-FX651	TZe-FX661
<b>Strong Adhesive Laminated - 8 m</b>						
		TZe-S121	TZe-S131	TZe-S141	TZe-S151	
	TZe-S211	TZe-S221	TZe-S231	TZe-S241	TZe-S251	TZe-S261
		TZe-S621	TZe-S631	TZe-S641	TZe-S651	
<b>Fabric - 3 m</b>						
			TZe-FA3	TZe-FA4B		
<b>Security Laminated - 8 m</b>						
				TZe-SE4		

## HSe heat-shrink tube range (1.5 metres)

5,8 mm	8,8 mm	11,7 mm	17,7 mm	23,6 mm
HSe-211	HSe-221	HSe-231	HSe-241	HSe-251

(Tape availability differs by country)

## FLe die-cut label range (72 labels)

45mm x 21mm
FLe-2511
FLe-6511
FLe-7511

