

DYMO®

DURABLE LABELS



DYMO® LW Durable Labels offers stronger resistance on challenging surfaces.

- ▶ Industrial-strength adhesive
- ▶ Protective coated labels offering extra-resistance
- ▶ Scratch- and tear-resistant plastic material

Typical LW Durable label applications:



LABEL TYPE	ITEM CODE	DESCRIPTION	SIZE (W x H mm)	LABELS/ROLL ROLLS/BOX	ADHESIVE	MATERIAL
	1976200	LW Durable Labels	25 x 89	100/roll - 1/box	Permanent	Polypropylene with protective coating
	1933081	LW Durable Labels	25 x 89	350/roll - 2/box		
	1976411	LW Durable Labels	25 x 54	160/roll - 1/box		
	1933085	LW Durable Labels	19 x 64	450/roll - 2/box		
	1933083	LW Durable Labels	25 x 25	850/roll - 2/box		
	1933084	LW Durable Labels	57 x 32	800/roll - 1/box		
	1976414	LW Durable Labels	59 x 102	50/roll - 1/box		
	1933088	LW Durable Labels	59 x 102	300/roll - 1/box		
	1933087	LW Durable Labels	59 x 190	170/roll - 1/box		
	1933086	LW Durable Labels*	104 x 159	200/roll - 1/box		

*For use with LabelWriter™ 4XL only

	Multi-surface	Solvent Resistant	Moisture	Temperature	Mailing & Shipping	Name badges	Inventory	Floor Marking	Shelving	Compatibility
	Properties				Applications					Compatibility
LW Paper	-	-	-	-18° C to 25° C	✓	✓	-	-	-	All LabelWriter™ printers
LW Durable	✓	✓	✓	-18° C to 50° C	✓	-	✓	✓	✓	All LabelWriter™ printers*

†Check compatible DYMO® labelling machines on page 9.

*not recommended for use with the LabelWriter® 450 Duo

Find the right label for the right application