

Magellan 3410VSi	
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, Counter/Wall Mount, Euro Power Supply, 15' RS232 cable	M3410-010210-07104
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, Counter/Wall Mount, No Power Supply, 15' USB Keyboard POT cable	M3410-010210-00604
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, Counter/Wall Mount, No Power Supply, 15' USB OEM POT cable	M3410-010210-00403
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, Counter/Wall Mount, No Power Supply, No Cable	M3410-010210
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, Counter/Wall Mount, US/Canada Power Supply, 15' RS232 cable	M3410-010210-01104
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, No Accessories	M3410-010200
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, No Mount, Brazil Power Supply, 15' RS232 interface cable	M3410-010200-0E104
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, No Mount, Euro Power Supply, 15' RS232 cable	M3410-010200-07104
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, No Mount, Euro Power Supply, USB cable Type A, 15'™, USB Keyboard I/F	M3410-010200-07604
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, No Mount, No Power Supply, 15' USB OEM POT cable	M3410-010200-00403
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, No Mount, No Power Supply, USB Keyboard Type A 15	M3410-010200-00604
Magellan 3410VSi, Default Configuration, 1D/2D Scanning, No Mount, US/Canada Power Supply, 15' RS232 interface cable	M3410-010200-01104

Magellan 3450VSi Imager	
Magellan 3450VSi, Kit, Host POT, RS-232 WN Scanner, 1D/2D Model, DE9P Beetle, DC Plug, 4.5 m / 15 ft Cable	M3460-010200-00230
Magellan 3450VSi, Kit, Host POT, RS-232WN Scanner, 1D/2D Model, Counter/Wall Mount, DE9P Beetle, DC Plug, 4.5 m / 15 ft Cable	M3460-010210-00230
Magellan 3450VSi, Kit, OEM USB Scanner, 1D/2D Model with Digimarc, Counter/Wall Mount, POT 4.6 m Cable	M3450-010310-00403
Magellan 3450VSi, Kit, OEM USB Scanner, 1D/2D Model, POT 4.6 m Cable	M3450-010200-00403
Magellan 3450VSi, Kit, OEM USB Scanner, 1D/2D Model, Counter/Wall Mount, CSS with Omni-Mount, POT 4.6 m Cable	M3450-010210-20403
Magellan 3450VSi, Kit, OEM USB Scanner, 1D/2D Model, Counter/Wall Mount, POT 4.6 m Cable	M3450-010210-00403
Magellan 3450VSi, Kit, RS-232 Scanner, 1D/2D Model with Digimarc, Counter/Wall Mount, CSS with Omni-Mount, Power Brick/Cord (US), PC DB9 4.5 m/15 ft Ext Pwr Cable	M3450-010310-21104
Magellan 3450VSi, Kit, RS-232 Scanner, 1D/2D Model with Digimarc, Counter/Wall Mount, Power Brick/Cord (EU), PC DB9 4.5 m/15 ft Ext Pwr Cable	M3450-010310-07104
Magellan 3450VSi, Kit, RS-232 Scanner, 1D/2D Model with Digimarc, Counter/Wall Mount, Power Brick/Cord (US), PC DB9 4.5 m/15 ft Ext Pwr Cable	M3450-010310-01104
Magellan 3450VSi, Kit, RS-232 Scanner, 1D/2D Model with Digimarc, Power Brick/Cord (EU), PC DB9 4.5 m/15 ft Ext Pwr Cable	M3450-010300-07104


Magellan 3450VSi, Kit, RS-232 Scanner, 1D/2D Model, Power Brick/Cord (China), PC DB9 4.5 m/15 ft Ext Pwr Cable	M3450-010200-05104
Magellan 3450VSi, Kit, RS-232 Scanner, 1D/2D Model, Counter/Wall Mount, Power Brick/Cord (EU), PC DB9 4.5 m/15 ft Ext Pwr Cable	M3450-010210-07104
Magellan 3450VSi, Kit, RS-232 Scanner, 1D/2D Model, Power Brick/Cord (EU), PC DB9 4.5 m/15 ft Ext Pwr Cable	M3450-010200-07104
Magellan 3450VSi, Kit, USB Comm Scanner, 1D/2D Model, Counter/Wall Mount, Power Brick/Cord (EU), Type A 4.5 m/15 ft Cable	M3450-010210-07904
Magellan 3450VSi, Kit, USB Keyboard Scanner, 1D/2D Model with Digimarc, Counter/Wall Mount, Power Brick/Cord (EU), Type A 4.5 m/15 ft Cable	M3450-010310-07604
Magellan 3450VSi, Kit, USB Keyboard Scanner, 1D/2D Model with Digimarc, Counter/Wall Mount, Power Brick/Cord (JP), Type A 4.5 m/15 ft Cable	M3450-010310-04604
Magellan 3450VSi, Kit, USB Keyboard Scanner, 1D/2D Model, Power Brick/Cord (China), Type A 4.5 m/15 ft Cable	M3450-010200-05604
Magellan 3450VSi, Kit, USB Keyboard Scanner, 1D/2D Model, Counter/Wall Mount, CSS with Omni-Mount, Power Brick/Cord (EU), Type A 4.5 m/15 ft Cable	M3450-010210-27604
Magellan 3450VSi, Kit, USB Keyboard Scanner, 1D/2D Model, Counter/Wall Mount, Power Brick/Cord (EU)	M3450-010210-07600
Magellan 3450VSi, Kit, USB Keyboard Scanner, 1D/2D Model, Counter/Wall Mount, Power Brick/Cord (EU), Type A 4.5 m/15 ft Cable	M3450-010210-07604
Magellan 3450VSi, Kit, USB Keyboard Scanner, 1D/2D Model, Counter/Wall Mount, Power Brick/Cord (US), Type A 4.5 m/15 ft Cable	M3450-010210-01604
Magellan 3450VSi, Kit, USB Keyboard Scanner, 1D/2D Model, Power Brick/Cord (EU), Type A 4.5 m/15 ft Cable	M3450-010200-07604
Magellan 3450VSi, Scanner, Multi-Interface, 1D/2D Model (Required Cable and/or Power Accessories Sold Separately)	M3450-010200
Magellan 3450VSi, Scanner, Multi-Interface, 1D/2D Model with Digimarc (Required Cable and/or Power Accessories Sold Separately)	M3450-010300
Magellan 3450VSi, Scanner, Multi-Interface, 1D/2D Model, Counter/Wall Mount (Required Cable and/or Power Accessories Sold Separately)	M3450-010210


EASEOFCARE AGREEMENTS	
MAGELLAN 3410VSi EofC 2 DAYS COMPREHENSIVE, 3 YEARS	ZSC2M3410VS31
MAGELLAN 3410VSi EofC 2 DAYS COMPREHENSIVE, 5 YEARS	ZSC2M3410VS51
MAGELLAN 3410VSi EofC 2 DAYS COMPREHENSIVE, RENEWAL	ZSC2M3410VSR1
MAGELLAN 3410VSi EofC 5 DAYS, 3 YEARS	ZSN5M3410VS31
MAGELLAN 3410VSi EofC 5 DAYS, 5 YEARS	ZSN5M3410VS51
MAGELLAN 3410VSi EofC 5 DAYS, RENEWAL	ZSN5M3410VSR1
MAGELLAN 3450VSi EofC 2 DAYS COMPREHENSIVE, 3 YEARS	ZSC2M3450VS31

MAGELLAN 3450VSi EofC 2 DAYS COMPREHENSIVE, 5 YEARS	ZSC2M3450VS51
MAGELLAN 3450VSi EofC 2 DAYS COMPREHENSIVE, RENEWAL	ZSC2M3450VSR1
MAGELLAN 3450VSi EofC 5 DAYS, 3 YEARS	ZSN5M3450VS31
MAGELLAN 3450VSi EofC 5 DAYS, 5 YEARS	ZSN5M3450VS51
MAGELLAN 3450VSi EofC 5 DAYS, RENEWAL	ZSN5M3450VSR1
MGL 3410VSi EofC OVERNIGHT REPLACEMENT, COMPREHENSIVE, 3 YEARS	ZSC1M3410VS31
MGL 3410VSi EofC OVERNIGHT REPLACEMENT, COMPREHENSIVE, 5 YEARS	ZSC1M3410VS51
MGL 3410VSi EofC OVERNIGHT REPLACEMENT, COMPREHENSIVE, RENEWAL	ZSC1M3410VSR1
MGL 3450VSi EofC OVERNIGHT REPLACEMENT, COMPREHENSIVE, 3 YEARS	ZSC1M3450VS31
MGL 3450VSi EofC OVERNIGHT REPLACEMENT, COMPREHENSIVE, 5 YEARS	ZSC1M3450VS51
MGL 3450VSi EofC OVERNIGHT REPLACEMENT, COMPREHENSIVE, RENEWAL	ZSC1M3450VSR1


CABLES	
Cable, IBM USB, Power Off Terminal, Straight, 2 m	8-0754-07
Cable, RS-232, 9D, Beetle, 4.5 m/15 ft	90A052129
Cable, RS-232, DE9P, SNI Beetle, POT, DC Plug, 4.5 m/15 ft	90A052380
Cable, RS-232, ICL, PC, 9D,4.5 m/15 ft	90A052121
Cable, USB, Type A, Power Off Terminal, 2 m	8-0754-12
CABLE,USB,SERIES A,POT,1M	90A052363
CABLE,USB,TYPEA,EXT PWR,15'	90A052292
CBL ASSY,USB+ POT,ERI, BARREL PLUG, 4.6M	90A052406
CBL ASY,(RoHS),DUAL USB,TYPE A,POT,15'	90A052325
CBL ASY,OEM,USB,POT, BARREL,DC PLUG,4.6M	90A052311

MISCELLANEOUS		
----------------------	--	--

	Customer Service Scanner (Mount Ordered Separately.)	90ACC0169
--	--	-----------

	Customer Service Scanner with Omni Mount Accessory	90ACC0170
--	--	-----------

MOUNTS/STANDS		
----------------------	--	--

	Mount, Table/Wall Mount, Magellan 3450VSi	90ACC0299
--	---	-----------

Mount, Tilt Riser, Magellan 3450VSi	90ACC0323
-------------------------------------	-----------

POWER SUPPLIES/CORDS		
-----------------------------	--	--

Power Brick, Worldwide, 12V/18W	90ACC0193
Power Cord, 100V, Japan	6003-0927
Power Cord, 120V, US, Twist & Lock	6003-0932
Power Cord, 220V, Australia	6003-0925
Power Cord, 220V, Italy/Chile	6003-0924
Power Cord, 240V, UK	6003-0923
POWER CORD, AC, BIS INDIA, 5', RoHS	90ACC0192
Power Cord, AC, IEC/EU	6003-0940
Power Cord, IEC C13, Argentina	6003-0926
Power Cord, IEC C13, Brazil (For use with 8-0935)	6003-0942
Power Cord, IEC C13, China	6003-0935
Power Cord, IEC C13, Korea	6003-0930
US Power Cord, 110V, US, Standard	6003-0941