





Magellan 9300i Scanner/Scale	
Magellan 9300i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing with Scale Sentry, EU Power Cord/Brick (Cable Sold Separately.)	931024111-00310
Magellan 9300i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing with Scale Sentry, EU Power Cord/Brick, Retail USB E/P Cable	931024111-00351
Magellan 9300i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing with Scale Sentry, EU Power Cord/Brick, RS-232 WN Cable	931024111-00321
Magellan 9300i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing with Scale Sentry, EU Power Cord/Brick, USB Keyboard Type A E/P Cable	931024111-00361
Magellan 9300i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing, EU Power Cord/Brick, RS-232 Std Cable	931024110-00312
Magellan 9300i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing, EU Power Cord/Brick, USB Type A E/P Cable, 15 ft	931024110-00352
Magellan 9300i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing, USB POT Cable	931024110-00053
Magellan 9300i Scanner Only, Adaptive Scale Config, Med Sapphire Platter/Shelf Mount w/Flip-up Produce Rail, Std Processing with Scale Sentry, USB POT Cable	931024111-00053
Magellan 9300i Scanner Only, Std Config, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing	931014110
Magellan 9300i Scanner Only, Std Config, No Platter/Short Shelf Mount, Standard Processing	931010210
Magellan 9300i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, Standard Processing, EU Power Cord/Brick (Cable Sold Separately.)	931013110-00310
Magellan 9300i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, Standard Processing, EU Power Cord/Brick, RS-232 Std Cable, EAS	931013110-003121
Magellan 9300i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, Standard Processing, USB POT Cable	931013110-00053
Magellan 9300i Scanner/Scale, EU Factory Pre-Verified Metric Config/Single Interval w/ Display, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing, Metric Single Display/Single Interval, None, EU Power Cord/Brick, RS-232 Std Cab	9360441030-020313
Magellan 9300i Scanner/Scale, EU Non-preverified Metric Config/Single Interval, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing, EU Power Cord/Brick, RS-232 Single Cable	9320341020-000331
Magellan 9300i Scanner/Scale, Factory Pre-Verified Metric Config/Dual Interval w/ Display, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing, EU Power Cord/Brick, RS-232 Single Cable	9360441320-220331
Magellan 9300i Scanner/Scale, Factory Pre-Verified Metric Config/Dual Interval w/ Display, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing, EU Power Cord/Brick, RS-232 WN Cable, EAS	9360441320-2203211
Magellan 9300i Scanner/Scale, FR Factory Pre-Verified Metric Config/Single Interval w/ Display, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing with Scale Sentry, EU Power Cord/Brick (Cable Sold Separately.)	9360441131-020310
Magellan 9300i Scanner/Scale, FR Factory Pre-Verified Metric Config/Single Interval w/ Display, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing with Scale Sentry, Retail USB POT Cable	9360441131-020053




Magellan 9300i Scanner/Scale, FR Factory Pre-Verified Metric Config/Single Interval w/ Dual Display, Med Sapphire Platter/Shelf Mount w/ Flip-up Produce Rail, Standard Processing with Scale Sentry, EU Power Cord/Brick, Retail USB Type A E/P Cable	9360441131-040352
--	-------------------

EASEOFCARE AGREEMENTS	
MAG9300i, SCANNER ONLY, 2 DAYS, 3 YEARS, COMPREHENSIVE	ZSC2M93NS31
MAG9300i, SCANNER ONLY, 2 DAYS, 5 YEARS, COMPREHENSIVE	ZSC2M93NS51
MAG9300i, SCANNER ONLY, 2 DAYS, RENEWAL, COMPREHENSIVE	ZSC2M93NSR1
MAG9300i, SCANNER ONLY, 5 DAYS, 3 YEARS	ZSN5M93NS31
MAG9300i, SCANNER ONLY, 5 DAYS, 5 YEARS	ZSN5M93NS51
MAG9300i, SCANNER ONLY, 5 DAYS, RENEWAL	ZSN5M93NSR1
MAG9300i, SCANNER ONLY, MINIMUM REPAIR CHARGE	ZR0M93SOMIN
MAG9300i, SCANNER ONLY, OVERNIGHT, 3 YEARS, COMPREHENSIVE	ZSC1M93NS31
MAG9300i, SCANNER ONLY, OVERNIGHT, 5 YEARS, COMPREHENSIVE	ZSC1M93NS51
MAG9300i, SCANNER ONLY, OVERNIGHT, RENEWAL, COMPREHENSIVE	ZSC1M93NSR1
MAG9300i, SCANNER ONLY, WHOLE UNIT REPAIR	ZR0M93SOMAX
MAG9300i, SCANNER SCALE, 2 DAYS, 3 YEARS, COMPREHENSIVE	ZSC2M93SS31
MAG9300i, SCANNER SCALE, 2 DAYS, 5 YEARS, COMPREHENSIVE	ZSC2M93SS51
MAG9300i, SCANNER SCALE, 2 DAYS, RENEWAL, COMPREHENSIVE	ZSC2M93SSR1
MAG9300i, SCANNER SCALE, 5 DAYS, 3 YEARS	ZSN5M93SS31
MAG9300i, SCANNER SCALE, 5 DAYS, 5 YEARS	ZSN5M93SS51
MAG9300i, SCANNER SCALE, 5 DAYS, RENEWAL	ZSN5M93SSR1
MAG9300i, SCANNER SCALE, MINIMUM REPAIR CHARGE	ZR0M93SSMIN
MAG9300i, SCANNER SCALE, OVERNIGHT, 3 YEARS, COMPREHENSIVE	ZSC1M93SS31
MAG9300i, SCANNER SCALE, OVERNIGHT, 5 YEARS, COMPREHENSIVE	ZSC1M93SS51
MAG9300i, SCANNER SCALE, OVERNIGHT, RENEWAL, COMPREHENSIVE	ZSC1M93SSR1
MAG9300i, SCANNER SCALE, WHOLE UNIT REPAIR	ZR0M93SSMAX

CABLES	
Cable IBM 4683, Port 17, POS, 4.5 m/15 ft	90A052131
CABLE, EAS, INTERLOCK, 1800MM	90A052247
Cable, IBM 46XX, Port 9E, 4.5 m/15 ft	90A052132
Cable, IBM USB, External Power, 4.5 m/15 ft	90A052133
Cable, IBM USB, POT, 3 PIN, 4.6M	90A052276
Cable, RS-232, 9D, Beetle, 4.5 m/15 ft	90A052129
Cable, RS-232, ICL, PC, 9D,4.5 m/15 ft	90A052121
Cable, RS-232, PC Scale, Female, 15 ft	90A052138
Cable, RS-232, PC, 25D,4.5 m/15 ft	90A052125
Cable, RS-232, SASI, Super Star, 15 ft	90A052137
Cable, RS-232, SASI, Super Star, RJ4, 15 ft	90A052122
Cable, RS-232, SNI Beetle, 4.5 m/15 ft	90A052197
Cable, USB, Type A, External Power, 4.5 m/15 ft	90A052135

MISCELLANEOUS		
	Customer Service Scanner (Mount Ordered Separately.)	90ACC0169
	Customer Service Scanner with Bonnet Back Mount Accessory	90ACC0175
	Customer Service Scanner with Bonnet Side Mount Accessory	90ACC0174
	Customer Service Scanner with Omni Mount Accessory	90ACC0170

Scale Zero Button, Magellan 9300i/9400i	90ACC0393
---	-----------

MOUNTS/STANDS		
	Bonnet Back Mount for Customer Service Scanner (CSS Ordered Separately)	90ACC0172
	Bonnet Side Mount for Customer Service Scanner (CSS Ordered Separately)	90ACC0171
	Omni Mount for Customer Service Scanner (CSS Ordered Separately)	90ACC0173

POWER SUPPLIES/CORDS		
Power Brick, Worldwide		90ACC0194
Power Cord, 100V, Japan		6003-0927
Power Cord, 120V, US, Twist & Lock		6003-0932
Power Cord, 220V, Australia		6003-0925
Power Cord, 220V, Italy/Chile		6003-0924
Power Cord, 240V, UK		6003-0923
Power Cord, AC, IEC/EU		6003-0940
Power Cord, Euro Monitor		6003-0931
Power Cord, IEC C13, Brazil (For use with 8-0935)		6003-0942
US Power Cord, 110V, US, Standard		6003-0941

REMOTE SCALE DISPLAYS

	Kit, Remote Scale Display, English, Dual Head, Dual Interval, US/Canada/Puerto Rico	90ACC0107
	Kit, Remote Scale Display, English, Dual Head, Single Interval, US/Canada/Puerto Rico	90ACC0103
	Kit, Remote Scale Display, English, Single Head, Dual Interval, US/Canada/Puerto Rico	90ACC0106
	Kit, Remote Scale Display, English, Single Head, Single Interval, US/Canada/Puerto Rico	90ACC0102
	Kit, Remote Scale Display, Metric, Dual Head, Dual Interval, Europe	90ACC0109
	Kit, Remote Scale Display, Metric, Dual Head, Single Interval, Europe	90ACC0105
	Kit, Remote Scale Display, Metric, Single Head, Dual Interval, Europe	90ACC0108
	Kit, Remote Scale Display, Metric, Single Head, Single Interval, Europe	90ACC0104