

<b>Magellan 9600i</b>	
Magellan 9600i Scanner Only, Adaptive Scale Ready, Med Platter/Flip-up Produce Rail/Shelf Mount with Scale Sentry (Power Accessories and Cable Sold Separately)	96113102000-000101
Magellan 9600i Scanner Only, Adaptive Scale Ready, Med Platter/Flip-up Produce Rail/Shelf Mount with Scale Sentry, EU Power Brick/Cord, RS-232 Std Cable	96113102000-004110
Magellan 9600i Scanner Only, Adaptive Scale Ready, Med Platter/Flip-up Produce Rail/Shelf Mount with Scale Sentry, EU Power Brick/Cord, USB E/P Cable	96113102000-004510
Magellan 9600i Scanner Only, Adaptive Scale Ready, Med Platter/Flip-up Produce Rail/Shelf Mount with Scale Sentry, RS-232 Std Cables	96113102000-000120
Magellan 9600i Scanner Only, Adaptive Scale Ready, Med Platter/Flip-up Produce Rail/Shelf Mount with Scale Sentry, USB POT Cable	96113102000-000530
Magellan 9600i Scanner Only, Adaptive Scale Ready, Med Platter/Flip-up Produce Rail/Shelf Mount with Scale Sentry, USB POT Cable	96113102000-000531
Magellan 9600i Scanner Only, Long Platter/Fixed Produce Rail/Flange Mount with Scale Sentry (Power Accessories and Cable Sold Separately)	96122001000-000100
Magellan 9600i Scanner Only, Long Platter/Fixed Produce Rail/Flange Mount with Scale Sentry, US Std Power Brick/Cord, USB E/P Cable	96122001000-003511
Magellan 9600i Scanner Only, Long Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry (Power Accessories and Cable Sold Separately)	96121001000-000100
Magellan 9600i Scanner Only, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry (Power Accessories and Cable Sold Separately)	96111001000-000100
Magellan 9600i Scanner Only, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, USB POT Cable	96111001000-000530
Magellan 9600i Scanner Only, Med Platter/Flush/Shelf Mount, EU Power Brick/Cord, USB POT Cable	96116001000-004530
Magellan 9600i Scanner Only, Med Platter/Flush/Shelf Mount, USB POT Cable	96116001000-000540
Magellan 9600i Scanner Only, Short Platter/Shelf Mount (Power Accessories and Cable Sold Separately)	96101001000-000100
Magellan 9600i Scanner Only, Short Platter/Shelf Mount, EU Power Brick/Cord, RS-232 WN Cable	96101001000-004210
Magellan 9600i Scanner Only, Short Platter/Shelf Mount, US Std Power Brick/Cord, USB Type A E/P Cable	96101001000-003520
Magellan 9600i Scanner Only, Short Platter/Shelf Mount, USB COMM POT Cable	96101001000-000550
Magellan 9600i Scanner Only, Short Platter/Shelf Mount, USB POT Cable	96101001000-000530
Magellan 9600i Scanner/Scale, Long Platter/Fixed Produce Rail/Flange Mount with Scale Sentry, Brazil/Single Interval with Bubble/Metric Config with Display, Brazil Power Brick/Cord, RS-232 Std Cable	96222C13000-0E8140
Magellan 9600i Scanner/Scale, Long Platter/Fixed Produce Rail/Flange Mount with Scale Sentry, US/Single Interval/English Config (Power Accessories and Cable Sold Separately)	96222212000-000100
Magellan 9600i Scanner/Scale, Long Platter/Fixed Produce Rail/Flange Mount with Scale Sentry, US/Single Interval/English Config with Display, USB POT Cable	96222211000-010530

Magellan 9600i Scanner/Scale, Long Platter/Fixed Produce Rail/Flange Mount with Scale Sentry, US/Single Interval/English Config, USB POT Cable	96222212000-000530
Magellan 9600i Scanner/Scale, Long Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry,US/Single Interval/English Config (Power Accessories and Cable Sold Separately)	96221212000-000100
Magellan 9600i Scanner/Scale, Long Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry,US/Single Interval/English Config, US Std Power Brick/Cord, USB Type A E/P Cable	96221212000-003520
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Flange Mount with Scale Sentry, Brazil/Single Interval with Bubble/Metric Config with Display, Brazil Power Brick/Cord, RS-232 Std Cable	96212C13000-0E8140
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Flange Mount with Scale Sentry, US/Single Interval/English Config, US Std Power Brick/Cord, USB Type A E/P Cable	96212212000-003520
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, EU/Single Interval/Metric Config with Display, RS-232 WN Cables (Power Accessories Sold Separately)	96211313000-020220
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, EU/Single Interval/Metric Config with Display, RS-232 WN Cables (Power Accessories Sold Separately)	96211313000-020221
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, EU/Single Interval/Metric Config with Display, UK Power Brick/Cord, RS-232 Std Cables	96211313000-027121
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, EU/Single Interval/Metric Config with Display, USB POT Cable	96211313000-020531
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, EU/Single Interval/Metric Config with Display, USB POT Cable	96211313000-020541
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, US/Single Interval/English Config (Power Accessories and Cable Sold Separately)	96211212000-000100
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, US/Single Interval/English Config, US Std Power Brick/Cord, USB Type A E/P Cable	96211212000-003520
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, US/Single Interval/English Config, USB POT Cable	96211212000-000531
Magellan 9600i Scanner/Scale, Med Platter/Fixed Produce Rail/Shelf Mount with Scale Sentry, US/Single Interval/English Config, USB POT Cable	96211212000-000540
Magellan 9600i Scanner/Scale, Med Platter/Flip-up Produce Rail/Shelf Mount with Scale Sentry, EU/Single Interval/Metric Config with Display, USB E/P Cable (Power Accessories Sold Separately)	96213313000-020510

<b>CABLES</b>	
Cable, IBM USB, External Power, 4.5 m/15 ft	90A052133
Cable, IBM USB, POT, 3 PIN, 4.6M	90A052276
Cable, RS-232, 9D, Beetle, 4.5 m/15 ft	90A052129
Cable, RS-232, ICL, PC, 9D,4.5 m/15 ft	90A052121
Cable, RS-232, PC Scale, Female, 15 ft	90A052138
Cable, RS-232, PC, 25D,4.5 m/15 ft	90A052125
Cable, RS-232, SNI Beetle, 4.5 m/15 ft	90A052197
Cable, USB, Type A, External Power, 4.5 m/15 ft	90A052135

<b>POWER SUPPLIES/CORDS</b>	
Power Brick, Worldwide	90ACC0194
Power Cord, 100V, Japan	6003-0927
Power Cord, 120V, US, Twist & Lock	6003-0932
Power Cord, 220V, Australia	6003-0925
Power Cord, 220V, Italy/Chile	6003-0924
Power Cord, 240V, UK	6003-0923
POWER CORD, AC, BIS INDIA, 5', RoHS	90ACC0192
Power Cord, AC, IEC/EU	6003-0940
Power Cord, IEC C13, Argentina	6003-0926
Power Cord, IEC C13, Brazil (For use with 8-0935)	6003-0942
Power Cord, IEC C13, Korea	6003-0930
US Power Cord, 110V, US, Standard	6003-0941