Magellan 9800i Scanner Only	
Magellan 9800i Scanner Only, Adaptive Scale, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, Checkpoint EAS, TDR Tall, EU Power Cord/Brick, Retail USB E/P Cable	9810210221-04351
Magellan 9800i Scanner Only, Adaptive Scale, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, Checkpoint EAS, TDR Tall, EU Power Cord/Brick, RS-232 WN Cable	9810210221-04321
Magellan 9800i Scanner Only, Adaptive Scale, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, EU Power Cord/Brick,RS-232 Standard Cable	9810210220-00313
Magellan 9800i Scanner Only, Adaptive Scale, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, Power Brick Only (No Line Cord), USB Keyboard Type A E/P Cable	9810210220-00761
Magellan 9800i Scanner Only, Adaptive Scale, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, TDR Tall, EU Power Cord/Brick (Cable Sold Separately.)	9810210220-04310
Magellan 9800i Scanner Only, Adaptive Scale, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, TDR Tall, EU Power Cord/Brick, Retail USB POT Cable	9810210220-04353
Magellan 9800i Scanner Only, Adaptive Scale, Med Sapphire Platter/Shelf Mount w/ Flip Up Produce Rail, Scale Sentry, IT/CHI Power Cord/Brick (Cable Sold Separately.)	9810214223-00510
Magellan 9800i Scanner Only, Long Sapphire Platter/Flange Mount w/ Fixed Produce Rail, TDR Tall, IT/CHI Power Cord/Brick, Retail USB E/P Cable	9810120120-04551
Magellan 9800i Scanner Only, Med Sapphire Platter/Flange Mount w/ Fixed Produce Rail, TDR Tall, IT/CHI Power Cord/Brick, Retail USB E/P Cable	9810112120-04551
Magellan 9800i Scanner Only, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, EU Power Cord/Brick, RS-232 Standard Cable	9810110120-00313
Magellan 9800i Scanner Only, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, EU Power Cord/Brick, USB Keyboard Type A E/P Cable	9810110120-00361
Magellan 9800i Scanner Only, Short Sapphire Platter/Shelf Mount, Checkpoint EAS, TDR Short, EU Power Cord/Brick, RS-232 WN Cable	9810101121-03321
Magellan 9800i Scanner Only, Short Sapphire Platter/Shelf Mount, Checkpoint EAS, TDR Tall, EU Power Cord/Brick, Retail USB POT Cable	9810101121-04353
Magellan 9800i Scanner Only, Short Sapphire Platter/Shelf Mount, Checkpoint EAS, TDR Tall, EU Power Cord/Brick, RS-232 Cable	9810101121-04311
Magellan 9800i Scanner Only, Short Sapphire Platter/Shelf Mount, Checkpoint EAS, TDR Tall, EU Power Cord/Brick, RS-232 Cable	9810101121-04312
Magellan 9800i Scanner Only, Short Sapphire Platter/Shelf Mount, Checkpoint EAS, TDR Tall, Japan Power Cord/Brick, RS-232 Standard Cable	9810101121-04913
Magellan 9800i Scanner Only, Short Sapphire Platter/Shelf Mount, Digimarc S/W, TDR Tall, Japan Power Cord/Brick, RS-232 Standard Cable	9810101130-04913
Magellan 9800i Scanner Only, Short Sapphire Platter/Shelf Mount, TDR Tall, No Brick, Retail USB POT Cable	9810101120-04053
Magellan 9800i Scanner Only, Short Sapphire Platter/Shelf Mount, TDR Tall, US Power Cord/Brick, Retail USB POT Cable	9810101120-04253

Magellan 9800i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, IT/CHI Power Cord/Brick (Cable Sold Separately.)	9810101120-00510
Magellan 9800i Scanner Only, Std Config, Short Sapphire Platter/Shelf Mount, Korea Power Cord/Brick, USB Keyboard Type A E/P Cable	9810101120-00B61

Magellan 9800i Scanner/Scale	
Magellan 9800i Scanner/Scale, Canada Metric Config/Single Interval w/Display, Long Sapphire Platter/Flange Mount w/Fixed Produce Rail, Retail OEM USB POT 4.6m Cable	98203030420-020054
Magellan 9800i Scanner/Scale, English Config/Single Interval/No Display, Long Sapphire Platter/Flange Mount w/ Fixed Produce Rail, Scale Sentry, TDR Tall, US Cord/Brick, RS-232 Cable	98202030121-004231
Magellan 9800i Scanner/Scale, English Config/Single Interval/Single Display, Long Sapphire Platter/Flange Mount w/ Fixed Produce Rail, Checkpoint EAS, TDR Tall, US Power Cord/Brick, Retail USB E/P Cable	98201030122-014251
Magellan 9800i Scanner/Scale, English Config/Single Interval/Single Display, Long Sapphire Platter/Flange Mount w/ Fixed Produce Rail, TDR Tall, No Brick, Retail USB POT Cable	98201030120-014054
Magellan 9800i Scanner/Scale, English Config/Single Interval/Single Display, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, Scale Sentry, TDR Tall, US Power Cord/Brick, RS-232 Standard Cables	98201010121-014212
Magellan 9800i Scanner/Scale, EU Factory Pre-Verified Metric Config/Dual Interval/Single Display, Med Sapphire Platter/Shelf Mount w/ Fixed Produce Rail, Consolidated Decoding, EU Power Cord/Brick, RS-232 Cables	984030132L1-040311
Magellan 9800i Scanner/Scale, Metric Config/Single Interval/No Display, Med Sapphire Platter/Shelf Mount w/Fixed Produce Rail, Consolidated Decoding w/Scale Sentry (All Accessories Sold Separately.)	982040102M1

EASEOFCARE AGREEMENTS	
MAG9800i, TDR, MINIMUM REPAIR CHARGE	ZR0M98TDRMIN
MAG9800i,S/O, WHOLE UNIT REPAIR	ZR0M98SOMAX
MAG9800i,S/O,MINIMUM REPAIR CHARGE	ZR0M98SOMIN
MAG9800i,S/S,MINIMUM REPAIR CHARGE	ZR0M98SSMIN
MAG9800i,S/S,WHOLE UNIT REPAIR	ZR0M98SSMAX
Magellan 9800i No Scale EofC 2 Days Comprehensive, 1 Year Renewal	ZSC2M98NSR1
Magellan 9800i No Scale EofC 2 Days Comprehensive, 3 Years	ZSC2M98NS31
Magellan 9800i No Scale EofC 2 Days Comprehensive, 5 Years	ZSC2M98NS51
Magellan 9800i No Scale EofC 5 Days, 1 Year Renewal	ZSN5M98NSR1
Magellan 9800i No Scale EofC 5 Days, 3 Years	ZSN5M98NS31
Magellan 9800i No Scale EofC 5 Days, 5 Years	ZSN5M98NS51

Magellan 9800i No Scale EofC Overnight Replacement Comprehensive, 1 Year Renewal	ZSC1M98NSR1
Magellan 9800i No Scale EofC Overnight Replacement Comprehensive, 3 Years	ZSC1M98NS31
Magellan 9800i No Scale EofC Overnight Replacement Comprehensive, 5 Years	ZSC1M98NS51
Magellan 9800i TDR No Scale EofC 2 Days Comprehensive, 1 Year Renewal	ZSC2M98NSRTD
Magellan 9800i TDR No Scale EofC 2 Days Comprehensive, 3 Years	ZSC2M98NS3TD
Magellan 9800i TDR No Scale EofC 2 Days Comprehensive, 5 Years	ZSC2M98NS5TD
Magellan 9800i TDR No Scale EofC 5 Days, 1 Year Renewal	ZSN5M98NSRTD
Magellan 9800i TDR No Scale EofC 5 Days, 3 Years	ZSN5M98NS3TD
Magellan 9800i TDR No Scale EofC 5 Days, 5 Years	ZSN5M98NS5TD
Magellan 9800i TDR No Scale EofC Overnight Replacement Comprehensive, 1 Year Renewal	ZSC1M98NSRTD
Magellan 9800i TDR No Scale EofC Overnight Replacement Comprehensive, 3 Years	ZSC1M98NS3TD
Magellan 9800i TDR No Scale EofC Overnight Replacement Comprehensive, 5 Years	ZSC1M98NS5TD
Magellan 9800i TDR W/Scale EofC 2 Days Comprehensive, 1 Year Renewal	ZSC2M98SSRTD
Magellan 9800i TDR W/Scale EofC 2 Days Comprehensive, 3 Years	ZSC2M98SS3TD
Magellan 9800i TDR W/Scale EofC 2 Days Comprehensive, 5 Years	ZSC2M98SS5TD
Magellan 9800i TDR W/Scale EofC 5 Days, 1 Year Renewal	ZSN5M98SSRTD
Magellan 9800i TDR W/Scale EofC 5 Days, 3 Years	ZSN5M98SS3TD
Magellan 9800i TDR W/Scale EofC 5 Days, 5 Years	ZSN5M98SS5TD
Magellan 9800i TDR W/Scale EofC Overnight Replacement Comprehensive, 1 Year Renewal	ZSC1M98SSRTD
Magellan 9800i TDR W/Scale EofC Overnight Replacement Comprehensive, 3 Years	ZSC1M98SS3TD
Magellan 9800i TDR W/Scale EofC Overnight Replacement Comprehensive, 5 Years	ZSC1M98SS5TD
Magellan 9800i W/Scale EofC 2 Days Comprehensive, 1 Year Renewal	ZSC2M98SSR1
Magellan 9800i W/Scale EofC 2 Days Comprehensive, 3 Years	ZSC2M98SS31
Magellan 9800i W/Scale EofC 2 Days Comprehensive, 5 Years	ZSC2M98SS51
Magellan 9800i W/Scale EofC 5 Days, 1 Year Renewal	ZSN5M98SSR1
Magellan 9800i W/Scale EofC 5 Days, 3 Years	ZSN5M98SS31
Magellan 9800i W/Scale EofC 5 Days, 5 Years	ZSN5M98SS51
Magellan 9800i W/Scale EofC Overnight Replacement Comprehensive, 1 Year Renewal	ZSC1M98SSR1

Magellan 9800i W/Scale EofC Overnight Replacement Comprehensive, 3 Years	ZSC1M98SS31
Magellan 9800i W/Scale EofC Overnight Replacement Comprehensive, 5 Years	ZSC1M98SS51

CABLES	
Cable IBM 4683, Port 17, POS, 4.5 m/15 ft	90A052131
Cable, IBM 46XX, Port 9E, 4.5 m/15 ft	90A052132
Cable, IBM USB, External Power, 4.5 m/15 ft	90A052133
Cable, IBM USB, POT, 4.6 m	90A052212
Cable, RS-232, 9D, Beetle, 4.5 m/15 ft	90A052129
Cable, RS-232, ICL, PC, 9D,4.5 m/15 ft	90A052121
Cable, RS-232, PC Scale, Female, 15 ft	90A052138
Cable, RS-232, PC, 25D,4.5 m/15 ft	90A052125
Cable, RS-232, SASI, Super Star, 15 ft	90A052137
Cable, RS-232, SASI, Super Star, RJ4, 15 ft	90A052122
Cable, RS-232, SNI Beetle, 4.5 m/15 ft	90A052197
Cable, USB, Type A, External Power, 4.5 m/15 ft	90A052135

MISCELLANEOUS	
ACCESSORY, BUTTONS, MGL9800i	90ACC0150
Conversion Kit, Long Flange to Medium Flange, Magellan 9800i	90ACC0217
Conversion Kit, Long Flange to Medium Shelf, Magellan 9800i	90ACC0404
Platter, Long, Sapphire Glass, Fixed Produce Rail, Scale Sentry, Magellan 9800i	90ACC0139
Platter, Long, Sapphire Glass, Flush Top (No Produce Rail), Magellan 9800i	90ACC0206
Platter, Medium, Sapphire Glass, Fixed Produce Rail, Scale Sentry, Magellan 9800i	90ACC0140
Platter, Medium, Sapphire Glass, Flip-Up Rail, Stainless Corners, Scale Sentry, Magellan 9800i	90ACC0357
Platter, Medium, Sapphire Glass, Flip-Up Rail, without Scale Sentry, Magellan 9800i	90ACC0387
Platter, Medium, Sapphire Glass, Flush Top (No Produce Rail), Magellan 9800i	90ACC0205
Platter, Short, Sapphire Glass, Magellan 9800i	90ACC0222

Top Down Imager, 7", Magellan 9800i		90ACC0403
	Top Down Reader, 9"	90ACC0213
	Top Down Reader, Tall, 12.4"	90ACC0079

MOUNTS/STANDS	
Kit, Checkstand Fill, Magellan 8500Xt/9400/9800i from NCR 7870/7875	90ACC0119

POWER SUPPLIES/CORDS	
Power Brick, Worldwide, 12V/30W, AC/DC	90ACC0196
Power Cord, 100V, Japan	6003-0927
Power Cord, 120V, US, Twist & Lock	6003-0932
Power Cord, 220V, Australia	6003-0925
Power Cord, 220V, Italy/Chile	6003-0924
Power Cord, 240V, UK	6003-0923
Power Cord, AC, IEC/EU	6003-0940
Power Cord, Euro Monitor	6003-0931
Power Cord, IEC C13, Brazil (For use with 8-0935)	6003-0942
Power Cord, IEC C13, Korea	6003-0930
US Power Cord, 110V, US, Standard	6003-0941

REMOTE SCALE DISPLAYS		
	Kit, Remote Scale Display, English, Dual Head, Dual Interval, US/Canada/Puerto Rico	90ACC0107
	Kit, Remote Scale Display, English, Dual Head, Single Interval, US/Canada/Puerto Rico	90ACC0103
	Kit, Remote Scale Display, English, Single Head, Dual Interval, US/Canada/Puerto Rico	90ACC0106
Kit, Remote Scale Display, English, Single Head, Single Interval, 22" Post		90ACC0128
	Kit, Remote Scale Display, English, Single Head, Single Interval, US/Canada/Puerto Rico	90ACC0102
	Kit, Remote Scale Display, Metric, Dual Head, Dual Interval, Europe	90ACC0109
Kit, Remote Scale Display, Metric, Dual Head, Single Interval, 22" Post		90ACC0130
	Kit, Remote Scale Display, Metric, Dual Head, Single Interval, Europe	90ACC0105
	Kit, Remote Scale Display, Metric, Single Head, Dual Interval, Europe	90ACC0108
Kit, Remote Scale Display, Metric, Single Head, Single Interval, 22" Post		90ACC0129
	Kit, Remote Scale Display, Metric, Single Head, Single Interval, Europe	90ACC0104