



Overview

## Quicklock

Circular Power Connectors up to 50 A · IP67

**Series 02**

**Quicklock Circular Connectors**

IP67

Circular power connectors with Quicklock mechanism  
**Size 12** for signal and load currents up to 5 A

Number of poles
Contact plating
Rated current
Rated voltage
Cable diameter



<b>0250</b> Quicklock plug with locking latch, size 12, straight version, with plastic housing and solder terminals	<b>0260</b> Quicklock socket, size 12, straight version, with plastic housing and solder terminals	<b>0270</b> Quicklock chassis socket, size 12, straight version, with plastic housing, solder terminals and protecting cap (IP65)
Number of poles: 2-8		
Contact plating: gold plated		
Rated current: 5 A (2-6 poles) · 3 A (7-8 poles)		
Rated voltage: 125 V		
Cable diameter: 3.0-6.0 mm		

**Series 02**

**Quicklock Circular Connectors**

IP67

Circular power connectors with Quicklock mechanism  
**Size 16** for signal and load currents up to 10 A

Number of poles
Contact plating
Rated current
Rated voltage
Cable diameter



<b>0251</b> Quicklock plug with locking latch, size 16, straight version, with plastic housing and solder terminals	<b>0261</b> Quicklock socket, size 16, straight version, with plastic housing and solder terminals	<b>026516</b> Quicklock socket with locking latch, size 16, straight version, with plastic housing and solder terminals	<b>024016</b> Quicklock chassis plug, size 16, straight version, with plastic housing, solder terminals and protecting cap (IP65)	<b>0271</b> Quicklock chassis socket, size 16, straight version, with plastic housing, solder terminals and protecting cap (IP65)
Number of poles: 2-9				
Contact plating: gold plated				
Rated current: 10 A (2-4 poles) · 5 A (5-9 poles)				
Rated voltage: 400 V				
Cable diameter: 3.0-9.0 mm				

**Series 02**

**Quicklock Circular Connectors**

IP67

Circular power connectors with Quicklock mechanism  
**Size 20** for signal and load currents up to 20 A

Number of poles
Contact plating
Rated current
Rated voltage
Cable diameter



<b>0252</b> Quicklock plug with locking latch, size 20, straight version, with plastic housing and solder terminals	<b>0262</b> Quicklock socket, size 20, straight version, with plastic housing and solder terminals	<b>026520</b> Quicklock socket with locking latch, size 20, straight version, with plastic housing and solder terminals	<b>024020</b> Quicklock chassis plug, size 20, straight version, with plastic housing, solder terminals and protecting cap (IP65)	<b>0272</b> Quicklock chassis socket, size 20, straight version, with plastic housing, solder terminals and protecting cap (IP65)
Number of poles: 2-12				
Contact plating: gold plated				
Rated current: 20 A (2-4 poles) · 12 A (5-7 poles) · 5 A (9-12 poles)				
Rated voltage: 500 V				
Cable diameter: 7.0-13.0 mm				

**Series 02**

**Quicklock Circular Connectors**

IP67

Circular power connectors with Quicklock mechanism  
**Size 28** for signal and load currents up to 50 A

Number of poles
Contact plating
Rated current
Rated voltage
Cable diameter



<b>0254</b> Quicklock plug with locking latch, size 28, straight version, with plastic housing and screw clamps (8-pole version with solder terminals)	<b>0264</b> Quicklock socket, size 28, straight version, with plastic housing and screw clamps	<b>025528</b> Quicklock plug, size 28, straight version, with plastic housing and screw clamps	<b>026528</b> Quicklock socket with locking latch, size 28, straight version, with plastic housing and screw clamps (8-pole version with solder terminals)	<b>024028</b> Quicklock flange chassis plug, size 28, straight version, with metal housing, screw clamps (8-pole version with solder terminals) and protecting cap (IP65)	<b>0274</b> Quicklock flange chassis socket, size 28, straight version, with metal housing, screw clamps (8-pole version with solder terminals) and protecting cap (IP65)
Number of poles: 2,3 and 8 (0264, 025528 only 2-,3-pole)					
Contact plating: gold plated					
Rated current: 50 A (2 poles) · 43 A (3 poles) · 17 A (8 poles)					
Rated voltage: 500 V AC					
Cable diameter: 4.0-11.5 mm					

**Accessories**



**029012 · 029016 · 029020**  
Protecting cap, IP65, size 12, 16 and 20



---

[www.lumberg.com](http://www.lumberg.com) · [info@lumberg.com](mailto:info@lumberg.com)

---