


INDEX


Instrument cables (guitar cables)	Page 8	Stereo cables	Page 12
Instrument extension cables	Page 8	Toslink cables	Page 15
Patch cables	Page 8	Analogue VGA cables	Page 20
Multicore cables	Page 8	HDMI cables	Page 20
Studio cables	Page 9	HDMI-DVI cables	Page 20
Headphone extension cables	Page 10	FireWire cables	Page 21
Microphone cables	Page 10	Mini DisplayPorts	Page 21
Y-cables	Page 10	Velcro straps	Page 21
Midi cables	Page 12	In General	Page 22
Insert cables	Page 12		

THE BRAND

Products that are sold under the name Rock-Cable® have become well established among musicians in the past 7 years since the brand was founded in 2004. Professional as well as semi-professional artists appreciate the outstanding product benefits and the excellent price-performance ratio, which we are able to offer and achieve thanks to optimum production efficiency.

The budget-friendly Rock-Cable® line comprises a rich assortment of audio products and cables for video applications and thus offers a professional alternative. Secondary noise reducing technologies such as "conductive plastic" and capacity-optimised materials are benefits which cannot be found with other products in this price range.





TIMBRES

The Rock-Cable® Audio Line comprises a rich assortment of products. The spectrum ranges from Y-splitters, adapter and MIDI cables to a number of audio cables for computer, guitar, bass, microphone and keyboard applications.

The Audio Line is a very cost-effective alternative to other professional product lines on the market. Secondary noise reducing technologies such as "conductive plastic" and capacity-optimised materials are benefits which cannot be found in other products in this price range. The audio cables are soldered by hand and assembled with REAN® connectors with metal housings. The connectors feature nickel or gold-plated contacts and moulded bushings which can be easily opened for service purposes.

* REAN (Made in China) is a registered Trademark of Neutrik AG.



	Instrument cables (guitar cables) Unbalanced cable assembled with 6.35 mm mono phone plugs with gold-plated contacts on both sides (ex RCIG*PP).	NRA-070-0030-003 NRA-070-0030-006 NRA-070-0030-009 NRA-070-0030-020 NRA-070-0030-050 NRA-070-0030-070 NRA-070-0030-100	30 cm 60 cm 90 cm 2 meters 5 meters 7 meters 10 meters	
7 3	Instrument cable (guitar cables) Unbalanced cable assembled with one 6.35 mm mono angled phone plug (nickel-plated contacts) to one 6.35 mm mono straight phone plug (gold-plated contacts), (ex RCIG*PPR).	NRA-070-0271-050 NRA-070-0271-070 NRA-070-0271-100	5 meters 7 meters 10 meters	
	Instrument extension cable Unbalanced cable assembled with one 6.35 mm phone plug to one 6.35 mm phone jack, both sides mono and with gold-plated contacts (ex RCST*PMJM).	NRA-070-0520-050 NRA-070-0520-070	5 meters 7 meters	
1	Patch cables Unbalanced cable assembled with 6.35 mm mono angled phone plugs with nickel-plated contacts on both sides (ex RCP*PP). Due to the 90°-angled connectors, the cable is lead away from the rack and thus solves space problems.	NRA-070-0041-000 NRA-070-0040-003 NRA-070-0040-006 NRA-070-0040-009	15 cm 30 cm 60 cm 90 cm	
4	Multicore cables The Rock-Cable® assortment comprises multicore cables with an excellent price-performance ratio. They all have strain-relief as well as anti-kink protection and they are assembled with a trapezoid stage box. The cables are supplied in a convenient Rock-Cable® gig bag (ex. RCMC*).			
	Assembled 12-way with a:Trapezoid box; b: 8 x XLR m & 4 x XLR f 12-way with a:Trapezoid box; b: 8 x XLR m & 4 x XLR f 16-way with a:Trapezoid box; b: 12 x XLR m & 4 x XLR f 16-way with a:Trapezoid box; b: 12 x XLR m & 4 x XLR f 20-way with a:Trapezoid box; b: 16 x XLR m & 4 x XLR f 28-way with a:Trapezoid box; b: 24 x XLR m & 4 x XLR f	NRA-070-0431-150 NRA-070-0431-300 NRA-070-0441-150 NRA-070-0441-300 NRA-070-0451-300 NRA-070-0471-300	15 meters 30 meters 15 meters 30 meters 30 meters	

The state of the s	Studio cables Balanced cable assembled with one XLR female connector (nickel-plated contacts) to one 6.35 mm stereo phone plug (gold-plated contacts), (ex RCST*FXPS).	NRA-070-0060-020 NRA-070-0060-050 NRA-070-0060-100	2 meters 5 meters 10 meters	
	Studio cables Balanced cable assembled with one XLR male connector (nickel-plated contacts) to one 6.35 mm stereo phone plug (gold-plated contacts), (ex RCST*MXPS).	NRA-070-0050-020 NRA-070-0050-050 NRA-070-0050-100	2 meters 5 meters 10 meters	
The state of the s	Studio cables Balanced cable assembled with 6.35 mm stereo phone plugs with gold-plated contacts on both sides (ex RCST*PPS).	NRA-070-0010-006 NRA-070-0010-009 NRA-070-0010-020 NRA-070-0010-050	60 cm 90 cm 2 meters 5 meters	
	Studio cables Unbalanced cable assembled with one XLR female connector (nickel-plated contacts) to one 6.35 mm mono phone plug (gold-plated contacts), (ex RCST*FXPM).	NRA-070-0420-020 NRA-070-0420-050 NRA-070-0420-070	2 meters 5 meters 7 meters	
	Studio cables Unbalanced cable assembled with one XLR male connector (nickel-plated contacts) to one 6.35 mm mono phone plug (gold-plated contacts), (ex RCST*MXPM).	NRA-070-0490-020 NRA-070-0490-050 NRA-070-0490-070	2 meters 5 meters 7 meters	
	Studio cables Balanced cable assembled with 3.5 mm stereo mini plugs with gold-plated contacts on both sides (ex RCST*MPMP).	NRA-070-0020-006 NRA-070-0020-009 NRA-070-0020-020 NRA-070-0020-030 NRA-070-0020-050	60 cm 90 cm 2 meters 3 meters 5 meters	

	Microphone cables Balanced microphone cable assembled with one XLR female connector to one XLR male connector, both with nickel-plated contacts (ex RCM*MXFX).	NRA-070-0260-020 NRA-070-0260-050 NRA-070-0260-070 NRA-070-0260-100	2 meters 5 meters 7 meters 10 meters	
Sec.	Headphone extension cables Balanced cable assembled with one 3.5 mm mini plug to one 3.5 mm mini jack, both with gold-plated contacts (ex RCST*MPMJ).	NRA-070-0750-030 NRA-070-0750-050	3 meters 5 meters	
	Headphone extensions Balanced cable assembled with one 6.35 mm phone plug to one 6.35 mm phone jack, both sides stereo and with gold-plated contacts (ex RCST*PJS).	NRA-070-0510-020 NRA-070-0510-050 NRA-070-0510-070 NRA-070-0510-100	2 meters 5 meters 7 meters 10 meters	
	Y-cable Y-cable assembled with one 6.35 mm mono phone jack to 2x phono plugs (RCA), all with gold-plated contacts.	NRA-070-0590-003	30 cm	
	Y-cable Y-cable assembled with one XLR female connector to 2x XLR male connectors, all with nickel-plated contacts (ex RCY03FXMXMX).	NRA-070-0640-003	30 cm	
The state of the s	Y-cable Y-cable assembled with one 6.35 mm mono phone plug to 2x male phono connectors (RCA), all with gold-plated contacts (ex RCYO3PMC).	NRA-070-0560-003	30 cm	

Y-cable Y-cable assembled with one phono jack to 2x phono plugs (RCA), all with gold-plated contacts (ex RCY03FCC).	NRA-070-0610-003	30 cm	
Y-cable Y-cable assembled with one phono plug (RCA) to 2x phono jacks, all with gold-plated contacts (ex RCY03CFC).	NRA-070-0620-003	30 cm	
Y-cable Y-cable assembled with one 6.35 mm mono phone jack to 2x phono jacks (RCA), all with gold-plated contacts (ex RCY03JMFC).	NRA-070-0600-003	30 cm	
Y-cable Y-cable assembled with one 6.35 mm phone jack to 2x 6.35 mm phone plugs, both sides mono and with gold-plated contacts (ex RCY03JMP).	NRA-070-0580-003	30 cm	
Y-cable Y-cable assembled with one 6.35 mm mono phone plug to 2x female phono connectors, all with gold-plated contacts (ex RCY03PMFC).	NRA-070-0570-003	30 cm	
Y-cable Y-cable assembled with one 6.35 mm phone plug to 2x 6.35 mm phone jacks, both sides mono and with gold-plated contacts (ex RCY03PMJMJM).	NRA-070-0550-003	30 cm	

	Y-cables Y-cable assembled with one 6.35 mm phone plug to 2x 6.35 mm phone plugs, both sides mono and with gold-plated contacts (ex RCYo3PMP).	NRA-070-0540-003	30 cm	
	Y-cables Y-cable assembled with one 6.35 mm phone plug to 2x 6.35 mm phone jacks, both sides stereo and with gold-plated contacts (ex RCYO3PSJSJS).	NRA-070-0630-003	30 cm	
	Midi-Kabel 5-pole midi cable (3-pole connected), assembled with REAN connectors on both sides (ex RCMI*). These 5-pole REAN® connectors are manually soldered.	NRA-070-0070-009 NRA-070-0070-020 NRA-070-0070-050 NRA-070-0070-070 NRA-070-0070-100	90 cm 2 meters 5 meters 7 meters 10 meters	
A STATE OF THE PARTY OF THE PAR	Insert cables Insert cable assembled with one 6.35 mm stereo phone plug (gold-plated contacts) to one XLR male connector and one XLR female connector (both with nickel-plated contacts), (ex RCIN*PSMXFX).	NRA-070-0120-006 NRA-070-0120-020 NRA-070-0120-050	60 cm 2 meters 5 meters	
A STATE OF THE PARTY OF THE PAR	Insert cables Insert cable assembled with one 6.35 mm stereo phone plug to 2x 6.35 mm mono phone plugs, all with gold-plated contacts (ex RCIN*PSP).	NRA-070-0160-010 NRA-070-0160-020 NRA-070-0160-050	1 meter 2 meters 5 meters	
	Stereo cables Stereo cable assembled with one 6.35 mm stereo phone plug to 2x phono plugs (RCA), all with gold-plated contacts (ex RCIN*PSC).	NRA-070-0180-020 NRA-070-0180-050	2 meters 5 meters	

Stereo cables Cable assembled with 2x phono plugs (RCA) to 2x 6.35 mm mono phone plugs, all with gold-plated contacts, (ex RCSI*CP).	NRA-070-0090-006 NRA-070-0090-010 NRA-070-0090-020 NRA-070-0090-050	60 cm 1 meter 2 meters 5 meters	
Stereo cables Cable assembled with 2x XLR female cable connectors (nickel-plated contacts) to 2x phono plugs (gold-plated contacts), (ex RCSI*FXC).	NRA-070-0100-006 NRA-070-0100-010 NRA-070-0100-020 NRA-070-0100-050	60 cm 1 meter 2 meters 5 meters	
Stereo cables Stereo adapter cable assembled with 2x XLR male cable connectors (nickel-plated contacts) to 2x phono plugs (gold-plated contacts), (ex RCSI*MXC).	NRA-070-0110-006 NRA-070-0110-010 NRA-070-0110-020 NRA-070-0110-050	60 cm 1 meter 2 meters 5 meters	
Stereo cables Stereo adapter cable assembled with one 6.35 mm stereo phone jack to 2x 6.35 mm mono phone plugs, all with gold-plated contacts, (ex RCY*JSP).	NRA-070-0670-003	30 cm	
Stereo cables Stereo adapter cable assembled with one 3.5 mm stereo mini jack to 2x phono plugs (RCA), all with gold-plated contacts, (ex RCY03MJFC).	NRA-070-0680-000 NRA-070-0680-003	15 cm 30 cm	
Stereo cables Stereo adapter cable assembled with one 3.5 mm mini plug to 2x phono plugs, all with gold-plated contacts (ex RCIN*MPC).	NRA-070-0150-010 NRA-070-0150-020 NRA-070-0150-030 NRA-070-0150-050	1 meter 2 meters 3 meters 5 meters	


To the same of the	Stereo cables Stereo adapter cable assembled with one 3.5 mm stereo mini plug to 2x 6.35 mono phone plugs, all with gold-plated contacts (ex RCIN*MPP).	NRA-070-0170-020 NRA-070-0170-050	2 meters 5 meters	
	Stereo cables Stereo adapter cable assembled with one 3.5 mm mini plug (gold-plated contacts) to 2x XLR female connectors (nickel-plated contacts), (ex RCIN*MPFX).	NRA-070-0140-006 NRA-070-0140-020 NRA-070-0140-050	60 cm 2 meters 5 meters	
	Stereo cables Stereo adapter cable assembled with one 3.5 mm mini plug (gold-plated contacts) to 2x XLR male connectors (nickel-plated contacts), (ex RCIN*MPMX).	NRA-070-0130-006 NRA-070-0130-020 NRA-070-0130-050	60 cm 2 meters 5 meters	
The state of the s	Stereo cables Stereo adapter cable assembled with one 6.35 mm stereo phone plug to 2x phono jacks (RCA), all with gold-plated contacts (ex RCY03PSFC).	NRA-070-0660-003	30 cm	
	Stereo cables Stereo adapter cable assembled with one 3.5 mm stereo mini jack to 2x phono jacks (RCA), all with gold-plated contacts.	NRA-070-0690-000	15 cm	
	Stereo cables Stereo adapter cable assembled with one 3.5 mm stereo mini plug to 2x phono jacks, all with gold-plated contacts.	NRA-070-0157-000	15 cm	

A CONTRACTOR OF THE PARTY OF TH	Stereo cables Stereo cable assembled with 2x phono plugs (RCA) on each side, with gold-plated contacts (ex RCC*CC).	NRA-070-0080-006 NRA-070-0080-010 NRA-070-0080-020 NRA-070-0080-030 NRA-070-0080-050	60 cm 1 meter 2 meters 3 meters 5 meters	
A ROBERT OF THE PARTY OF THE PA	Stereo cables Siam cable assembled with 2x 6.35 mm phone plugs to 2x 6.35 mm phone plugs, both sides mono and with gold-plated contacts (ex RCSI*PP).	NRA-070-0720-010 NRA-070-0720-020 NRA-070-0720-050	1 meter 2 meters 5 meters	
	Stereo cables Stereo cable assembled with one 6.35 mm stereo phone plug to 2x 6.35 mm mono phone jacks, all with gold-plated contacts (ex RCYO3PSJMJM).	NRA-070-0650-003	30 cm	
	Stereo cables Stereo adapter cable assembled with one 3.5 mm stereo mini plug to 2x 6.35 mm mono phone jacks (ex RCY*MPJMJM).	NRA-070-0530-003	30 cm	
	Stereo cables Stereo cable assembled with 2x phono plugs to 2x phono jacks, all with gold-plated contacts (ex RCC*CFC).	NRA-070-0760-050	5 meters	
	Toslink cables Black Toslink cable, assembled with Toslink connectors with gold-plated contacts on both sides, and with PVC jacket and black chromed metal housings.	NRV-070-010-010 NRV-070-010-020 NRV-070-010-030 NRV-070-010-050 NRV-070-010-100	1 meter 2 meters 3 meters 5 meters 10 meters	



VIDEO LINE A FEAST FOR THE






A FEAST FOR THE EYES

Due to increased demand for low-budget video and data cables, we launched a video product line. The Rock-Cable® Video Line is in no way inferior to the Audio Line: It comprises cables with tried-and-tested standards to very attractive, cost-effective conditions.

The range includes analogue VGA and VGA audio cables in different lengths, HDMI and HDMI-DVI cables as well as mini DisplayPorts which are increasingly coming into focus. Just like the audio cables, the video cables are soldered by hand.



HDMI-DVI cables Black cable with PVC jacket, assembled with one HDMI male connector to one DVI-D female connector (DVI-D single-link), both with gold-plated contacts.	NRV-070-080-001 NRV-070-080-005	10 cm 50 cm	
Analogue VGA cables with audio Black VGA cable with PVC jacket, assembled with one 15-pole VGA male connector with screw terminals to one 3.5 mm stereo mini plug, both with gold-plated contacts.	NRV-070-050-010 NRV-070-050-025 NRV-070-050-050 NRV-070-050-075 NRV-070-050-100	1 meter 2.5 meters 5 meters 7.5 meters 10 meters	
HDMI flat cables 1.4 Black HDMI 1.4 flat ribbon cable with PVC jacket, assembled with black/white HDMI male connectors with gold-plated contacts. The cable has a width of 12.5 mm.	NRV-070-060-005 NRV-070-060-010 NRV-070-060-020 NRV-070-060-030 NRV-070-060-050	50 cm 1 meter 2 meters 3 meters 5 meters	
HDMI cables Black HDMI 1.4 cable with PVC jacket, assembled with black/blue HDMI male connectors with gold-plated contacts on both sides.	NRV-070-090-005 NRV-070-090-0075 NRV-070-090-010 NRV-070-090-020 NRV-070-090-030 NRV-070-090-050 NRV-070-090-100	50 cm 75 cm 1 meter 2 meters 3 meters 5 meters	
HDMI-A-C cables 1.4 Black high-speed HDMI cable, assembled with one HDMI male connector type A and one HDMI male connector type C, both with nickel-plated contacts.	NRV-070-100-005 NRV-070-100-010 NRV-070-100-015 NRV-070-100-020	50 cm 1 meter 1.5 meters 2 meters	
HDMI-DVI cables Black cable with PVC jacket, assembled with one HDMI male connector to one DVI male connector (DVI-D single-link), both with gold-plated contacts.	NRV-070-070-005 NRV-070-070-0075 NRV-070-070-010 NRV-070-070-020 NRV-070-070-030 NRV-070-070-050 NRV-070-070-100	50 cm 75 cm 1 meter 2 meters 3 meters 5 meters 10 meters	

	FireWire cables 4/4 Black, 4-pole FireWire adapter cable with black PVC jacket, ferrit core and gold-plated contacts, with 4 wires solely responsible for data transmission. Cable according to IEEE 1394.	NRV-070-020-015 NRV-070-020-025 NRV-070-020-050	1.5 meters 2.5 meters 5 meters	
	FireWire cables 4/6 Black, 6-pole FireWire adapter cable with PVC jacket, ferrit core and gold-plated contacts, with 4 wires for data transmission and 2 wires for power supply. The data transmission is bi-directional. Cable according to IEEE 1394.	NRV-070-030-015 NRV-070-030-025 NRV-070-030-050	1.5 meters 2.5 meters 5 meters	
	Mini DisplayPort White adapter cable with one Mini DisplayPort to one HDMI female receptacle.	NRV-070-110-0015	15 cm	
	Mini DisplayPort White adapter cable with one Mini DisplayPort to one DVI-D female single-link.	NRV-070-120-0015	15 cm	
	Mini DisplayPort Mini DisplayPort to one VGA female receptacle.	NRV-070-130-0015	15 cm	
	Rock-Cable velctro strap Black, 5 mm wide Velcro® strap, available on reels of 100 m. The fastener is delivered in a PE bag and can simply be cut with scissors to the desired length. Ideal for neat cable management and for various packaging options.	NRA-070-0003-000	100 meters	

IN GENERAL

Damages

Damages caused by interferences and resulting modifications of the products are excluded from liability. Damages due to improper handling and consequential damages are also not covered.

Quality features

All audio cables by Rock-Cable® are soldered by hand and assembled with REAN® connectors with metal housings. The connectors feature nickel- or gold-plated contacts and moulded bushings which can be easily opened for service purposes. Rock-cable® products fulfil all necessary requirements and are available at attractive prices thanks to excellent production efficiency.

Technical information

Technical changes by the manufacturer are possible and can be implemented without prior notice. Technical data and drawings are non-binding and provided for information purposes only. According to official safety regulations regarding the use of electronic devices, all components requiring testing that do not bear the SEV identification label – even if they bear a similar label – may only be used in the voltage range of up to 50 V AG or 72 V DC.

NOTES

