









# Knives & Blades




## Knives

	Order no.	Description	Size	
			Inch	mm
	<b>XN100</b>	Knife, Light duty for soft material	5 13/16	148
	<b>XN200</b>	Knife, Medium duty for hard material	5 3/4	146
	<b>XN210</b>	Knife, Heavy duty plastic handle for coars jobs	5 7/16	137
	<b>XNS100</b>	Light and medium duty knife set. Contains 10 assorted blades: XN100, XN200, XNB103 (2 pcs.), XNB105 (2 pcs.), XNB101, XNB203, XNB205 (2 pcs.), XNB201		

## Blades for XN100

	Order No.	Description	Pack quantity
	<b>XNB101</b>	Blade, Standard	5
	<b>XNB103</b>	Blade, Fine pointed	5
	<b>XNB103B</b>	Blade, Fine pointed	100
	<b>XNB105</b>	Blade, Stencil	5

## Blades for XN200 and XN210

	Order No.	Description	Pack quantity
	<b>XNB201</b>	Blade, Chisel	5
	<b>XNB203</b>	Blade, General purpose	5
	<b>XNB205</b>	Blade, Pointed	5

# Shear cutters and pliers

## Shear cutter - general purpose

- Low profile, general-purpose cutter
- Superior blade by-pass shear cutting action
- Greatly reduced mechanical shock delivered to the work
- ESD safe
- Soft grips and feature safety clips
- Flush cuts soft wire up to 20 AWG (0.8 mm)



Order no.	Description	Size	
		Inch	mm
<b>170MN</b>	Shearcutter - General purpose, 127 mm (5 Inch)	5	127
<b>175MN</b>	Shearcutter with safety clips, soft handles	5	127

## Sheet metal Snip



Order no.	Description	Size	
		Inch	mm
<b>86NCG</b>	Snip, electronic	6.5	165

## Wire Stripper & Cutters

- Adjustable for different wire strengths



Order no.	Description	Size	
		Inch	mm
<b>100XV</b>	Wire Stripper & Cutter, adjustable	5	127
<b>101SNV</b>	Wire Stripper & Cutter, spring-opening	5	127