

Fluke laser levels Rugged, precision tools for efficient layout

Built with the ruggedness you expect from Fluke. Tested to survive a one meter drop. Accurate to 6 mm at 30 meters (3-point lasers), to 3 mm at 10 meters (2-line lasers). Fast settling, self-leveling gimbal gives you accurate marks almost instantly

Product summary All laser level models

Rugged design withstands rough handling on the job site; drop tested at 1 meter.

Includes magnetic wall bracket for easy, stable mounting.

Fluke-3PR and Fluke-3PG

- Self-leveling 3 point laser level allows for fast, accurate layout of reference points
- Accurate to 6 mm at 30 meters (1/4 inch at 100 feet)
- Includes floor stand for fast, easy overhang and centerline measurements
- Green laser is up to 3 times brighter for improved visibility and long range applications (Fluke-3PG only)

Fluke-180LR and Fluke-180LG

- Self-leveling, horizontal- and vertical-cross line laser level for rapid, accurate leveling and layout
- Accurate to 3 mm at 10 meters (1/8 inch at 30 feet)
- Green laser for improved visibility. Up to 3 times brighter, and suited for long range applications (Fluke-180LG only)

Fluke-LDR and Fluke-LDG Laser Line Detectors

- Laser line detector for use in high ambient light settings
- Visual and audible indicators for ease of use
- Rugged design
- Compatible with Fluke-180LR (Fluke-LDR) or Fluke-180LG (Fluke-LDG)
- Includes mounting bracket for quick, steady positioning

Fluke-180LR System and Fluke-180LG System

- Self-leveling, horizontal- and vertical-cross line laser level
- Includes laser line detector and detector bracket for use in high ambient light settings





Specifications



		3PR, 3PG	180LR, 180LG	LDR, LDG
Light source		Semiconductor laser diode		NA
Leveling range		≤6 °		NA
Leveling		Automatic		
Working range		≤30 m	≤60 m	≤60 m
Detection height		NA		≤50 mm
Accuracy		≤6 mm @ 30 m	≤3 mm @ 9 m	Fine: 0.75 mm
				Medium: 1.75 mm
Batteries		3 x AA Alkaline IEC LR6		1 x 9 V Alkaline IEC LR61
Battery life	Red	≥30 hrs, continuous use	≥35 hrs, continuous use with single beam	≥30 hrs, continuous use
	Green	10 hrs to 12 hrs, continuous use	2 hrs to 6 hrs, continuous use with single beam	
Dimensions (H x W x L)		140 mm x 102 mm x 57 mm	93 mm x 61 mm x 93 mm	94 mm x 94 mm x 42 mm
Weight (with batteries)		0.52 kg	0.50 kg	0.20 kg
Warranty		3 years		
Laser		IEC 60825-1: Class 3R		
Max output power		<5 mW		NA
Wavelength		Red: 635 nm Green: 510 nm		



©2016 Fluke Corporation. Specifications subject to change without notice. 9/2016 6008417a-en Modification of this document is not permitted without written permission from Fluke Corporation.