

Prototyping Boards Dual Inline



RE060-HP

- SRBP paper FR2 1.5 mm single-sided 35 µm CU
- organic soldering protection (OSP)

- 37 x 56 single-hole conductor 2.10 mm Ø
- Hole spacing 2.54 x 2.54 mm
- Hole dia 1.00 mm
- Connector 32/64/96 - channel DIN 41612 type C
- size 100 x 160 mm