

LIFT High-tech in motion

LIFT is the totally practical combination of sophisticated looks and high-precision mechanical design. The unit is recessed neatly in the top of the desk or table when not in use. Simply touch to raise out of the desk or table and it's ready for docking on all four sides. Once you have finished using the connections, simply push it back into its initial recessed position by hand.

The benefits at a glance

- · Simply touch to raise
- · Design that can't fail to impress
- $\boldsymbol{\cdot}$ Access points on four sides
- · Incredibly compact dimensions
- · Low built-in depth
- · 4 plug-in units on one height unit

LIFT can be supplied in a variety of power and data connection configurations. This highly compact unit needs a drill hole only 140 mm in diameter for installation. Built-in depth both open and closed is just 195 mm.

By setting cutting-edge technology in motion, LIFT makes power and data supply a truly enjoyable experience.







Simply touch to raise and lower LIFT. The unit has connection points on four sides and can be equipped with a variety of power and data connection configurations.



Enclosure colour BLACK

Version Art. no.

LIFT: Power socket outlets

Enclosure colour black; power input: 0.5 m cable and GST18i3 plug

	\cdot 4 x socket outlet with earthing contact, shuttered, black, set at 35°
904.004	· 4 x French / UTE socket outlet, shuttered, black, set at 35°

904.024* · 4 x Swiss / CH socket outlet, black, set at 0°

904.020* \cdot 4 x UK 3.15 A individually fused, shuttered, black, set at 90 $^{\circ}$

LIFT: 2 x CAT6 + power socket outlets

Enclosure colour black, power input. 3.0 m cable and plug, 3.0 m data cable and RJ45 plug		lour black, power input. 3.0 m cable and plug, 3.0 m data cable and h545 plug
		· 3 x socket outlet with earthing contact, shuttered, black, set at 35°
	904.005	· 3 x French / UTE socket outlet, shuttered, black, set at 35°
100	004.005*	Ov. Curing / Old analyst author blook and at 00

+	904.025*	· 3 x Swiss / CH socket outlet, black, set at 0°
	904.021*	· 3 x UK 3.15 A individually fused, shuttered, black, set at 90°

LIFT: 2 x CAT6, 1 x VGA + miniature jack + power socket outlets

Enclosure colour black; power input: 3.0 m cable and plug; CAT6 3.0 m data cable and RJ45 plug; VGA 15-pole and miniature jack with 3.0 m cable and plug

		· 2 x socket outlet with earthing contact, shuttered, black, set at 35°
	904.006	· 2 x French / UTE socket outlet, shuttered, black, set at 35°
4	004 026*	· 2 v Swigs / CH socket outlet, black, set at 0°

	· 2 x Swiss / CH socket outlet, black, set at 0°
904.022*	· 2 x UK 3.15 A individually fused, shuttered, black, set at 90°

LIFT: 2 x CAT6, 2 x USB + power socket outlets

Enclosure colour black; power input: 3.0 m cable and plug;

CAT6 3.0 m data cable and RJ45 plug; USB A socket with 3.0 m cable and plug

	· 2 x socket outlet with earthing contact, shuttered, black, set at 35°
904.007	· 2 x French / UTE socket outlet, shuttered, black, set at 35°

 \cdot 2 x Swiss / CH socket outlet, black, set at 0° 904.027* 904.023* · 2 x UK 3.15 A individually fused, shuttered, black, set at 90°

LIFT: 2 x CAT 6, 1 x VGA + miniature jack , 1 x HDMI, power socket outlet

Enclosure colour black; power input: 3.0 m cable and plug



- · 2 x CAT6 RJ45 with 3.0 m data cable and RJ45 plug
- · 1 x VGA + miniature jack each with 3.0 m cable
- · 1 x HDMI with 3.0 m cable

U LIFT: 1 x USB double charger (5.2 V/2.15 A), 2 x CAT6 + power socket outlets

Enclosure colour black; power input: 3.0 m cable and plug; 3.0 m data cable and RJ45 plug



· 2 x CAT6 RJ45 socket



Enclosure colour SILVER

Art. no. Version

LIFT: Power socket outlets

Enclosure colour silver; power input: 0.5 m cable and GST18i3 plug

904.008

· 4 x socket outlet with earthing contact, shuttered, black, set at 35°





LIFT: 2 x CAT6 + power socket outlets

Enclosure colour silver; power input: 3.0 m cable and plug; 3.0 m data cable and RJ45 plug

904.009 · 3 x socket outlet with earthing contact, shuttered, black, set at 35°



LIFT: 2 x CAT6, 1 x VGA + miniature jack + power socket outlets

Enclosure colour silver; power input: 3.0 m cable and plug;

CAT6 3.0 m data cable and RJ45 plug; VGA 15-pole and miniature jack with 3.0 m cable and plug

010 · 2 x socket outlet with earthing contact, shuttered, black, set at 35°



LIFT: 2 x CAT6, 2 x USB + power socket outlets

Enclosure colour silver; power input: 3.0 m cable and plug;

CAT6 3.0 m data cable and RJ45 plug; USB A socket with 3.0 m cable and plug

904.011 · 2 x socket outlet with earthing contact, shuttered, black, set at 35°



Hole saw Ø 140 mm

For Lift installation

904.900 · Hole saw for clamping, with centre drill

· 140 mm diameter



Similar to illustration

Mounting tool for hole saw

918.900 · with centre drill



Similar to illustration