

Approvals

Last updated 2011-03-28



Types	DEMKO	FIMKO	NEMKO	SEMKO	INTERTEK	UL-Canada
HE1	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE1N	315036-01	FI25173	P09211004	904958	EN60998-2-1	
HE1H	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE2L	315036-01	FI25173	P09211004	904958	EN60998-2-1	
HE2N	315036-01	FI25173	P09211004	904958	EN60998-2-1	
HE2HN	315036-01	FI25173	P09211004	904958	EN60998-2-1	
HE4	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE4HN	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE4EH	315036-01	FI25173	P09211004	904958	EN60998-2-1	
HE6	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE6H	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE6N	315036-01	FI25173	P09211004	904958	EN60998-2-1	
HE10	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE10H	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE16	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE16H	315036-01	FI25173	P09211004	904958	EN60998-2-1	E 211022
HE25	314989-02	FI25067A1	P09210798/A1	907407	EN60998-2-1 *	
HE1101	315597-01	FI26522	P10213577	1014562	EN60998-2-1	
HE164	315588-1	FI26524	P10213578	1014564	EN60998-2-1	
HE122				9814132/01-02		
HE123				9814132/01-02		
HE251	312173-01	FI 19594	P03100522	302128	EN60998-2-1	
HE252	315600-01	FI 26523	P10213579	1014563	EN60998-2-1	
HE253	D-00052	263608	P06205937	1100605	EN60998-2-1	
HE254	315001-01	FI25123	P09210880	906433	EN60998-2-1 *	
HE34	315032-01	FI25065A1	P09210799/A1	907410	EN60998-2-1	
HE42 ST						E 211022
HE42S ST						E 211022
HE2 BU						E 211022
HE2S BU						E 211022

EN60998-2-1 * = EN60998-2-1 + EN 60335-1 (750°C in < 2 sec for domestic applications July2006.)