



NOTE:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 300V 10M Ω;
 - Contact resistance:3 Ω Max;
 - Dielectric strength:100V AC/Minute, 1mA.
- ROHS2.0 AND REACH COMPLIANT
- PRINTING:AWM STYLE 2725 80 °C 30V USB 2.0 High Speed Cable
- Current Rate:500mA max
- Voltage:5V DC
- Data Transfer: 480Mbps
- Operating Temperature:0°C~45°C
Storage Temperature:-20°C~ 70°C

ITEM NO.	LENGTH
11.02.8336	1800 ± 30mm
11.02.8337	3000 ± 50mm
11.02.8338	4500 ± 70mm

DESC.	ROLINE USB2.0 Cable C-B, M/M
-------	------------------------------

MATERIAL LIST:

④	OUTER MOLD	Shore 88A PVC COLOUR: BLACK	2	
③	USB B TYPE	USB B /M Type, The Pin Gold Plating, the shell for Nickel Plating	1	
②	USB C TYPE	USB C /M Type, The Pin Gold Plating, the shell for Nickel Plating	1	
①	CABLE	USB 2.0 28AWG BC*1P+28AWG BC*2C+AEB JACKET:PVC/BLACK OD4.0±0.2MM	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK

		NEW	2022-12-20	A
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.

SECOMP