


ITEM	PART#	DESCRIPTION	QTY	UOM
A	5024390200	2.0 W/B Single Plug Hsg 2Ckt	1	PC
B	5024380000	2.0 W/B Single Plug Term W/Pt Chain	2	PC
C	--	WHITE PART ID LABEL	1	PC

FROM	TO	DESCRIPTION	COLOUR
A1	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A2	--	1X22AWG DISC SR-PVC BK UL10002	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2219591020	Clik-Mate 2.0 R-S 2ckt 50mm disc Sn	50±5	15
2219591021	Clik-Mate 2.0 R-S 2ckt 100mm disc Sn	100±5	15
2219591022	Clik-Mate 2.0 R-S 2ckt 150mm disc Sn	150±5	15
2219591023	Clik-Mate 2.0 R-S 2ckt 300mm disc Sn	300±5	15
2219591024	Clik-Mate 2.0 R-S 2ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR

DETAIL A

NOTES

- CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
- CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
- LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
- LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
- TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
- FREE ENDS MUST BE STRIPPED, TWISTED & TINNED.
- THE LENGTH OF TINNING IS 5±1 MM. TINNING DIA MUST BE 0.9MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2022/02/12	A	INITIAL RELEASE	THANUB

DOCUMENT STATUS	P1	RELEASE DATE	2022/12/23	12:42:18
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
$\frac{F}{A} = 0$	DIMENSION UNITS	SCALE	CURRENT REV DESC:		
$\frac{E}{E} = 0$	mm	NTS	EC NO: 732309		
$\frac{P}{P} = 0$	GENERAL TOLERANCES (UNLESS SPECIFIED)		DRWN: THANUB 2022/12/02		
DIVISIONAL SYMBOLS	ANGULAR TOL	± °	CHK'D: SKUMAR07 2022/12/23		
	4 PLACES	±	APPR: SKUMAR07 2022/12/23		
	3 PLACES	±	INITIAL REVISION:		
	2 PLACES	±	DRWN: THANUB 2022/12/02		
	1 PLACE	±	APPR: SKUMAR07 2022/12/23		
	0 PLACES	±	DOCUMENT NUMBER		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION	DRAWING	SERIES
				A4-SIZE	221959
			MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			2219591020	GENERAL MARKET	1 OF 1