


ITEM	PART#	DESCRIPTION	QTY	UOM
A	5024391000	2.0 W/B Single Plug Hsg 10Ckt	1	PC
B	5024380000	2.0 W/B Single Plug Term W/Pit Chain	10	PC
C	---	WHITE PART ID LABEL	1	PC

FROM	TO	DESCRIPTION	COLOUR
A1	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A2	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A3	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A4	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A5	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A6	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A7	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A8	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A9	--	1X22AWG DISC SR-PVC BK UL10002	BLACK
A10	--	1X22AWG DISC SR-PVC BK UL10002	BLACK



PART NUMBER	TITLE	L1	L2(REF)
2219591100	Clik-Mate 2.0 R-S 10ckt 50mm disc Sn	50±5	15
2219591101	Clik-Mate 2.0 R-S 10ckt 100mm disc Sn	100±5	15
2219591102	Clik-Mate 2.0 R-S 10ckt 150mm disc Sn	150±5	15
2219591103	Clik-Mate 2.0 R-S 10ckt 300mm disc Sn	300±5	15
2219591104	Clik-Mate 2.0 R-S 10ckt 600mm disc Sn	600±5	15

MOLEX P/N
MOLEX
BATCH WK/YR
DETAIL A

- NOTES
- CABLE ASSEMBLY TO BE TESTED 100% FOR CONTINUITY AND POLARITY.
 - CONNECTOR VIEW SHOWN IS FROM MATING SIDE.
 - LABEL TEXT MUST BE 2 MM MAX. IN HEIGHT WITH ARIAL FONT.
 - LABEL MUST BE WRAPPED IN FLAG TYPE ON A SINGLE CABLE.
 - TINNING SHOULD BE DONE WITH LEAD FREE SOLDER BAR ONLY.
 - FREE ENDS MUST BE STRIPPED, TWISTED & TINNED. THE LENGTH OF TINNING IS 5±1 MM. TINNING DIA MUST BE 0.9MM MAX.

REVISION			
DATE	REV	DESCRIPTION	CHANGER
2022/02/12	A	INITIAL RELEASE	THANUB

DOCUMENT STATUS	P1	RELEASE DATE	2022/12/23	12:42:19
-----------------	----	--------------	------------	----------

FUNCTIONAL SYMBOLS $\frac{E}{A} = 0$ $\frac{E}{E} = 0$ $\frac{E}{P} = 0$ DIVISIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC:		<p>SEE TABLE</p> <p>PRODUCT CUSTOMER DRAWING</p>		
	DIMENSION UNITS	SCALE	EC NO: 732309				
	mm	NTS	DRWN: PRAVES6 2022/12/02				
	GENERAL TOLERANCES (UNLESS SPECIFIED)		CHK'D: SKUMAR07 2022/12/23				
ANGULAR TOL ± °		APPR: SKUMAR07 2022/12/23		DOCUMENT NUMBER	DOC TYPE	DOC PART	REVISION
4 PLACES ±		INITIAL REVISION:		2219591100	PSD	000	A
3 PLACES ±		DRWN: PRAVES6 2022/12/02					
2 PLACES ±		APPR: SKUMAR07 2022/12/23					
1 PLACE ±		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					
0 PLACES ±		THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER	CUSTOMER	SHEET NUMBER
			A4-SIZE	221959	SEE TABLE	GENERAL MARKET	1 OF 1