


REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
А		NEW RELEASE	TWC	TC	Ν.Ο.	9-22-05
В		UPDATED LED SPECS, ADDED R∘HS COMPLIANT NOTE, ADDED ESD NOTE AND SYMBOL.	KLJ	NO	MES	2-15-08
С		UPDATE LED INT (3.55 & 42) WAS (2.24 &37) FOR 5972301213F,202F	JTD	NO	MES	2-29-12



REEL SPROCKET HOLES—	
CATHODE MARKING—	\forall
	. 472
.315 — Smm PITCH	<u> </u>

BI-COLOR OPERATING CHARACTERISTICS AT TA = 25 °C AMBIENT															
DIALIGHT P/N	COLOR	FORWARD VOLTAGE (V) @ IF = 10 mA		LUMINOUS INTENSITY (mcd) @ IF = 2 mA		LUMINOUS INTENSITY (mcd) @ Ir = 10 mA		PEAK WAVELENGTH (nm)	DOMINANT WAVELENGTH (nm)		VIEWING ANGLE (2 9 1/2)				
		MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	MIN.	TYP.	MAX.	TYP.	MIN.	TYP.	MAX.	(
597-2001-213F, -202F	RED	1.7	1.8	2.2	4.5	7.8	11.2	20	40	60	643	624	630	636	120
597-2301-213F, -202F	GREEN	1.7	1.8	2.2	3.55	5.6	9.0	10	42	50	572	566	570	575	120
597-2401-213F, -202F	YELLOW	1.7	1.8	2.2	5.6	14.0	22.4	25	70	115	591	580	587	595	120

ABSOLUTE MAXIMUM RATINGS AT 25°C AMBIENT	UNITS	RED	GREEN	YELLOW
POWER DISSIPATION	mW	45	40	45
CONTINUOUS FORWARD CURRENT	mΑ	20		
PEAK FORWARD CURRENT tp < 10 μS, D=.005	mΑ	100		
REVERSE VOLTAGE @ 10 μA	٧	12		
SOLDERING TEMPERATURE, 10 SEC.	°C	260		
OPERATING TEMPERATURE	°C	-40 TO +100		
STORAGE TEMPERATURE	°C	- 4	0 TO + I	00

RoHS COMPLIANT 597-2X01-2XXF

Part Numbers with the "F" suffix ending are RoHS Compliant. For example: 597-2401-207F

Reel and bag packaging are marked with "RoHS Compliant" label or equivalent markings. These parts can be used with RoHS reflow profile. Parts can be wave soldered, dip soldered or hand soldered using typical lead-free soldering process with max 260°C temp. for 10 sec.



FSCM

83330

ATTENTION: **OBSERVE PRECAUTIONS FOR** HANDLING ELECTROSTATIC SENSITIVE DEVICES

| FAMILY TABLE:

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE

FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.								
SCALE: DRAWING SCALE	DRAWING NUMBER	REV						
ALL DIM'S IN: INCHES (MM)	C-17300	\cap						
TOLERANCES: UNLESS OTHERWISE SPECIFIED	C-11300							
FRACTIONS: ±1/64 DECIMALS (.XX): ±.01 DECIMALS (.XXX): ±.005	TITLE SMT-SIDELED RoHS COMPLIANT							
DECIMALS (.XXXX): ±.0005 ANGLES: ±1°	MATERIAL							
FINISH:	Dialiaht 1501 ROUTE	34 SOUTH						

SHEET