





TOLERANCE UNLESS OTHERWISE SPECIFIED	
.X	±0.15
.XX	±0.10


THIS IS A C.A.D. GENERATED DRAWING  
DO NOT MAKE MANUAL REVISIONS TO MASTER.



ISSUE NUMBER	
ORIGINAL	①
4 POS WAS 5 POS	
J.L.	SEPT.08/2022 ②



PCB LAYOUT  
LAYOUT TOLERANCE: ±0.05MM



**SPECIFICATION:**

CONTACT:	BRASS
PLATING:	GOLD FLASH PLATING ALL OVER
INSULATION:	PA46, COLOR BLACK
VOLTAGE RATING:	12V
CURRENT RATING:	2A MAX
INSULATION RESISTANCE:	100MEGA OHMS MIN
DIELECTRIC WITHSTAND VOLTAGE:	100V RMS AT 60HZ
CONTACT RESISTANCE:	30mOHM MAX. BEFORE TEST AND 60mOHM MAX. AFTER TEST
MECHANICAL LIFE:	30000 CYCLES MIN.
OPERATING TEMPERATURE RANGE:	-30°C~+85°C
SALT SPRAY TEST TIME:	48H



THIS SERIES FULLY CONFORMS TO  
THE EUROPEAN UNION DIRECTIVES  
2011/65/EU FOR RoHS COMPLIANCY.



YOUR CONNECTION TO QUALITY & SERVICE

EDAC INC  
TORONTO, ONTARIO  
CANADA

THESE DRAWINGS AND SPECIFICATIONS  
ARE THE PROPERTY OF EDAC INC., AND  
SHALL NOT BE REPRODUCED, OR COPIED  
OR USED AS THE BASIS FOR THE  
MANUFACTURE OR SALE OF APPARATUS  
WITHOUT WRITTEN PERMISSION.

**POGO CONNECTOR, 4 POS, FEMALE**

ACAD REFERENCE NO.: 686-0042231-121	
DRAWN: E.S	DATE: JUL.17/2022
CHECKED: R.S.M.	DATE: SEPT.08/2022
SCALE: (IN C.A.D. 1:1)	SHEET 1 OF 1
DRAWING NUMBER: 686-0042231-121	ISSUE
PART NUMBER: 686-0042231-121	2