

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NO WARRANTY, EXPRESSED OR IMPLIED. IS MADE BY	
PANDUIT WITH RESPECT TO ADHESIVE BOND PERFOMANCE.	
AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH	
THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE	
TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S	CONTROL.

1.00	
[25.4]	0.20
	[5.1]

PANDUIT	WEIGHT	USE WITH ANY OF		
PART	bs/100 pcs	THESE CABLE TIE		
NUMBER*	(g)/100 pcs	CROSS-SECTIONS		
ABM100-A	0.33 (150)	M, I, S SG100M, & SG1501		



ADHESIVE BACKING: RUBBER BASED ADHESIVE PRESSURE SENSITIVE FOAM TAPE 0.04 [1.0] THICK WITH A PROTECTIVE LINER. MOUNT IS DESIGNED TO SUPPORT 0.50 lbs (227g) MAX. WEIGHT ON A CLEAN DRY SMOOTH SURFACE.

## NOTES

- 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR
- PACKAGE SIZE AND COLOR.

  2. THE '-A' SUFFIX REPRESENTS RUBBER ADHESIVE.
- 3. SUPPLIED IN STRIPS OF TWO.
- 4. MOUNT HAS A MAXIMUM CONTINUOUS OPERATING
- TEMPERATURE OF 120°F (49°C).

  5. HOLE FOR STANDARD S6 FLAT HEAD SCREW.

[5.1]					DIMENSIONS IN BRACKETS ARE METRIC [ mm ]						
						G03597HJ_DC_G0033BA/06B					
						:			CORP. TINLEY PARK, ILLINOIS		
									ABM100-A FOUR-WAY MOUNT		
			200						DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)	MENSIONAL TOLERANCES ARE: (1	
6B	12-16-08	PSG.	AI.	REVISED DIMENSIONS AND WEIGHT	GB0033BA	6B	KLA		DRAWN BY MJK MAT'L: SCALE NO	NE	
6	8-24-05	TMSA		REMOVED PART NUMBER ABM25	GB0033BA	6			12/09/92 NY ON 6/6 DRAWING NO.	DWG	
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP	GBOC GBOC	)33BA A	