


REVISIONS					
ZONE	REV.	DESCRIPTION	DATE	E.C.O. NUMBER	ENGR
A7	A	DIELECTRIC TEST VOLTAGE REDUCED FROM 1,000 TO 500	1-9-14	2019453	



- ELEMENT: NON-INDUCTIVE PATTERN.
- RESISTANCE AT 0°C: 14.10 OHMS (15.51/12.69).
- TEMPERATURE LIMIT: -55°C TO 120°C AT ZERO POWER.
- DIELECTRIC STRENGTH: 500 VOLTS RMS AT 60 Hz FOR 1 MINUTE, ELEMENT TO OUTER SURFACES.
- LEADWIRE: AWG #30, STRANDED, TFE INSULATED PER MIL-W-16878/4.
- INSULATION: OPTICAL GRADE POLYESTER.
- DIMENSIONS PRECEDED BY * ARE CONTROLLED BY ENGINEERING DESIGN AND TOOLING.
- PART IS RoHS COMPLIANT.

APPLICABLE STANDARDS:
ASME Y14.5M-1994: DIMENSIONING AND TOLERANCING

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
DIMENSIONS IN [] ARE MILLIMETERS

ONE PLACE (.0) } ±.030
TWO PLACES (.00)
THREE PLACES (.000)

ANGLES: ±2°

APPROVALS	DATE
DR BN 1786	9-4-13
CHK HH 3841	10-3-13
ENGR TDV 2167	10/16/13
APR	
USED ON	

TITLE:
**THERMAL-CLEAR HEATER
MODEL H6987**

DRAWING NOT TO SCALE

DWG SIZE **B** THIRD ANGLE PROJECTION

MINCO
WWW.MINCO.COM

COMPANY CONFIDENTIAL
PROPRIETARY INFORMATION OF MINCO PRODUCTS, INC.
DO NOT DUPLICATE

DWG. NO. **H6987** REV. **A**

CAGE IDENT 09359 SHEET 1 OF 1