

SPECIFICATIONS:

- MATERIAL
HOUSING: POLYCARBONATE (PC),
CONTACT: PHOSPHOR BRONZE
FINE GOLD PLATED OVER NICKEL,
- MECHANICAL
CABLE TO PLUG TENSILE STRENGTH:
20lbs MINIMUM,
DURABILITY: 200 MATING CYCLES MIN,

- ELECTRICAL
UL APPLICATIONS: 250 VOLTS AC
MAX. AT 2 AMPS,
DIELECTRIC WITHSTANDING VOLTAGE:
500 VOLTS AC,
INSULATION RESISTANCE: 500 MEGOHMS,
TERMINATION RESISTANCE: 35 MILLIOHMS
MAX. AFTER ENVIRONMENTAL TESTING,

REACH
RoHS



UNLESS OTHERWISE SPECIFIED TOLERANCE : X.X ±0.3 X.XX ±0.15		ANGLES : ±2°		TITLE 8P8C		G00350			
DRAWN BY Bonnie		CHECKED BY Eric		APPROVED BY Mark		SIZE A4	UNIT mm	PART NO. -	REV. D
DWG NO. -		SCALE NA		THIRD ANGLE PROJECTION		PAGE 1 OF 2			
TOOLING NO. -		ITEM NO. 331-6386				DATE 2018-10-09			

Logo color: Red

Text Color: White

Background Color: Red

Background Color: White

Bar code & RoHS ,PE Loge ,Text color : Black

331-6386 100

8/8

Made In Taiwan

RoHS

PE XX/XX

REF 75

REF 55

数量

RS PN

產地

台灣製造 Made in Taiwan

條碼內容: 3316386

RS PN: 料號中的“-”不可輸入 (Code 128)

RoHS狀態

可回收材料標示

生產周期 (年/周)

XX/XX

Week周

Year年

331-6386 100

8/8


Made In Taiwan

RoHS

PE XX/XX

REACH

RoHS

UNLESS OTHERWISE SPECIFIED TOLERANCE :		ANGLES : ±2°		 榮昌科技股份有限公司 GRAND-TEK TECHNOLOGY CO., LTD.	
X.X ±0.3		X.XX ±0.15		DO NOT SCALE DRAWING	
DRAWN BY	Bonnie			TITLE 8P8C	
CHECKED BY	Eric			G00350	
APPROVED BY	Mark			SIZE A4	UNIT mm
DWG NO.	-			PART NO.	-
TOOLING NO.	-			SCALE NA	THIRD ANGLE PROJECTION
				ITEM NO.	331-6386
				PAGE	2 OF 2
				DATE	2018-10-09
				REV.	D