


ROHS-COMPLIANT

REV	DESCRIPTION	DATE
C	ROHS COMPLIANT EDIT PACKING, ADD BARCODE NO.	05/14/08'
D	ADD LENGTH, EDIT TEST	12/26/11'



NOTE:

- CABLE: UL-20276 [30AWG(7/0.10 T.C)x1P INS:FOAM-SKIN-PE + D.W(7/0.127 T.C) + AL/MY(SPREAD THE WRING)x4C + 28AWG(7/0.127 T.C)x1P INS:HD-PE + 30AWG(7/0.10 T.C)x3C INS:HD-PE + AL/MY + B.D(85%) PVC JACKET; OD:6.0±0.2mm COLOR:BLACK(NK-K01),(SPACE SHUTTLE).
- CONNECTOR:
 - P1: HDMI 19P MALE CONTACT:15u"; SHELL:NICKEL PLATED .
 - P2: DVI 18+1 DIGITAL MALE CONTACT:G/F,SHELL-NICKEL PLATED .
- SHIELD P1:INNER MOLD MUST BE WRAPPED COPPER 360° TO CONNECTOR SHELL & CABLE BRAID .
- HOOD:P1&P2:MOLDED TYPE,PVC 45P,COLOR:BLACK(NK-K01) .
- ELECTRICAL TEST:
 - (1)100% OPEN SHORT & MIS WIRE TEST .
 - (2)CONTACT RESISTANCE (SEE LIST) Max .
 - (3)INSULATION RESISTANCE 10M ohm Min .
- PACKING:EACH PC / POLY BAG + HEADER CARD(ROLINE,SIZE:205x84mm) + P/N LABEL.

Tolerance	Inch	M/M
X	.015	.30
XX	.010	.10
XXX	.005	.05
Draw		
FANNIE 12/26/11'		
Chek		
Engr		

P/N	L(mm)	T(mm)	PCS/CTN	BAR CODE NO.	CONTACT RESISTANCE
11.04.5519	1000	20	20	7611990198115	3Ω
11.04.5552	5000	50	10	7611990158300	5Ω
11.04.5532	3000	30	20	7611990158294	3Ω
11.04.5522	2000	30	20	7611990158287	3Ω

Rotronic Co., Ltd.


ROLINE DVI Cable, DVI M - HDMI M, 1m, black

Item No.: see the chart

Scale	NONE	Units	M/M	Third Angle Projection
REV:D	Sheet. 1/2			

REV	DESCRIPTION	DATE
C	ECC # 111226-5 EDIT PACKING, ADD, BARCODE NO.	05/14/08'
D	ECC # 111226-4 ADD LENGTH, EDIT TEST	12/26/11'

PIN OUT



Tolerance	Inch	M/M
X	.015	.30
XX	.010	.10
XXX	.005	.05
Draw		
FANNIE 12/26/11'		
Chek		
Engr		

Rotronic Co., Ltd.		
ROLINE DVI Cable, DVI M - HDMI M, 1m, black		
Item No.: see the chart		
Scale	NONE	Units
	M/M	
Third Angle Projection		REV:D
		Sheet. 2/2