


# ROHS-COMPLIANT

LTR	REV.	DESCRIPTION	DATE

DISPLAYPORT MALE  
INS:BLACK

DISPLAYPORT MALE  
INS:BLACK



**NOTE:**

1.CABLE: UL-20276 [#30(7/0.1 T.C)×1P INS:FOAM-PE+D.W(7/0.1 T.C)+AL/MY +Hot-melt Mylar]×5C + #30(7/0.1 T.C)×4C INS:Polyethylene+AL/MY+ B.D(85%) PVC JACKET; OD:6.5±0.2mm COLOR:MATT BLACK(NK-K01) .

**2.CONNECTOR:**

P1 & P2: DISPLAYPORT 20P MALE W/PCB & LATCH CONTACT:15u" SHELL:Ni-PLATED.

3.SHIELD:INNER MOLD MUST BE WRAPPED COPPER TO CONNECTOR SHELL & CABLE BRAID

4.HOOD:ASS'Y TYPE, PLASTIC HOOD COLOR:BLACK(NK-K01)

**5.ELECTRICAL TEST:**

- (1)100% OPEN SHORT & MIS WIRE TEST.
- (2)CONTACT RESISTANCE 3 ohm Max .
- (3)INSULATION RESISTANCE 10M ohm Min .
- (4)HI-POT DC300V

6.PACKING:EACH PC / POLY BAG + HEADER CARD + BAR CODE LABEL.

200-1161-3	11.04.5605	5000	50	10	7611990186280
200-1161-2	11.04.5603	3000	30	20	7611990186273
200-1161-1	11.04.5602	2000	30	20	7611990186266
DWG	P/N	L(mm)	T(mm)	PCS/CTN	BAR CODE NO.

Tolerance Inch M/M		
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05
Draw	FANNIE 01/14/09'	
Chek		
Engr		

**Rotronic co., LTD.**

Title  
DISPLAYPORT ASS'Y CABLE

Customer P/N

App'd Customer: T-RAG

Scale NONE Units M/M Third Angle Projection

Dwg No. 200-1161 REV:A Sheet.1/2