


9.2±0.3MM

2000±30mm




Conn.1 HDMI A Type Male Molding

Conn.2 HDMI A Type Female Molding

**ELECTRICAL TEST:**

- 1.100% OPEN & SHORT & MIS WIRE TEST
- 2.CONTACT RESISTANCE:2 OHM(MAX)
- 3.INSULATION RESISTANCE:10M OHM(MIN)
- 4.HI-POT TEST:DC 300V/10ms

**Pin Assignment**



NO	ITEM	DESCRIPTION	Q'TY	UNIT	PCS
8	A6-0000015	HDMI M DUST CAP	1	pcs	
7	A6-0000146	HDMI F DUST CAP	1	pcs	
6	A6-R104248	HDMI F BLACK ABS JACKET	1	pcs	
5	A2-R020299	HDMI F 19P w/PCB Solder shell gold plated insulation:black	1	pcs	
4	A5-R047001	45P Black PVC	20	g	
3	A5-R047011	Transparent PE	6	g	
2	A2-R020044	HDMI M 19P Shell gold plated solder insulation:Black	1	pc	
1	A4-R001726	High Speed HDMI Cable with Ethernet: UL20276 [30AWG(7/0.102TC) *1PR+DW+AL/MY]*5C+30AWG(7/0.102TC)*4C+AL/MY+DW+Braid(50%AL) +Jacket Color: Black OD:6.0±0.2mm	L	m	
NO	ITEM	DESCRIPTION	Q'TY	UNIT	PCS

Φ	TOLERANCE INCHES	M/M
.X	.015	.30
.XX	.010	.10
.XXX	.005	.05

DRAWN BY		JOE	
CHECK BY			
APPD BY			

<b>Rotronic Co., Ltd.</b>			
TITLE: VALUE HDMI High Speed with Ethernet Cable, M/F, 2M			
CUSTOMER :		11.99.5575	
CUSTOMER P/N :			
SCALE	NONE	DRAWING NO.:	REV. A
UNIT	MM	DATE	12.05.28
			CA1790089
			1/1