


9.2±0.3MM


3000±40mm



ELECTRICAL TEST:

- 1.100% OPEN & SHORT & MIS WIRE TEST
- 2.CONTACT RESISTANCE:2 OHM(MAX)
- 3.INSULATION RESISTANCE:10M OHM(MIN)
- 4.HI-POT TEST:DC 300V/10ms

Pin Assignment



NO	ITEM	DESCRIPTION	Q'TY	UNIT	PCS
8	A6-0000015	HDMI M DUST CAP	1	pcs	
7	A6-0000146	HDMI F DUST CAP	1	pcs	
6	A6-R104248	HDMI F BLACK ABS JACKET	1	pcs	
5	A2-R020299	HDMI F 19P w/PCB Solder shell gold plated insulation:black	1	pcs	
4	A5-R047001	45P Black PVC	20	g	
3	A5-R047011	Transparent PE	6	g	
2	A2-R020044	HDMI M 19P Shell gold plated solder insulation:Black	1	pc	
1	A4-R001727	High Speed HDMI Cable with Ethernet: UL20276 [28AWG(7/0.127TC) *1PR+DW+AL/MY]*5C+28AWG(7/0.127TC)*4C+AL/MY+DW+Braid(50%AL) +Jacket Color: Black OD:7.3±0.2mm	L	m	

TOLERANCE		DRAWN BY	CHECK BY	APPD BY
Φ	INCHES			
	M/M			
.X	.015	JOE		
.XX	.010			
.XXX	.005			
TITLE: VALUE HDMI High Speed with Ethernet Cable, M/F, 3M				
CUSTOMER :				
CUSTOMER P/N :				
SCALE NONE				
UNIT MM				
DATE 12.05.28				
DRAWING NO.:				
REV. A				
CA1790090				

Rotronic Co., Ltd.

DESCRIPTION

NO ITEM

Q'TY

UNIT

m

pcs

pcs

pcs

pcs

g

g

pc

L

1

1

1

1

1

1

1

1

1

1

1

1

1

1

1

1

1

1

1/1