INTERFACE SUPPORTS

UNIVERSAL ENCLOSURES

Mini Series 72mm Empty Modular Interface Supports

HAND HELD CASES

HEAVY DUTY ENCLOSURES

DIN RAIL ENCLOSURES

SUPPORTS

INTERFACE

ELECTRICAL ENCLOSURES

DIECAST & METAL ENCLOSURES

DESKTOP & INSTRUMENT CASES

MULTI-PURPOSE & POTTING BOXES

19" ENCLOSURES

19" CABINETS

DEVELOPMENT BOARD ENCLOSURES

CUSTOM SIZED ENCLOSURES

FSPT/CUSTOM **SERVICES**

- Suitable for 72mm width PCB's
- Modular Construction for easy assembly
- Snap fit DIN Rail mounting fixtures
- Moulded in green UL94-V0 flame retardant PA
- Wall mounting kit option
- Terminal blocks available in same colour
- Integral marker facility
- Registered Design No: 2106418®

- · Available in different colours
- End section foot for top hat DIN Rail


CIME/M



PCB BASE ELEMENTS			END SECTION		PART	
LENGTH	11.25mm	22.5mm	45.0mm	10mm	21.25mm	COUNT
20mm				2		2
31.25mm				1	1	2
42.5mm					2	2
53.75mm	1				2	3
65mm		1			2	3
76.25mm			1	1	1	3
87.5mm			1		2	3
98.75mm	1		1		2	4
110mm		1	1		2	4
121.25mm			2	1	1	4
132.5mm			2		2	4
143.75mm	1		2		2	5
155mm		1	2		2	5
166.25mm			3	1	1	5
177.5mm			3		2	5

The table above shows how, for a given PCB length, modules can be selected to make an interface support

TYPE NO.	DESCRIPTION	WIDTH
CIME/M/BE1125SS	Base element	11.25mm
CIME/M/BE2250SS	Base element	22.5mm
CIME/M/BE4500SS	Base element	45.0mm
CIME/M/SE1125SS	End Section	11.25mm
CIME/M/SE2250SS	End Section	22.5mm
CIME/M/SEF1125SS	End Section with foot	11.25mm
CIME/M/SEF2250SS	End Section with foot	22.5mm
CIME/M/FE0000SS	Foot element	



Wall Mounting Plates

- Flush and raised surface mounting plates
- Press into sides of end section without tool
- Use foot element on long lengths with raised plates

E NO	STYLE	
E/M/MPF	Flush	
E/M/MPR	Raised	



TYPE



