



VanCryst

VS261/VS461 2/4-Port DVI Video Switch

The 2-port VS261 and 4-port VS461 chart a revolutionary new direction in multimedia functionality by combining a Single Link DVI video switch with stereo quality audio. Now you can easily switch between the digital video and audio output of 2/4 digital devices (such as DVD players or computers), and enjoy it on a single DVI display and set of speakers. Conveniently switch between DVI input sources using pushbuttons located on the unit's front panel or sit back and use the IR remote control.

The VS261 / VS461 improves upon previous designs by supporting Single Link DVI (Digital Video Interface), providing superior video quality up to 1920 x 1200. DVI supports both digital video input (flat panel displays, data projectors, plasma displays, digital TVs and set-top boxes) and analog video input (traditional monitors and TVs)




Features

- Displays the video output of two or four digital devices (e.g.,DVD player, computer) on a single DVI display device
- Fully compliant with DVI-Digital and DVI-Analog
- Audio-enabled
- Quick and easy switching via front panel pushbuttons or IR remote control
- Superior video quality up to 1920 x 1200
- Power On Detection if one DVI source is powered off, the VS261/VS461 will automatically switch to the next poweredon source
- Stackable design
- Supports PCs and Macs
- HDCP Compatible

ATEN International Co., Ltd.

3F., No.125, Sec. 2, Datong Rd., Sijhih District., New Taipei City 221, Taiwan Phone: 886-2-8692-6789 Fax: 886-2-8692-6767 www.aten.com E-mail: marketing@aten.com



Video Out DVI	Audio RCA	IR Remote Control

Specification

Function		VS261	VS461	
Computer Connections		2	4	
Port Selection		Pushbuttons; IR Remote Control		
Connectors	Video In	2 x DVI Female	4 x DVI Female	
		(White)	(White)	
	Audio In	4 x Stereo RCA Jack	8 x Stereo RCA Jack	
		Female (Red/White)	Female (Red/White)	
	Video Out	1 x DVI Female (White)		
	Audio Out	2 x Stereo RCA Jack Female (Red/White)		
	Power	1 x DC Jack		
LEDs	Online	2 (Orange)	4 (Orange)	
	Selected	2 (Green)	4 (Green)	
Video		1920 x 1200 @ 60Hz		
Power Consumption		DC 5.3V,1.91W	DC 5.3V,4.93W	
Environment	Operating Temp.	0–50°C		
	Storage Temp.	-20–60°C		
	Humidity	0-80% RH, Non-condensing		
Physical Properties	Housing	Metal		
	Weight	0.50kg	0.75kg	
	Dimensions	14.00x 8.70 x 5.50	21.00 x 8.70 x 5.50	
	(L x W x H)	cm	cm	



Printed 02/2013 V2.0

© Copyright 2013 ATEN® International Co., Ltd. ATEN and the ATEN logo are trademarks of ATEN International Co., Ltd. ATEN and the ATEN logo are trademarks are the property of their respective owners