# **QVT** Split cable glands



Туре	Order No.	Cable inserts	Thread Thread length	PU	Description
QVT 20	45695	1 x QT	M20 x 1.5 Length: 13 mm	10	Ø30,80 24,6 M20x1,5
QVT 25	45702	1 x QT	M25 x 1.5 Length: 13 mm	10	Ø 31  24,6  M25x1,5
QVT 32	45711	1 x QT	M32 x 1.5 Length: 13 mm	10	Ø 39 24,6 M32x1,5
QVT 40   2	45715	2 x QT	M40 x 1.5 Length: 13 mm	10	Ø50 26,4 M40x1,5
QVT 50   4	45722	4 x QT	M50 x 1.5 Length: 13 mm	10	φ62 47,40 M50x1,5



#### Product description

QVT is a circular split frame for quick and easy installation of cables or complete cable harnesses.

The QVT range is especially suitable for small machines, devices and instruments, because of the extremly small structure.

## Advantages

- Compact and small structure
- Routing of assembled cables
- Warranty of pre-terminated cables remains
- Retrofitting and maintenance can be carried out easily and quickly
- Suitable for metric or standard hole sizes
- Locknut is part of delivery.

## Specification

Material Polycarbonate
Colour similar RAL 7035
Flame class UL-94 Vo, self-extinguishing

Protection class IP 54, with gasket and correct

selection of the cable inserts

Temperature - 30°C to + 100°C (static)
Properties halogen-free, silicone-free
Cut-out dimension metric standard sizes

#### Accessories

QT Cable inserts Page 41
KVT-EMC bracket Page 93
KGM locknut Page 124