

Frame type plug-in units PRO with hood

Frame type plug-in units PRO with hood, 3/6 U, front panel shielded (textile gasket)



- Protects a PCB against mechanical damage and deflects electrostatic discharge; for euroboard formats
- Suitable in all subracks and these cases: ratiopacPRO/-air, propacPRO and compacPRO
- Useable connectors in accordance with EN 60603-2 (DIN 41612)
- 2 depths, for 160 mm and 220 mm boards

Delivery comprises (kit)

Item	Qty	Description
1	1	Front panel, U profile, 2.5 mm, front anodised, rear conductive, alignment pin pressed-in
2	1	Handle, grey, PPE, UL 94 V-1
3	1	Side panel, Al extrusion, colourless passivated, with groove for one PCB
4	1	Hood, Al, 1 mm, with perforation, rear panel integrated
5	1	EMC textile gasket
6	1	Assembly kit (incl. PCB fixing for slot 1)

Illustration shows 12 HP width, side panel depth 167 mm

04808007



ServicePLUS see page 7.74

Order Information

	5 HP	6 ... 14 HP	Height U	Width HP	Depth = 167 mm Part no.	Depth = 227 mm Part no.
		3	5	24813-005	24813-055	
		3	6	24813-006	24813-056	
		3	7	24813-007	24813-057	
		3	10	24813-010	24813-060	
		3	12	24813-012	24813-062	
		3	14	24813-014	24813-064	
		6	5	24813-505	24813-555	
		6	6	24813-506	24813-556	
		6	7	24813-507	24813-557	
		6	10	24813-510	24813-560	
		6	12	24813-512	24813-562	
		6	14	24813-514	24813-564	

■ Dimension drawings see from page 7.88