
19" chassis - multipacPRO



h = clear height (overall) (H - 3.0 mm) b = clear installation width = 447 mm



Front handle



ServicePLUS see page 6.118

19" complete chassis from steel with plain top cover and base plate

- Complete chassis, St (AlZn coated) with Al extrusion front panel
- Detachable rear panel for easy machining
- EMC shielding of approx. 30 dB(A) at 1 GHz (without additional shielding material)
- In accordance with standard IEC 60297-3-101
- In the 1 U version 19" and ATX power supplies can be assembled up to a clearance of 40 mm

Delivery comprises (Kit)

Item	Qty	Description	
1	1	Front panel, Al extrusion, 3 mm; in 1 U: front anodised, rear etched;	
		from 2 U: front and rear side of front panels clear passivated	
2	1	Base body, plain, St, 1 mm, (AlZn coated)	
3	1	Rear panel, St, 1 mm (AlZn coated)	
4	1	Cover, plain, St, 1 mm (AlZn coated)	
5	1	Assembly kit	

Order Information

Height	Height H	Depth T	Part no.
U	mm	mm	
1	43.7	220	20860-120
1	43.7	280	20860-121
1	43.7	340	20860-122
2	88.1	280	20860-126
2	88.1	340	20860-127
Accessories			

_	00.1	0-10	20000-127
Accessories			
Front handle anodised, PU	•	t for 1 U, Al extrusion,	20860-256
Front handle anodised, PU	,	t for 2 U, Al extrusion,	20860-257

Note

- Further versions with steel front panel (pizza box) available on request
- Telescopic slides cannot be used
- No special EMC version available
- Standardised internal mounting kits cannot be used



For further information www.schroff.biz/oneclick oneClick search code = Part no.