

## **DATA SHEET**

54115200

## SKINTOP® K-M/KR-M ATEX plus

valid from:

29.11.2013

SKINTOP® K-M/KR-M ATEX *plus* is a special cable gland, based of polyamide. It is particularly designed for the use of electrical equipment in areas with risk of explosion, which require class"e" security (DIN/EN 60079-0, DIN/EN 60079-7, DIN/EN 61241-0, DIN/EN 61241-1).





## **Components:**

Gland Body Plastic polyamide-based, (UL 94 –V2)

Cap Nut Plastic polyamide-based, (UL 94 – V2)

Seal Insert Elastomer

O-Ring NBR (for M12x1.5 up to M63x1.5)

## **Technical features:**

Connecting Thread M12x1.5, up to M63x1.5 in according to EN 60 423, Chart 1

Functional Thread Multi-start trapezoidal thread

IP Protection IP66 and IP 68 in according to EN 60 529

Temperature Range - 20°C up to + 80°C for M12x1,5 up to M63x1,5

Type KR = standard with reduced seal insert

Colour RAL 9005, UV resistant

Approval:







EC Type Examination Certification: IBExU 08 ATEX 1063x

IECEx Certificate IECEx IBE 13.0027x

For more information please see our current catalogue. Please do not hesitate to contact our laboratory if there are any questions regarding resistance against aggressive agents and special oil.

elaborated by:			_
TE-VZ: M. Steinberg	document:	DB54115200_7EN	page 1 von 1