

80BK

FLUKE®

TYPE K INTEGRATED DMM PROBE

- Compatible with multimeters with temperature measurement functions
- Standard banana jack output
- Convenient one-piece construction
- Maximum continuous temperature: 260 °C (500 °F)
- Accuracy: ± 2.2 °C or 2% whichever is greater (0 to 260 °C), ANSI/MC96.1-1982 Standard Tolerances
- Not suitable for liquid immersion
- Warranty: One year



WARNING To avoid the potential for fire or electrical shock do not use this product on electrically live circuits

- For assistance or information on Fluke products call: 800.443.5853 in the USA and Canada, 31.40.2.678.200 in Europe or 425.356.5500 from other countries; or visit us at our website at www.fluke.com

Fluke Corporation
P.O. Box 9090
Everett, WA
98206-9090

Fluke Europe B.V.
P.O. Box 1186
5602 BD Eindhoven,
The Netherlands

P/N 1273124

PLEASE RECYCLE



3/2000

©2000 Fluke Corporation
All rights reserved.
Made in China
www.fluke.com

