

**TEMPERATURE DATALOGGER
SEFRAM LOG 1601****Box content:**

- ✓ 1 Temperature Datalogger SEFRAM
- ✓ 1 USB cable
- ✓ 1 PC software (Compatible with Windows XP, 7, 8)
downloadable from SEFRAM website

Powering-on the datalogger:

To power-on your datalogger, press « START » pushbutton during more than 2 seconds. The datalogger starts and displays temperature.

Installing the software:

Download the software from the SEFRAM website:

<https://bkpmedia.s3.amazonaws.com/downloads/software/LOG1601.zip>

Open the downloaded file and run « setup.exe ». The installation process starts. Please follow the instructions on your computer.

Setting-up the datalogger:

- Connect your datalogger to the PC with the USB cable supplied.
- Press “Start” pushbutton of the datalogger during more than 2 seconds to power-on the datalogger (during first connection your computer will install automatically the driver). The PC and the datalogger are now connected.
- Click on “Temperature Datalogger “ of your computer to run the software
- Click on “Setup” to enter the “Setup” menu
- Define the parameters for your logger (name, sampling time, units...)
- Click on “Save” to save your setup

Recording data (temperature):

To start or stop recording temperature with your datalogger, press « START ». When the datalogger is recording, « REC » symbol is display on the LCD of the datalogger.

Changing units between °C and °F:

Press once on « °C/°F » pushbutton.

Technical specifications:

- Measurement range : -40 to 85°C (-40 to 185°F)
- Accuracy : ± 0,6°C (1,2°F) from -20 to 50°C (-4 to 122°F)
± 1,0°C (1,8°F) for other ranges
- Resolution : 0,1°C
- Memory : 50 000 records
- Display : 3 digits LCD, with units and symbols
- LED : 1 red LED for alarm, 1 green LED for record
- Sampling : 5/10/30 Seconds, 1/5/10/30 Minutes, 1 / 2 Hour
- Battery : 1 battery lithium ½ AA 3,6V
- Battery life time : 1 year (typical)
- External power supply of the datalogger : 5VDC, 0,5A (adapter not supplied)
- Operating temperature : -40 to +85°C
- Storage temperature : -40°C to +85°C
- Dimensions : 85*60*24mm
- Weight : 77g

Optional accessories:

Battery (3.6V ½AA Lithium) : 915005200

Main adaptor: 916201000

Battery replacement:

When the battery symbol shows an empty battery, you have to replace the battery. Save your data, power-off the datalogger and remove the back cover by unscrewing the 4 screws located at the corners. Remove and replace the battery, checking the polarity. Put back the cover and the 4 screws. Be sure to use the same type of battery as the one specified. Your datalogger is ready to work.

SEFRAM
32, rue E. Martel BP 55
F42009 – Saint-Etienne cedex 2 - France
Tel : +33 4.77.59.01.01
Fax : +33 4.77.57.23.23
Web : www.sefram.fr
E-mail : sales@sefram.fr